



This document only lists all tested devices. For specific device models compatible with modules, please view [Optics-to-Device Compatibility Tool](#).

Brand	Model
Cisco	3900 Series
	ASR 902
	ASR 920
	ASR1004-6TGE
	C9200-24PXG-A
	C9200-24PXG-E
	C9300-24H-A
	C9300-24H-E
	C9300-24P-A
	C9300-24P-E
	C9300-24S-A
	C9300-24S-E
	C9300-24S-M
	C9300-24T-A
	C9300-24T-E
	C9300-24TX-A
	C9300-24TX-E
	C9300-24U-A
	C9300-24U-A-UL
	C9300-24U-E
	C9300-24U-E-UL
	C9300-24UB-A

Brand	Model
Cisco	C9300-24UB-E
	C9300-24UX-A
	C9300-24UX-E
	C9300-24UXB-A
	C9300-24UXB-E
	C9300-24UXM-A
	C9300-24UXM-E
	C9300-24Y-A
	C9300-24Y-E
	C9300-24Y-M
	C9300-48H-A
	C9300-48H-E
	C9300-48P-A
	C9300-48P-E
	C9300-48S-A
	C9300-48S-E
	C9300-48S-M
	C9300-48T-A
	C9300-48T-E
	C9300-48TX-A
	C9300-48TX-E
	C9300-48U-A
	C9300-48U-A-UL

Brand	Model
Cisco	C9300-48U-E
	C9300-48U-E-UL
	C9300-48UB-A
	C9300-48UB-E
	C9300-48UN-A
	C9300-48UN-E
	C9300-48UXM-A
	C9300-48UXM-E
	C9300X-12Y
	C9300X-12Y-A
	C9300X-12Y-E
	C9300X-12Y-M
	C9300X-24HX-A
	C9300X-24HX-E
	C9300X-24HX-M
	C9300X-24Y-A
	C9300X-24Y-E
	C9300X-24Y-M
	C9300X-48HX-A
	C9300X-48HX-E
	C9300X-48HX-M
	C9300X-48HXN-A
	C9300X-48HXN-E

Brand	Model
Cisco	C9300X-48HXN-M
	C9300X-48TX-A
	C9300X-48TX-E
	C9300X-48TX-M
	C9300L-24P-4G-A
	C9300L-24P-4G-E
	C9300L-24P-4X-A
	C9300L-24P-4X-E
	C9300L-24P-4X-M
	C9300L-24T-4G-A
	C9300L-24T-4G-E
	C9300L-24T-4X-A
	C9300L-24T-4X-E
	C9300L-24T-4X-M
	C9300L-24UXG-2Q
	C9300L-24UXG-4X-A
	C9300L-24UXG-4X-E
	C9300L-24UXG-4X-M
	C9300L-48P-4G-A
	C9300L-48P-4G-E
	C9300L-48P-4X-A
	C9300L-48P-4X-E
	C9300L-48P-4X-M

Brand	Model
Cisco	C9300L-48PF-4G-A
	C9300L-48PF-4G-E
	C9300L-48PF-4X-A
	C9300L-48PF-4X-E
	C9300L-48PF-4X-M
	C9300L-48T-4G-A
	C9300L-48T-4G-E
	C9300L-48T-4X-A
	C9300L-48T-4X-E
	C9300L-48T-4X-M
	C9300L-48UXG-2Q-A
	C9300L-48UXG-2Q-E
	C9300L-48UXG-4X-A
	C9300L-48UXG-4X-E
	C9300L-48UXG-4X-M
	C9300LM-24U-4Y-A
	C9300LM-24U-4Y-E
	C9300LM-48T-4Y-A
	C9300LM-48T-4Y-E
	C9300LM-48U-4Y-A
	C9300LM-48U-4Y-E
	C9300LM-48UX-4Y-A
	C9300LM-48UX-4Y-E

Brand	Model
Cisco	C9500-24Y4C
	C9500-32C
	C9500-48Y4C
	CBS250-24T-4X
	CBS350-24T-4X
	C1000-8T-2G-L
	C1000-8T-E-2G-L
	C1000-8P-2G-L
	C1000-8P-E-2G-L
	C1000-8FP-2G-L
	C1000-8FP-E-2G-L
	C1000-16T-2G-L
	C1000-16T-E-2G-L
	C1000-16P-2G-L
	C1000-16P-E-2G-L
	C1000-16FP-2G-L
	C1000-24T-4G-L
	C1000-24P-4G-L
	C1000-24FP-4G-L
	C1000-48T-4G-L
	C1000-48P-4G-L
	C1000-48FP-4G-L
	C1000-24T-4X-L

Brand	Model
Cisco	C1000-24P-4X-L
	C1000-24FP-4X-L
	C1000-48T-4X-L
	C1000-48P-4X-L
	C1000-48FP-4X-L
	C1000FE-24T-4G-L
	C1000FE-24P-4G-L
	C1000FE-48T-4G-L
	1000FE-48P-4G-L
	2960X-48FPD-L
	2960X-48LPD-L
	2960X-24PD-L
	2960X-48FPS-L
	2960X-48LPS-L
	2960X-24PS-L
	2960X-24PSQ-L
	Catalyst 3560 Series
	Catalyst 3560-X Series
	Catalyst 3750 Series
	Catalyst 9200L
	Catalyst C9300X-12Y-A
	DS-C9124-K9
	DS-C9134-K9

Brand	Model
Cisco	DS-C9148-32P-K9
	ESW540
	HyperFlex HX240c M4
	ME-3400G-2CS-A V02
	MS425-16
	N3K-C3548P-XL
	N5K-C5672UP
	N540-ACC-SYS
	N9K-C92160YC-X
	N9K-C93180YC-EX
	N9K-C93180YC-FX3
	NCS-5501
	NCS-55A2-MOD-S
	NEXUX 9316D-GX
	NEXUX N3K-C3432D-S
	Nexus 93180YC-FX
	Nexus 93180YC-FX3
	Nexus C9332D-GX2B
	Nexus N9K-C9372PX-E
	Nexus 9332D-GX2B
	SG200-10FP
	SG200-26FP
	SG250X-24

Brand	Model
Cisco	SG350-8PD
	SG500XG-8F8T
	SR2024
	SX350X-24F-K9
	WS-C3560-24TS-S
	WS-C4500X-16SFP+
	WS-C4500X-24X-IPB
	WS-C4500X-24X-ES
	WS-C4500X-32SFP+
	WS-C4500X-40X-ES
	WS-C4500X-F-16SFP+
	WS-C4500X-F-32SFP+
	ACX2100-AC
	EX 4200-24T
Juniper	EX2300-24T
	EX3400-24T
	EX4400-24T
	EX4550
	EX4600
	EX4650-48Y
	MX204
	PTX1000
	PTX10001-36MR

Brand	Model
Juniper	PTX10002-36QDD
	QFX10002-72Q
	QFX5110-48S
	QFX5120-48Y
	QFX5130-32CD
	QFX5200-32C
	QFX5200-32C-32Q
	QFX5200-48Y
	QFX5210-64C
	QFX5220-32CD
	QFX5240-64OD
	QFX5240-64QD
	SRX1500
	SRX380
	7050SX3-48YC12
	7060SX2-48YC6
Arista	7280SR3-48YC8
	DCS-7010T-48
	DCS-7020SR-24C2-R
	DCS-7050QX-32S-R
	DCS-7050SX3-48YC8-R
	DCS-7050TX-64-R
	DCS-7060CX2-32S-R

Brand	Model
Arista	DCS-7060DX4-32
	DCS-7060DX5-64E-F
	DCS-7060PX5-64E-F
	DCS-7124S
	DCS-7280DR3K-24-F
	DCS-7280PR3-24-F
	DCS-7280SR2-48YC6
FS	IES3220-4T2F
	IES5100-24TF
	IES5110-20FMS
	IES5120-28TS-P
	IES5120-48T4S
	IES5220-6S-3ES
	N5860-48SC
	N8000-32Q
	N8550-24CD8D
	N8560-32C
	N8560-48BC
	N8560-64C
	N9510-64D
	NC8200-4TD
	NSG-3100
	NVR202-16C-16P

Brand	Model
FS	S1400-24T4F
	S3150-8T2FP
	S3200-8MG4S-U
	S3250-16TF-U
	S3260-16T4FP
	S3270-10TM-P
	S3400-24T4FP
	S3400-48T6SP
	S3400C-24MG4S-P
	S3410-24TS-P
	S3410-24TF-P
	S3410-48TS-P
	S3700-24T4F
	S3900-24F4S-R
	S3900-24T4S-R
	S3900-48T4S
	S3900-48T6S-R
	S3910-24TF
	S3910-24TS
	S3910-48TS
	S5500-24TF6S
	S5500-48T6SP-R
	S5800-48T4S

Brand	Model
FS	S5800-8TF12S
	S5810-28FS
	S5810-28TS
	S5810-48TS-P
	S5850-24T16B
	S5850-24XMG
	S5850-32S2Q
	S5850-48B8C-PE
	S5850-48S2Q4C
	S5850-48S6Q-R
	S5860-20SQ
	S5860-24MG-U
	S5860-24XB-U
	S5860-48SC
	S5860-48XMG-U
3Com	S8050-20Q4C
	S8550-6Q2C
ADTRAN	3CR17402-91
Alcatel-Lucent	NetVanta 1638
	OS6900
	OS6900X48
Allied Telesis	OmniSwitch 6850-48
	AT-x950-28XSQ

Brand	Model
Aruba	2930F(JL255A)
	6300M(JL658A)
	CX 6100
	CX10000-48Y6C(R8P13A)
	CX10000-48Y6C(R8S96A)
	CX 8325P-32C
	JL624A 8325-48Y8C
	JL625A 8325-48Y8C
	JL626A 8325-32C
	JL627A 8325-32C
	JL857A 8325-48Y8C
	JL858A 8325-48Y8C
	JL859A 8325-32C
	JL860A 8325-32C
BALADE	S2500-24P
	RackSwitch G8000
Brocade	Brocade 300
	Brocade 5100
	ICX 6610-48
	ICX7750-48F
	ICX7850-48F
	VDX-6720
	VDX6940-144S

Brand	Model
CentreCom	9242T/SP
Ciena	5164-AC
	Ciena 3930
	DGS-1210-28MP
D-Link	DGS-1510-28X
	DWS-3227
	DXS-5000-54S
Dell	EMC S5232F-ON
	S4048F-ON
	S4112F-ON
	S4148F-ON
	S5048-ON
	S5248F-ON
	S5448F-ON
Edge-Core	Z9332F-ON
	5812-54X-O-AC-B-US
	DCS203(AS7326-56X)
Extreme	BR-SLX-9540-24S-AC-F
	SLX 9140
	Summit X670V-48t
	X440-G2-24p-10GE4
Fortinet	X690-48x-2q-4c
	FortiSwitch 1048E

Brand	Model
Fortinet	FortiGate 600E
H3C	FlexFabric 5900
	FlexFabric 5950 32QSFP28
	S3600
	S6520X-30HC-EI
	5400R ZL2
HP	Comware Switch 5710(JL585A)
	ProCurve 1800-24G
	Procurve 2824 Switch J4903A
	ProCurve Switch 5406zl(J8697A)
	StorageWorks 2/12 Edge
HUAWEI	CE6860-48S8CQ-EI
	CE6863E-48S6CQ
	CE6880-24S4Q2CQ-EI
	S5720-32X-E1-AC
	S5732-H24S6Q
	S6720-30L-HI-24S
	S6720S-26Q-LI-24S-AC
	Secospace USG6305
	Secospace USG6305-W
	Secospace USG6306
	Secospace USG6308
	Secospace USG6310

Brand	Model
HUAWEI	Secospace USG6310S
	Secospace USG6310S-W
	Secospace USG6310S-WL
	Secospace USG6310S-WL-OVS
	Secospace USG6320
	Secospace USG6330
	Secospace USG6350
	Secospace USG6360
	Secospace USG6370
	Secospace USG6380
	Secospace USG6390
	Secospace USG6390E
	Secospace USG6507
	Secospace USG6510
	Secospace USG6510-WL
	Secospace USG6530
	Secospace USG6550
	Secospace USG6570
	Secospace USG6620
	Secospace USG6630
	Secospace USG6650
	Secospace USG6660
	Secospace USG6670

Brand	Model
HUAWEI	Secospace USG6680
	USG6101
	USG6106
	USG6110
	USG6120
	USG6150
	USG6160
	USG6180
MikroTik	CCR1009-7G-1C-1S+
	CCR1036-12G-4S-EM
	CRS326-24S+2Q+RM
	CRS504-4XQ-IN
	CRS520-4XS-16XQ-RM
Netgear	GS324TP
	GS728T
	GS748T
	GS752TS
	GS752TXS
	M4100-D12G
	M4200-10MG-POE+
	M4300-24X24F
	M4300-52G
	M4500-48XF8C

Brand	Model
Netgear	M5300-28GF3
	MS510TX
	S3300-52X
	XS708T
	XS712T
	XS748T
Nvidia/Mellanox	MQM8700-HS2F
	MQM9700-NS2F
	MQM9790-NS2F
	MSB7800-ES2F
	MSN2410-CB2F
	MSN4700-WS2FC
	SN2010
	SN2700
	SN3420-CB2FC
	SN3700
Ubiquiti	SN5600
	SX1024
	ES-48-750W
	US-16-XG
	US-8-60W



Shenzhen (China)

Address: 24F, Yingfeng Center, Haitian 2nd Rd,
Nanshan District, Shenzhen
Tel: +86 400 865 2852
Email: sales@feisu.com

Delaware (United States)

Address: 380 Centerpoint Blvd, New Castle,
DE 19720, United States
Tel: +1 (888) 468 9910
Email: us@fs.com

Munich (Germany)

Address: NOVA Gewerbepark Building 7, Am
Gfild 7,85375 Neufahrn bei Munich, Germany
Tel: +49 (0) 8131 377 3008
Email: de@fs.com

Singapore

Address: 30A Kallang Pl, #11-10/11/12 Singapore
339213
Tel: +65 3138 1992
Email: sg@fs.com

Wuhan (China)

Address: 9-14F, Optical Valley Software Park
A7, Guanshan Ave, Wuhan
Tel: +86 400 865 2852
Email: sales@feisu.com

Birmingham (United Kingdom)

Address: Regus Edmund House, 12-22 Newhall
Street, Birmingham, B3 3AS
Tel: +44 (0) 121 726 4775
Email: uk@fs.com

Melbourne (Australia)

Address: 57-59 Edison Rd, Dandenong South,
VIC 3175, Australia
Tel: +613 5909 9990
Email: au@fs.com

Tokyo (Japan)

Address: JS Progress Building, 4-1-23 Heiwajima,
Ota-ku, Tokyo 〒143-0006
Tel: +813 6897 9438
Email: jp@fs.com



FS has several offices around the world. Addresses, phone numbers are listed on the FS Website at https://www.fs.com/contact_us.html
FS and FS logo are trademarks or registered trademarks of FS in the U.S. and other countries.