


Transceivers DACs and AOCs Supported on S5860-20SQ Switch



Supported Transceivers and Cables Information

The following tables list supported 1G SFP, 10G SFP+, 25G SFP28 and 40G QSFP+ transceivers and cables for S5860-20SQ switch. This switch was tested by FS technicians to ensure compatibility.

Model of Switch

- S5860-20SQ

S5860-20SQ Switch Stacking Compatible State

S5860-20SQ switch is compatible with a variety of high-speed cables and transceivers and can realize stacking. Here’s a look at the details.

Transceivers Stacking Compatible Datasheet

Description	ID	Rate	S5860-20SQ	Remarks
			Compatibility	
SFP-GB-GE-T	11773	1000BASE-T	√	
SFP1G-SX-85	11774	1G	√	
SFP1G-LX-31	11775	1G	√	
SFP1G-EX-55	49943	1G	√	
SFP1G-ZX-55	11776	1G	√	
CWDM-SFP1G-ZX	33234	1G	√	
DWDM-SFP1G-ZX	47697	1G	√	
SFP-GE-BX	11802/11795	1G	√	
SFP-GE-BX40	36889/36888	1G	√	
SFP-GE-BX60	37953/37958	1G	√	
SFP-GE-BX80	49480/49481	1G	√	
SFP-10GSR-85	11552	10G	√	
SFP-10GLR-31	11555	10G	√	
SFP-10GLRM-31	11556	10G	√	
SFP-10GER-31	48813	10G	√	
SFP-10GER-55	11557	10G	√	
SFP-10GZR-55	36436	10G	√	
CWDM-SFP10G-80（1490nm）	19368	10G	√	
CWDM-SFP10G-80（1490nm）	19369	10G	√	
CWDM-SFP10G-80（1530nm）	19370	10G	√	
CWDM-SFP10G-80（1550nm）	19371	10G	√	
DWDM-SFP10G-80（C17-C61）	31202	10G	√	
SFP-10G-BX	36351/36353	10G	√	

Transceivers Stacking Compatible Datasheet


Description	ID	Rate	S5860-20SQ	Remarks
			Compatibility	
SFP-10G-BX40	19359/19358	10G	√	
SFP-10G-BX60	37075/37076	10G	√	
SFP-10G-BX80	42492/42488	10G	√	
SFP28-25GSR-85	67991	25G	√	
QSFP-SR4-40G	36157	40G	√	
QSFP-CSR4-40G	36165	40G	√	
QSFP-LX4-40G	48724	40G	√	
QSFP-LR4-40G	36170	40G	√	
CVR-QSFP-SFP10G	72582	40G	√	

Cables Stacking Compatible Datasheet

Description	ID	Length (m)	S5860-20SQ	Remarks
			Compatibility	
10G SFP+ Passive Direct Attach Copper Twinax Cable	30856	2	√	
	30862	3	√	
25G SFP28 Passive Direct Attach Copper Twinax Cable	65843	3	√	
40G QSFP+ Passive Direct Attach Copper Twinax Cable	30884	1	√	
	48948	2	√	
40G QSFP+ to 4x 10G SFP+ Passive Direct Attach Copper Twinax Cable	48867	2	√	
	30903	3	√	
10G SFP+ Active Optical Cable	30889	3	√	
	30890	5	√	
	30895	10	√	

Cables Stacking Compatible Datasheet

Description	ID	Length (m)	S5860-20SQ	Remarks
			Compatibility	
25G SFP28 Active Optical Cable	68337	5	√	
	68339	10	√	
40G QSFP+ Active Optical Cable	30910	2	√	
	30912	5	√	
40G QSFP+ to 4x 10G SFP+ Active Optical Cable	30905	2	√	
	30907	5	√	



 <https://www.fs.com>



The information in this document is subject to change without notice. FS has made all efforts to ensure the accuracy of the information, but all information in this document does not constitute any kind of warranty.