



IxNetwork Report

Test: RFC2544 - Throughput/Latency

Test Date: 10/14/2020 15:40:47

www.ixiacom.com
www.ixiacom.com/support

Table of Contents

1.	Cover	1
2.	Info	3
3.	Port Map	4
4.	Aggregate Graphs	5
5.	IterationCharts	13
6.	Aggregated Results	19
7.	Aggregated Results Per Iteration	20
8.	Per Flow Results	25
9.	Iteration Data	27
10.	Theoretical Max Rates	36

RFC2544 - Throughput/Latency - Info**Test Information****Product Information**

Product Label :	S5800-48F4SR
Product Version :	7.2.4.7
Serial Number :	CG2002249482N0028
Comments :	

Test Settings

Date Executed :	10/14/2020
Time Executed :	15:40:47
User Name :	FS.COM
Number of Trials Executed :	1
Stream Duration (sec) :	20

Output Parameters


Number of Trials Passed :	N/A
Test Duration :	00:35:57

RFC2544 - Throughput/Latency - Port Map Information


Port Map :	Tx Port	Tx Speed (Mbps)	Rx Port	Rx Speed (Mbps)
	10.32.133.101:3:9	1000	10.32.133.101:3:11	1000

RFC2544 - Throughput/Latency - Aggregated Graph

Total Frames Transmitted and Received




RFC2544 - Throughput/Latency - Aggregated Graph



RFC2544 - Throughput/Latency - Aggregated Graph


Aggregated Frame Loss



Trial - Framesize - Iteration


RFC2544 - Throughput/Latency - Aggregated Graph

Aggregated Frame Loss per Frame Size




RFC2544 - Throughput/Latency - Aggregated Graph


Aggregated Frame Loss per Line Rate



RFC2544 - Throughput/Latency - Per Flow Graph





RFC2544 - Throughput/Latency - Aggregated Graph



RFC2544 - Throughput/Latency - Per Flow Graph


Tx / Rx Frame Count




Trial

RFC2544 - Throughput/Latency - Iteration Graph


Aggregated Frame Loss for Trial 1 and Framesize 64




Aggregated Frame Loss for Trial 1 and Framesize 128






Aggregated Frame Loss for Trial 1 and Framesize 256



Aggregated Frame Loss for Trial 1 and Framesize 512




Aggregated Frame Loss for Trial 1 and Framesize 1024**Aggregated Frame Loss for Trial 1 and Framesize 1280**


Aggregated Frame Loss for Trial 1 and Framesize 1518

RFC2544 - Throughput/Latency - Iteration Graph

Tx / Rx Frames per Frame Size



RFC2544 - Throughput/Latency - Iteration Graph



RFC2544 - Throughput/Latency - Aggregated Results

Trial / Framesize / Iteration	Agg L2 Throughput				Agg L1 Throughput		Throughput (frames)		Agg Latency			
	AggTx Rate %	Agg Rx Rate			Tx Rate Mbps	Rx Rate Mbps			Min (ns)	Max (ns)	Average (ns)	
		%	FPS	Mbps								
Trial: 1 / FS: 64 / Iter: 9	100.00	100	1488095.2	761.905			Tx : Rx : Loss : Loss% :	29761905.000 29761905.000 0 0.00	875	895	883.000	
Trial: 1 / FS: 128 / Iter: 9	100.00	100	844594.6	864.865			Tx : Rx : Loss : Loss% :	16891892.000 16891892.000 0 0.00	907	935	921.000	
Trial: 1 / FS: 256 / Iter: 9	100.00	100	452898.6	927.536			Tx : Rx : Loss : Loss% :	9057971.000 9057971.000 0 0.00	732	760	743.000	
Trial: 1 / FS: 512 / Iter: 9	100.00	100	234962.4	962.406			Tx : Rx : Loss : Loss% :	4699248.000 4699248.000 0 0.00	740	757	746.000	
Trial: 1 / FS: 1024 / Iter: 9	100.00	100	119731.8	980.843			Tx : Rx : Loss : Loss% :	2394636.000 2394636.000 0 0.00	740	757	746.000	
Trial: 1 / FS: 1280 / Iter: 9	100.00	100	96153.8	984.615			Tx : Rx : Loss : Loss% :	1923077.000 1923077.000 0 0.00	732	757	743.000	
Trial: 1 / FS: 1518 / Iter: 9	100.00	100	81274.4	986.996			Tx : Rx : Loss : Loss% :	1625488.000 1625488.000 0 0.00	730	760	745.000	

RFC2544 - Throughput/Latency - Aggregated Results

Trial / Framesize / Iteration	Agg L2 Throughput				Agg L1 Throughput		Throughput (frames)	Agg Latency			
	Agg Tx Rate %	Agg Rx Rate			Tx Rate Mbps	Rx Rate Mbps		Min (ns)	Max (ns)	Average (ns)	
		%	FPS	Mbps							
Trial: 1 / FS: 64 / Iter: 1	10	10	148809.5	76.190			Tx : 2976190.000 Rx : 2976190.000 Loss : 0 Loss% : 0.00	870	892	880.000	
Trial: 1 / FS: 64 / Iter: 2	55	55	818452.5	419.048			Tx : 16369048.000 Rx : 16369048.000 Loss : 0 Loss% : 0.00	862	895	879.000	
Trial: 1 / FS: 64 / Iter: 3	78	78	1153274.7	590.477			Tx : 23065476.000 Rx : 23065476.000 Loss : 0 Loss% : 0.00	860	895	879.000	
Trial: 1 / FS: 64 / Iter: 4	89	89	1320685.0	676.191			Tx : 26413690.000 Rx : 26413690.000 Loss : 0 Loss% : 0.00	860	895	879.000	
Trial: 1 / FS: 64 / Iter: 5	94	94	1404391.1	719.048			Tx : 28087798.000 Rx : 28087798.000 Loss : 0 Loss% : 0.00	867	895	879.000	
Trial: 1 / FS: 64 / Iter: 6	97	97	1446242.7	740.476			Tx : 28924851.000 Rx : 28924851.000 Loss : 0 Loss% : 0.00	867	895	879.000	
Trial: 1 / FS: 64 / Iter: 7	99	99	1467169.8	751.191			Tx : 29343378.000 Rx : 29343378.000 Loss : 0 Loss% : 0.00	867	895	880.000	
Trial: 1 / FS: 64 / Iter: 8	99	99	1477633.5	756.548			Tx : 29552641.000 Rx : 29552641.000 Loss : 0 Loss% : 0.00	867	895	881.000	
Trial: 1 / FS: 64 / Iter: 9	100	100	1488095.2	761.905			Tx : 29761905.000 Rx : 29761905.000 Loss : 0 Loss% : 0.00	875	895	883.000	
Trial: 1 / FS: 128 / Iter: 1	10	10	84459.5	86.486			Tx : 1689189.000 Rx : 1689189.000 Loss : 0 Loss% : 0.00	867	892	879.000	
Trial: 1 / FS: 128 / Iter: 2	55	55	464527.2	475.676			Tx : 9290541.000 Rx : 9290541.000 Loss : 0 Loss% : 0.00	867	895	878.000	
Trial: 1 / FS: 128 / Iter: 3	78	78	654561.0	670.271			Tx : 13091216.000 Rx : 13091216.000 Loss : 0 Loss% : 0.00	867	895	878.000	
Trial: 1 / FS: 128 / Iter: 4	89	89	749577.8	767.568			Tx : 14991554.000 Rx : 14991554.000 Loss : 0 Loss% : 0.00	867	895	878.000	

Trial: 1 / FS: 128 / Iter: 5	94	94	797086.2	816.216	Tx : Rx : Loss : Loss% :	15941723.000 15941723.000 0 0.00	867	895	879.000
Trial: 1 / FS: 128 / Iter: 6	97	97	820840.6	840.541	Tx : Rx : Loss : Loss% :	16416807.000 16416807.000 0 0.00	867	895	878.000
Trial: 1 / FS: 128 / Iter: 7	99	99	832717.5	852.703	Tx : Rx : Loss : Loss% :	16654350.000 16654350.000 0 0.00	867	895	879.000
Trial: 1 / FS: 128 / Iter: 8	99	99	838656.3	858.784	Tx : Rx : Loss : Loss% :	16773121.000 16773121.000 0 0.00	907	935	918.000
Trial: 1 / FS: 128 / Iter: 9	100	100	844594.6	864.865	Tx : Rx : Loss : Loss% :	16891892.000 16891892.000 0 0.00	907	935	921.000
Trial: 1 / FS: 256 / Iter: 1	10	10	45289.9	92.754	Tx : Rx : Loss : Loss% :	905797.000 905797.000 0 0.00	725	757	739.000
Trial: 1 / FS: 256 / Iter: 2	55	55	249094.2	510.145	Tx : Rx : Loss : Loss% :	4981884.000 4981884.000 0 0.00	725	760	740.000
Trial: 1 / FS: 256 / Iter: 3	78	78	350996.4	718.841	Tx : Rx : Loss : Loss% :	7019928.000 7019928.000 0 0.00	725	760	740.000
Trial: 1 / FS: 256 / Iter: 4	89	89	401947.6	823.189	Tx : Rx : Loss : Loss% :	8038949.000 8038949.000 0 0.00	725	760	740.000
Trial: 1 / FS: 256 / Iter: 5	94	94	427423.1	875.362	Tx : Rx : Loss : Loss% :	8548460.000 8548460.000 0 0.00	725	760	740.000
Trial: 1 / FS: 256 / Iter: 6	97	97	440160.8	901.449	Tx : Rx : Loss : Loss% :	8803216.000 8803216.000 0 0.00	725	760	740.000
Trial: 1 / FS: 256 / Iter: 7	99	99	446529.8	914.493	Tx : Rx : Loss : Loss% :	8930593.000 8930593.000 0 0.00	725	760	740.000
Trial: 1 / FS: 256 / Iter: 8	99	99	449714.2	921.015	Tx : Rx : Loss : Loss% :	8994282.000 8994282.000 0 0.00	725	760	740.000
Trial: 1 / FS: 256 / Iter: 9	100	100	452898.6	927.536	Tx : Rx : Loss : Loss% :	9057971.000 9057971.000 0 0.00	732	760	743.000
Trial: 1 / FS: 512 / Iter: 1	10	10	23496.2	96.241	Tx : Rx : Loss : Loss% :	469925.000 469925.000 0 0.00	730	755	742.000

Trial: 1 / FS: 512 / Iter: 2	55	55	129229.3	529.323	Tx : Rx : Loss : Loss% :	2584586.000 2584586.000 0 0.00	730	757	743.000
Trial: 1 / FS: 512 / Iter: 3	78	78	182095.9	745.865	Tx : Rx : Loss : Loss% :	3641917.000 3641917.000 0 0.00	730	757	743.000
Trial: 1 / FS: 512 / Iter: 4	89	89	208529.1	854.135	Tx : Rx : Loss : Loss% :	4170583.000 4170583.000 0 0.00	730	757	743.000
Trial: 1 / FS: 512 / Iter: 5	94	94	221745.8	908.271	Tx : Rx : Loss : Loss% :	4434915.000 4434915.000 0 0.00	730	757	743.000
Trial: 1 / FS: 512 / Iter: 6	97	97	228354.1	935.338	Tx : Rx : Loss : Loss% :	4567082.000 4567082.000 0 0.00	730	757	743.000
Trial: 1 / FS: 512 / Iter: 7	99	99	231658.3	948.872	Tx : Rx : Loss : Loss% :	4633165.000 4633165.000 0 0.00	730	757	743.000
Trial: 1 / FS: 512 / Iter: 8	99	99	233310.3	955.639	Tx : Rx : Loss : Loss% :	4666207.000 4666207.000 0 0.00	730	757	743.000
Trial: 1 / FS: 512 / Iter: 9	100	100	234962.4	962.406	Tx : Rx : Loss : Loss% :	4699248.000 4699248.000 0 0.00	740	757	746.000
Trial: 1 / FS: 1024 / Iter: 1	10	10	11973.2	98.084	Tx : Rx : Loss : Loss% :	239464.000 239464.000 0 0.00	732	755	744.000
Trial: 1 / FS: 1024 / Iter: 2	55	55	65852.5	539.464	Tx : Rx : Loss : Loss% :	1317050.000 1317050.000 0 0.00	732	757	744.000
Trial: 1 / FS: 1024 / Iter: 3	78	78	92792.2	760.153	Tx : Rx : Loss : Loss% :	1855843.000 1855843.000 0 0.00	732	757	744.000
Trial: 1 / FS: 1024 / Iter: 4	89	89	106262.0	870.498	Tx : Rx : Loss : Loss% :	2125239.000 2125239.000 0 0.00	732	757	744.000
Trial: 1 / FS: 1024 / Iter: 5	94	94	112996.9	925.671	Tx : Rx : Loss : Loss% :	2259938.000 2259938.000 0 0.00	732	757	744.000
Trial: 1 / FS: 1024 / Iter: 6	97	97	116364.3	953.257	Tx : Rx : Loss : Loss% :	2327287.000 2327287.000 0 0.00	732	757	744.000
Trial: 1 / FS: 1024 / Iter: 7	99	99	118048.1	967.050	Tx : Rx : Loss : Loss% :	2360961.000 2360961.000 0 0.00	732	757	744.000

Trial: 1 / FS: 1024 / Iter: 8	99	99	118889.9	973.946	Tx : Rx : Loss : Loss% :	2377799.000 2377799.000 0 0.00	732	757	743.000
Trial: 1 / FS: 1024 / Iter: 9	100	100	119731.8	980.843	Tx : Rx : Loss : Loss% :	2394636.000 2394636.000 0 0.00	740	757	746.000
Trial: 1 / FS: 1280 / Iter: 1	10	10	9615.4	98.462	Tx : Rx : Loss : Loss% :	192308.000 192308.000 0 0.00	732	757	743.000
Trial: 1 / FS: 1280 / Iter: 2	55	55	52884.6	541.538	Tx : Rx : Loss : Loss% :	1057692.000 1057692.000 0 0.00	732	760	744.000
Trial: 1 / FS: 1280 / Iter: 3	78	78	74519.2	763.077	Tx : Rx : Loss : Loss% :	1490385.000 1490385.000 0 0.00	732	760	744.000
Trial: 1 / FS: 1280 / Iter: 4	89	89	85336.5	873.846	Tx : Rx : Loss : Loss% :	1706731.000 1706731.000 0 0.00	732	760	744.000
Trial: 1 / FS: 1280 / Iter: 5	94	94	90745.2	929.231	Tx : Rx : Loss : Loss% :	1814904.000 1814904.000 0 0.00	732	760	744.000
Trial: 1 / FS: 1280 / Iter: 6	97	97	93449.5	956.923	Tx : Rx : Loss : Loss% :	1868990.000 1868990.000 0 0.00	732	760	744.000
Trial: 1 / FS: 1280 / Iter: 7	99	99	94801.7	970.769	Tx : Rx : Loss : Loss% :	1896034.000 1896034.000 0 0.00	732	760	743.000
Trial: 1 / FS: 1280 / Iter: 8	99	99	95477.8	977.692	Tx : Rx : Loss : Loss% :	1909555.000 1909555.000 0 0.00	732	760	743.000
Trial: 1 / FS: 1280 / Iter: 9	100	100	96153.8	984.615	Tx : Rx : Loss : Loss% :	1923077.000 1923077.000 0 0.00	732	757	743.000
Trial: 1 / FS: 1518 / Iter: 1	10	10	8127.4	98.700	Tx : Rx : Loss : Loss% :	162549.000 162549.000 0 0.00	732	757	742.000
Trial: 1 / FS: 1518 / Iter: 2	55	55	44700.9	542.848	Tx : Rx : Loss : Loss% :	894018.000 894018.000 0 0.00	730	760	743.000
Trial: 1 / FS: 1518 / Iter: 3	78	78	62987.6	764.922	Tx : Rx : Loss : Loss% :	1259753.000 1259753.000 0 0.00	730	760	743.000
Trial: 1 / FS: 1518 / Iter: 4	89	89	72131.0	875.959	Tx : Rx : Loss : Loss% :	1442620.000 1442620.000 0 0.00	730	760	743.000

Trial: 1 / FS: 1518 / Iter: 5	94	94	76702.7	931.478	Tx :	1534054.000	730	760	743.000
					Rx :	1534054.000			
					Loss :	0			
					Loss% :	0.00			
Trial: 1 / FS: 1518 / Iter: 6	97	97	78988.5	959.237	Tx :	1579771.000	730	760	743.000
					Rx :	1579771.000			
					Loss :	0			
					Loss% :	0.00			
Trial: 1 / FS: 1518 / Iter: 7	99	99	80131.5	973.117	Tx :	1602629.000	730	760	743.000
					Rx :	1602629.000			
					Loss :	0			
					Loss% :	0.00			
Trial: 1 / FS: 1518 / Iter: 8	99	99	80702.9	980.056	Tx :	1614058.000	730	760	743.000
					Rx :	1614058.000			
					Loss :	0			
					Loss% :	0.00			
Trial: 1 / FS: 1518 / Iter: 9	100	100	81274.4	986.996	Tx :	1625488.000	730	760	745.000
					Rx :	1625488.000			
					Loss :	0			
					Loss% :	0.00			

RFC2544 - Throughput/Latency - Per Flow Statistics - Part 1 of 2

Trial / Framesize / Iteration	Tx Port	Rx Port	Flow Group	L2 Throughput				L1 Throughput		Throughput (frames)
				Tx Rate %	Rx Rate			Tx Rate Mbps	Rx Rate Mbps	
					%	FPS	Mbps			
Trial: 1 / FS: 64 / Iter: 9	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	100.00	100	1488095.2	761.91			Tx : 29761905 Rx : 29761905 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 9	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	100.00	100	844594.6	864.87			Tx : 16891892 Rx : 16891892 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 9	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	100.00	100	452898.6	927.54			Tx : 9057971 Rx : 9057971 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 9	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	100.00	100	234962.4	962.41			Tx : 4699248 Rx : 4699248 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 9	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	100.00	100	119731.8	980.84			Tx : 2394636 Rx : 2394636 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 9	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	100.00	100	96153.8	984.62			Tx : 1923077 Rx : 1923077 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 9	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	100.00	100	81274.4	987.00			Tx : 1625488 Rx : 1625488 Loss : 0 Loss% : 0.000

RFC2544 - Throughput/Latency - Per Flow Statistics - Part 2 of 2

Trial / Framesize / Iteration	Tx Port	Rx Port	Flow Group	Min Latency (ns)	Max Latency (ns)	Avg Latency (ns)
Trial: 1 / FS: 64 / Iter: 9	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	875	895	883
Trial: 1 / FS: 128 / Iter: 9	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	907	935	921
Trial: 1 / FS: 256 / Iter: 9	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	732	760	743
Trial: 1 / FS: 512 / Iter: 9	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	740	757	746
Trial: 1 / FS: 1024 / Iter: 9	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	740	757	746
Trial: 1 / FS: 1280 / Iter: 9	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	732	757	743
Trial: 1 / FS: 1518 / Iter: 9	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	730	760	745

RFC2544 - Throughput/Latency - Iteration Statistics - Part 1 of 2

Trial / Framesize / Iteration	Tx Port	Rx Port	Flow Group	L2 Throughput				L1 Throughput		Throughput (frames)	
				Tx Rate %	%	FPS	Mbps	Tx Rate Mbps	Rx Rate Mbps		
Trial: 1 / FS: 64 / Iter: 1	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	10.00	10.00	148809.5	76.19			Tx : 2976190 Rx : 2976190 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 2	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	55.00	55.00	818452.5	419.05			Tx : 16369048 Rx : 16369048 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 3	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	77.50	77.50	1153274.7	590.48			Tx : 23065476 Rx : 23065476 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 4	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	88.75	88.75	1320685.0	676.19			Tx : 26413690 Rx : 26413690 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 5	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	94.38	94.38	1404391.1	719.05			Tx : 28087798 Rx : 28087798 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 6	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	97.19	97.19	1446242.7	740.48			Tx : 28924851 Rx : 28924851 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 7	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	98.59	98.59	1467169.8	751.19			Tx : 29343378 Rx : 29343378 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 8	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	99.30	99.30	1477633.5	756.55			Tx : 29552641 Rx : 29552641 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 9	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	100.00	100.00	1488095.2	761.91			Tx : 29761905 Rx : 29761905 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 128 / Iter: 1	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	10.00	10.00	84459.5	86.49			Tx : 1689189 Rx : 1689189 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 128 / Iter: 2	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	55.00	55.00	464527.2	475.68			Tx : 9290541 Rx : 9290541 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 128 / Iter: 3	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	77.50	77.50	654561.0	670.27			Tx : 13091216 Rx : 13091216 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 128 / Iter: 4	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	88.75	88.75	749577.8	767.57			Tx : 14991554 Rx : 14991554 Loss : 0 Loss% : 0.000	

Trial: 1 / FS: 128 / Iter: 5	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	94.38	94.38	797086.2	816.22	Tx : 15941723 Rx : 15941723 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 6	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	97.19	97.19	820840.6	840.54	Tx : 16416807 Rx : 16416807 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 7	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	98.59	98.59	832717.5	852.70	Tx : 16654350 Rx : 16654350 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 8	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	99.30	99.30	838656.3	858.78	Tx : 16773121 Rx : 16773121 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 9	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	100.00	100.00	844594.6	864.87	Tx : 16891892 Rx : 16891892 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 1	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	10.00	10.00	45289.9	92.75	Tx : 905797 Rx : 905797 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 2	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	55.00	55.00	249094.2	510.15	Tx : 4981884 Rx : 4981884 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 3	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	77.50	77.50	350996.4	718.84	Tx : 7019928 Rx : 7019928 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 4	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	88.75	88.75	401947.6	823.19	Tx : 8038949 Rx : 8038949 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 5	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	94.38	94.38	427423.1	875.36	Tx : 8548460 Rx : 8548460 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 6	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	97.19	97.19	440160.8	901.45	Tx : 8803216 Rx : 8803216 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 7	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	98.59	98.59	446529.8	914.49	Tx : 8930593 Rx : 8930593 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 8	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	99.30	99.30	449714.2	921.02	Tx : 8994282 Rx : 8994282 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 9	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	100.00	100.00	452898.6	927.54	Tx : 9057971 Rx : 9057971 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 1	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	10.00	10.00	23496.2	96.24	Tx : 469925 Rx : 469925 Loss : 0 Loss% : 0.000

Trial: 1 / FS: 512 / Iter: 2	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	55.00	55.00	129229.3	529.32	Tx : 2584586	Rx : 2584586	Loss : 0	Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 3	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	77.50	77.50	182095.9	745.87	Tx : 3641917	Rx : 3641917	Loss : 0	Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 4	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	88.75	88.75	208529.1	854.14	Tx : 4170583	Rx : 4170583	Loss : 0	Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 5	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	94.38	94.38	221745.8	908.27	Tx : 4434915	Rx : 4434915	Loss : 0	Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 6	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	97.19	97.19	228354.1	935.34	Tx : 4567082	Rx : 4567082	Loss : 0	Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 7	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	98.59	98.59	231658.3	948.87	Tx : 4633165	Rx : 4633165	Loss : 0	Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 8	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	99.30	99.30	233310.3	955.64	Tx : 4666207	Rx : 4666207	Loss : 0	Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 9	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	100.00	100.00	234962.4	962.41	Tx : 4699248	Rx : 4699248	Loss : 0	Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 1	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	10.00	10.00	11973.2	98.08	Tx : 239464	Rx : 239464	Loss : 0	Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 2	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	55.00	55.00	65852.5	539.46	Tx : 1317050	Rx : 1317050	Loss : 0	Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 3	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	77.50	77.50	92792.2	760.15	Tx : 1855843	Rx : 1855843	Loss : 0	Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 4	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	88.75	88.75	106262.0	870.50	Tx : 2125239	Rx : 2125239	Loss : 0	Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 5	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	94.38	94.38	112996.9	925.67	Tx : 2259938	Rx : 2259938	Loss : 0	Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 6	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	97.19	97.19	116364.3	953.26	Tx : 2327287	Rx : 2327287	Loss : 0	Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 7	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	98.59	98.59	118048.1	967.05	Tx : 2360961	Rx : 2360961	Loss : 0	Loss% : 0.000

Trial: 1 / FS: 1024 / Iter: 8	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	99.30	99.30	118889.9	973.95	Tx : 2377799 Rx : 2377799 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 9	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	100.00	100.00	119731.8	980.84	Tx : 2394636 Rx : 2394636 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 1	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	10.00	10.00	9615.4	98.46	Tx : 192308 Rx : 192308 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 2	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	55.00	55.00	52884.6	541.54	Tx : 1057692 Rx : 1057692 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 3	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	77.50	77.50	74519.2	763.08	Tx : 1490385 Rx : 1490385 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 4	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	88.75	88.75	85336.5	873.85	Tx : 1706731 Rx : 1706731 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 5	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	94.38	94.38	90745.2	929.23	Tx : 1814904 Rx : 1814904 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 6	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	97.19	97.19	93449.5	956.92	Tx : 1868990 Rx : 1868990 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 7	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	98.59	98.59	94801.7	970.77	Tx : 1896034 Rx : 1896034 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 8	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	99.30	99.30	95477.8	977.69	Tx : 1909555 Rx : 1909555 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 9	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	100.00	100.00	96153.8	984.62	Tx : 1923077 Rx : 1923077 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 1	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	10.00	10.00	8127.4	98.70	Tx : 162549 Rx : 162549 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 2	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	55.00	55.00	44700.9	542.85	Tx : 894018 Rx : 894018 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 3	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	77.50	77.50	62987.6	764.92	Tx : 1259753 Rx : 1259753 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 4	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	88.75	88.75	72131.0	875.96	Tx : 1442620 Rx : 1442620 Loss : 0 Loss% : 0.000

Trial: 1 / FS: 1518 / Iter: 5	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	94.38	94.38	76702.7	931.48	Tx : 1534054
								Rx : 1534054
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 6	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	97.19	97.19	78988.5	959.24	Tx : 1579771
								Rx : 1579771
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 7	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	98.59	98.59	80131.5	973.12	Tx : 1602629
								Rx : 1602629
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 8	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	99.30	99.30	80702.9	980.06	Tx : 1614058
								Rx : 1614058
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 9	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	100.00	100.00	81274.4	987.00	Tx : 1625488
								Rx : 1625488
								Loss : 0
								Loss% : 0.000

RFC2544 - Throughput/Latency - Iteration Statistics - Part 2 of 2

Trial / Framesize / Iteration	Tx Port	Rx Port	Flow Group	Min Latency (ns)	Max Latency (ns)	Avg Latency (ns)
Trial: 1 / FS: 64 / Iter: 1	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	870	892	880.00
Trial: 1 / FS: 64 / Iter: 2	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	862	895	879.00
Trial: 1 / FS: 64 / Iter: 3	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	860	895	879.00
Trial: 1 / FS: 64 / Iter: 4	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	860	895	879.00
Trial: 1 / FS: 64 / Iter: 5	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	867	895	879.00
Trial: 1 / FS: 64 / Iter: 6	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	867	895	879.00
Trial: 1 / FS: 64 / Iter: 7	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	867	895	880.00
Trial: 1 / FS: 64 / Iter: 8	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	867	895	881.00
Trial: 1 / FS: 64 / Iter: 9	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	875	895	883.00
Trial: 1 / FS: 128 / Iter: 1	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	867	892	879.00
Trial: 1 / FS: 128 / Iter: 2	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	867	895	878.00
Trial: 1 / FS: 128 / Iter: 3	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	867	895	878.00
Trial: 1 / FS: 128 / Iter: 4	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	867	895	878.00
Trial: 1 / FS: 128 / Iter: 5	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	867	895	879.00
Trial: 1 / FS: 128 / Iter: 6	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	867	895	878.00
Trial: 1 / FS: 128 / Iter: 7	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	867	895	879.00
Trial: 1 / FS: 128 / Iter: 8	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	907	935	918.00
Trial: 1 / FS: 128 / Iter: 9	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	907	935	921.00
Trial: 1 / FS: 256 / Iter: 1	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	725	757	739.00

Trial: 1 / FS: 256 / Iter: 2	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	725	760	740.00
Trial: 1 / FS: 256 / Iter: 3	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	725	760	740.00
Trial: 1 / FS: 256 / Iter: 4	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	725	760	740.00
Trial: 1 / FS: 256 / Iter: 5	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	725	760	740.00
Trial: 1 / FS: 256 / Iter: 6	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	725	760	740.00
Trial: 1 / FS: 256 / Iter: 7	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	725	760	740.00
Trial: 1 / FS: 256 / Iter: 8	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	725	760	740.00
Trial: 1 / FS: 256 / Iter: 9	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	732	760	743.00
Trial: 1 / FS: 512 / Iter: 1	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	730	755	742.00
Trial: 1 / FS: 512 / Iter: 2	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	730	757	743.00
Trial: 1 / FS: 512 / Iter: 3	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	730	757	743.00
Trial: 1 / FS: 512 / Iter: 4	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	730	757	743.00
Trial: 1 / FS: 512 / Iter: 5	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	730	757	743.00
Trial: 1 / FS: 512 / Iter: 6	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	730	757	743.00
Trial: 1 / FS: 512 / Iter: 7	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	730	757	743.00
Trial: 1 / FS: 512 / Iter: 8	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	730	757	743.00
Trial: 1 / FS: 512 / Iter: 9	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	740	757	746.00
Trial: 1 / FS: 1024 / Iter: 1	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	732	755	744.00
Trial: 1 / FS: 1024 / Iter: 2	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	732	757	744.00
Trial: 1 / FS: 1024 / Iter: 3	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	732	757	744.00
Trial: 1 / FS: 1024 / Iter: 4	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	732	757	744.00

Trial: 1 / FS: 1024 / Iter: 5	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	732	757	744.00
Trial: 1 / FS: 1024 / Iter: 6	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	732	757	744.00
Trial: 1 / FS: 1024 / Iter: 7	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	732	757	744.00
Trial: 1 / FS: 1024 / Iter: 8	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	732	757	743.00
Trial: 1 / FS: 1024 / Iter: 9	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	740	757	746.00
Trial: 1 / FS: 1280 / Iter: 1	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	732	757	743.00
Trial: 1 / FS: 1280 / Iter: 2	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	732	760	744.00
Trial: 1 / FS: 1280 / Iter: 3	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	732	760	744.00
Trial: 1 / FS: 1280 / Iter: 4	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	732	760	744.00
Trial: 1 / FS: 1280 / Iter: 5	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	732	760	744.00
Trial: 1 / FS: 1280 / Iter: 6	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	732	760	744.00
Trial: 1 / FS: 1280 / Iter: 7	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	732	760	743.00
Trial: 1 / FS: 1280 / Iter: 8	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	732	760	743.00
Trial: 1 / FS: 1280 / Iter: 9	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	732	757	743.00
Trial: 1 / FS: 1518 / Iter: 1	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	732	757	742.00
Trial: 1 / FS: 1518 / Iter: 2	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	730	760	743.00
Trial: 1 / FS: 1518 / Iter: 3	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	730	760	743.00
Trial: 1 / FS: 1518 / Iter: 4	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	730	760	743.00
Trial: 1 / FS: 1518 / Iter: 5	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	730	760	743.00
Trial: 1 / FS: 1518 / Iter: 6	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	730	760	743.00
Trial: 1 / FS: 1518 / Iter: 7	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	730	760	743.00



Trial: 1 / FS: 1518 / Iter: 8	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	730	760	743.00
Trial: 1 / FS: 1518 / Iter: 9	Ethernet - 001	Ethernet - 002	S5800-48F4SR-Endpoint Set-1 - Flow Group 0001	730	760	745.00

Theoretical maximum Frame Rates (frames/second) for different frame sizes (bytes)

Speed	64	128	256	512	1024	1280	1518
10 Mbps	14881	8446	4529	2350	1198	962	813
100 Mbps	148810	84460	45290	23497	11973	9616	8128
1000 Mbps	1488096	844595	452899	234963	119732	96154	81275
10 Gbps	14880952	8445946	4528986	2349625	1197318	961539	812744
25 Gbps	37202380	21114864	11322463	5874060	2993295	2403846	2031859
40 Gbps	59523809	33783783	18115942	9398496	4789272	3846153	3250975
100 Gbps	148809523	84459459	45289855	23496240	11973180	9615384	8127438
155 Mbps (Oc - 3)	288000	145116	72840	36491	18263	14614	12324
622 Mbps (Oc - 12)	1152000	580465	291362	145965	73054	58454	49296
2488 Mbps (Oc - 48)	4608000	2321860	1165447	583860	292215	233817	197182
9952 Mbps (Oc - 192)	18432000	9287442	4661790	2335439	1168859	935270	788730