



IxNetwork Report

Test: RFC2544 - Throughput/Latency

Test Date: 09/02/2020 16:02:03

www.ixiacom.com
www.ixiacom.com/support

Table of Contents

1.	Cover	1
2.	Info	3
3.	Port Map	4
4.	Aggregate Graphs	5
5.	IterationCharts	13
6.	Aggregated Results	19
7.	Aggregated Results Per Iteration	20
8.	Per Flow Results	25
9.	Iteration Data	27
10.	Theoretical Max Rates	43

RFC2544 - Throughput/Latency - Info**Test Information****Product Information**

Product Label :	N8550-32C
Product Version :	Jul 26 2020
Serial Number :	772632X2011049
Comments :	

Test Settings

Date Executed :	09/02/2020
Time Executed :	16:02:03
User Name :	
Number of Trials Executed :	1
Stream Duration (sec) :	20

Output Parameters


Number of Trials Passed :	N/A
Test Duration :	00:35:39

RFC2544 - Throughput/Latency - Port Map Information

Port Map :	Tx Port	Tx Speed (Mbps)	Rx Port	Rx Speed (Mbps)
	10.32.133.101:6:1	100000	10.32.133.101:6:4	100000
	10.32.133.101:6:4	100000	10.32.133.101:6:1	100000

RFC2544 - Throughput/Latency - Aggregated Graph



Total Frames Transmitted and Received




Trial - Framesize - Iteration

RFC2544 - Throughput/Latency - Aggregated Graph

Tx / Rx Frames per Frame Size




RFC2544 - Throughput/Latency - Aggregated Graph**Aggregated Frame Loss**

Trial - Framesize - Iteration


RFC2544 - Throughput/Latency - Aggregated Graph

Aggregated Frame Loss per Frame Size




RFC2544 - Throughput/Latency - Aggregated Graph

Aggregated Frame Loss per Line Rate




RFC2544 - Throughput/Latency - Per Flow Graph





RFC2544 - Throughput/Latency - Aggregated Graph

Aggregated Latency



RFC2544 - Throughput/Latency - Per Flow Graph


Tx / Rx Frame Count




Trial

RFC2544 - Throughput/Latency - Iteration Graph


Aggregated Frame Loss for Trial 1 and Framesize 64




Aggregated Frame Loss for Trial 1 and Framesize 128




Aggregated Frame Loss for Trial 1 and Framesize 256




Aggregated Frame Loss for Trial 1 and Framesize 512




Aggregated Frame Loss for Trial 1 and Framesize 1024




Aggregated Frame Loss for Trial 1 and Framesize 1280




Aggregated Frame Loss for Trial 1 and Framesize 1518

RFC2544 - Throughput/Latency - Iteration Graph

Tx / Rx Frames per Frame Size



RFC2544 - Throughput/Latency - Iteration Graph



RFC2544 - Throughput/Latency - Aggregated Results

Trial / Framesize / Iteration	Agg L2 Throughput				Agg L1 Throughput		Throughput (frames)	Agg Latency			
	AggTx Rate %	%	FPS	Mbps	Tx Rate Mbps	Rx Rate Mbps		Min (ns)	Max (ns)	Average (ns)	
Trial: 1 / FS: 64 / Iter: 9	100.00	100	297619047.4	152380.952			Tx : 5952380952.000 Rx : 5952380952.000 Loss : 0 Loss% : .00	802	862	826.000	
Trial: 1 / FS: 128 / Iter: 9	100.00	100	168918918.8	172972.973			Tx : 3378378378.000 Rx : 3378378378.000 Loss : 0 Loss% : .00	805	860	826.000	
Trial: 1 / FS: 256 / Iter: 9	100.00	100	90579710.1	185507.246			Tx : 1811594202.000 Rx : 1811594202.000 Loss : 0 Loss% : .00	815	870	836.000	
Trial: 1 / FS: 512 / Iter: 9	100.00	100	46992481.2	192481.203			Tx : 939849624.000 Rx : 939849624.000 Loss : 0 Loss% : .00	802	855	822.000	
Trial: 1 / FS: 1024 / Iter: 9	100.00	100	23946360.1	196168.582			Tx : 478927204.000 Rx : 478927204.000 Loss : 0 Loss% : .00	765	810	787.500	
Trial: 1 / FS: 1280 / Iter: 9	100.00	100	19230769.2	196923.077			Tx : 384615384.000 Rx : 384615384.000 Loss : 0 Loss% : .00	750	795	772.500	
Trial: 1 / FS: 1518 / Iter: 9	100.00	100	16254876.4	197399.220			Tx : 325097530.000 Rx : 325097530.000 Loss : 0 Loss% : .00	737	792	758.000	

RFC2544 - Throughput/Latency - Aggregated Results

Trial / Framesize / Iteration	Agg L2 Throughput				Agg L1 Throughput		Throughput (frames)	Agg Latency			
	AggTx Rate %	%	FPS	Mbps	Tx Rate Mbps	Rx Rate Mbps		Min (ns)	Max (ns)	Average (ns)	
Trial: 1 / FS: 64 / Iter: 1	10	10	29761904.8	15238.095			Tx : 595238096.000 Rx : 595238096.000 Loss : 0 Loss% : .00	797	835	810.000	
Trial: 1 / FS: 64 / Iter: 2	55	55	163690714.1	83809.646			Tx : 3273809524.000 Rx : 3273809524.000 Loss : 0 Loss% : .00	790	835	806.500	
Trial: 1 / FS: 64 / Iter: 3	78	78	230654527.3	118095.118			Tx : 4613095238.000 Rx : 4613095238.000 Loss : 0 Loss% : .00	790	835	807.500	
Trial: 1 / FS: 64 / Iter: 4	89	89	264136732.0	135238.007			Tx : 5282738096.000 Rx : 5282738096.000 Loss : 0 Loss% : .00	792	837	808.500	
Trial: 1 / FS: 64 / Iter: 5	94	94	280877302.7	143809.179			Tx : 5617559524.000 Rx : 5617559524.000 Loss : 0 Loss% : .00	792	835	809.500	
Trial: 1 / FS: 64 / Iter: 6	97	97	289249195.0	148095.588			Tx : 5784970238.000 Rx : 5784970238.000 Loss : 0 Loss% : .00	792	835	810.500	
Trial: 1 / FS: 64 / Iter: 7	99	99	293433284.0	150237.841			Tx : 5868675596.000 Rx : 5868675596.000 Loss : 0 Loss% : .00	792	835	810.500	
Trial: 1 / FS: 64 / Iter: 8	99	99	295526695.5	151309.668			Tx : 5910528274.000 Rx : 5910528274.000 Loss : 0 Loss% : .00	792	837	811.500	
Trial: 1 / FS: 64 / Iter: 9	100	100	297619047.4	152380.952			Tx : 5952380952.000 Rx : 5952380952.000 Loss : 0 Loss% : .00	802	862	826.000	
Trial: 1 / FS: 128 / Iter: 1	10	10	16891891.9	17297.297			Tx : 337837838.000 Rx : 337837838.000 Loss : 0 Loss% : .00	797	835	810.000	
Trial: 1 / FS: 128 / Iter: 2	55	55	92905436.0	95135.167			Tx : 1858108108.000 Rx : 1858108108.000 Loss : 0 Loss% : .00	795	835	810.000	
Trial: 1 / FS: 128 / Iter: 3	78	78	130912140.6	134054.032			Tx : 2618243244.000 Rx : 2618243244.000 Loss : 0 Loss% : .00	795	835	808.500	
Trial: 1 / FS: 128 / Iter: 4	89	89	149915379.8	153513.349			Tx : 2998310810.000 Rx : 2998310810.000 Loss : 0 Loss% : .00	795	835	809.500	

Trial: 1 / FS: 128 / Iter: 5	94	94	159417131.1	163243.142	Tx : Rx : Loss : Loss% :	3188344594.000 3188344594.000 0 .00	797	835	810.000
Trial: 1 / FS: 128 / Iter: 6	97	97	164168336.7	168108.377	Tx : Rx : Loss : Loss% :	3283361486.000 3283361486.000 0 .00	797	835	810.500
Trial: 1 / FS: 128 / Iter: 7	99	99	166543602.2	170540.649	Tx : Rx : Loss : Loss% :	3330869932.000 3330869932.000 0 .00	797	845	811.500
Trial: 1 / FS: 128 / Iter: 8	99	99	167731367.7	171756.921	Tx : Rx : Loss : Loss% :	3354624156.000 3354624156.000 0 .00	797	835	811.500
Trial: 1 / FS: 128 / Iter: 9	100	100	168918918.8	172972.973	Tx : Rx : Loss : Loss% :	3378378378.000 3378378378.000 0 .00	805	860	826.000
Trial: 1 / FS: 256 / Iter: 1	10	10	9057971.0	18550.725	Tx : Rx : Loss : Loss% :	181159420.000 181159420.000 0 .00	802	837	814.500
Trial: 1 / FS: 256 / Iter: 2	55	55	49818822.9	102028.949	Tx : Rx : Loss : Loss% :	996376812.000 996376812.000 0 .00	802	840	814.500
Trial: 1 / FS: 256 / Iter: 3	78	78	70199300.2	143768.167	Tx : Rx : Loss : Loss% :	1403985508.000 1403985508.000 0 .00	802	840	814.500
Trial: 1 / FS: 256 / Iter: 4	89	89	80389512.3	164637.721	Tx : Rx : Loss : Loss% :	1607789856.000 1607789856.000 0 .00	802	840	814.500
Trial: 1 / FS: 256 / Iter: 5	94	94	85484641.1	175072.545	Tx : Rx : Loss : Loss% :	1709692028.000 1709692028.000 0 .00	802	840	815.000
Trial: 1 / FS: 256 / Iter: 6	97	97	88032104.2	180289.749	Tx : Rx : Loss : Loss% :	1760643116.000 1760643116.000 0 .00	805	840	815.500
Trial: 1 / FS: 256 / Iter: 7	99	99	89305960.1	182898.606	Tx : Rx : Loss : Loss% :	1786118660.000 1786118660.000 0 .00	805	842	816.000
Trial: 1 / FS: 256 / Iter: 8	99	99	89942749.4	184202.751	Tx : Rx : Loss : Loss% :	1798856432.000 1798856432.000 0 .00	810	875	822.000
Trial: 1 / FS: 256 / Iter: 9	100	100	90579710.1	185507.246	Tx : Rx : Loss : Loss% :	1811594202.000 1811594202.000 0 .00	815	870	836.000
Trial: 1 / FS: 512 / Iter: 1	10	10	4699248.1	19248.120	Tx : Rx : Loss : Loss% :	93984962.000 93984962.000 0 .00	795	827	805.000

Trial: 1 / FS: 512 / Iter: 2	55	55	25845858.7	105864.637	Tx : Rx : Loss : Loss% :	516917294.000 516917294.000 0 .00	795	827	805.000
Trial: 1 / FS: 512 / Iter: 3	78	78	36419170.4	149172.922	Tx : Rx : Loss : Loss% :	728383458.000 728383458.000 0 .00	795	827	805.000
Trial: 1 / FS: 512 / Iter: 4	89	89	41705833.8	170827.095	Tx : Rx : Loss : Loss% :	834116542.000 834116542.000 0 .00	795	827	805.500
Trial: 1 / FS: 512 / Iter: 5	94	94	44349163.0	181654.172	Tx : Rx : Loss : Loss% :	886983082.000 886983082.000 0 .00	795	830	805.500
Trial: 1 / FS: 512 / Iter: 6	97	97	45670816.9	187067.666	Tx : Rx : Loss : Loss% :	913416354.000 913416354.000 0 .00	795	830	805.500
Trial: 1 / FS: 512 / Iter: 7	99	99	46331655.0	189774.459	Tx : Rx : Loss : Loss% :	926632988.000 926632988.000 0 .00	795	832	806.500
Trial: 1 / FS: 512 / Iter: 8	99	99	46662067.3	191127.828	Tx : Rx : Loss : Loss% :	933241306.000 933241306.000 0 .00	795	835	806.500
Trial: 1 / FS: 512 / Iter: 9	100	100	46992481.2	192481.203	Tx : Rx : Loss : Loss% :	939849624.000 939849624.000 0 .00	802	855	822.000
Trial: 1 / FS: 1024 / Iter: 1	10	10	2394636.0	19616.858	Tx : Rx : Loss : Loss% :	47892720.000 47892720.000 0 .00	765	795	775.500
Trial: 1 / FS: 1024 / Iter: 2	55	55	13170499.3	107892.730	Tx : Rx : Loss : Loss% :	263409962.000 263409962.000 0 .00	765	797	775.500
Trial: 1 / FS: 1024 / Iter: 3	78	78	18558430.4	152030.662	Tx : Rx : Loss : Loss% :	371168582.000 371168582.000 0 .00	767	797	775.500
Trial: 1 / FS: 1024 / Iter: 4	89	89	21252397.1	174099.637	Tx : Rx : Loss : Loss% :	425047892.000 425047892.000 0 .00	767	797	775.500
Trial: 1 / FS: 1024 / Iter: 5	94	47	11299689.4	92567.056	Tx : Rx : Loss : Loss% :	225993774.000 225993774.000 0 .00	787	815	795.000
Trial: 1 / FS: 1024 / Iter: 6	97	97	23272864.8	190651.308	Tx : Rx : Loss : Loss% :	465457376.000 465457376.000 0 .00	757	815	771.500
Trial: 1 / FS: 1024 / Iter: 7	99	99	23609615.0	193409.966	Tx : Rx : Loss : Loss% :	472192290.000 472192290.000 0 .00	757	795	771.500

Trial: 1 / FS: 1024 / Iter: 8	99	99	23777987.9	194789.277	Tx : Rx : Loss : Loss% :	475559746.000 475559746.000 0 .00	757	797	772.000
Trial: 1 / FS: 1024 / Iter: 9	100	100	23946360.1	196168.582	Tx : Rx : Loss : Loss% :	478927204.000 478927204.000 0 .00	765	810	787.500
Trial: 1 / FS: 1280 / Iter: 1	10	10	1923076.9	19692.308	Tx : Rx : Loss : Loss% :	38461538.000 38461538.000 0 .00	742	780	756.000
Trial: 1 / FS: 1280 / Iter: 2	55	55	10576923.7	108307.698	Tx : Rx : Loss : Loss% :	211538462.000 211538462.000 0 .00	745	780	755.500
Trial: 1 / FS: 1280 / Iter: 3	78	78	14903845.5	152615.377	Tx : Rx : Loss : Loss% :	298076924.000 298076924.000 0 .00	742	780	756.000
Trial: 1 / FS: 1280 / Iter: 4	89	89	17067309.5	174769.250	Tx : Rx : Loss : Loss% :	341346154.000 341346154.000 0 .00	745	790	755.500
Trial: 1 / FS: 1280 / Iter: 5	94	94	18149039.1	185846.160	Tx : Rx : Loss : Loss% :	362980770.000 362980770.000 0 .00	742	782	755.500
Trial: 1 / FS: 1280 / Iter: 6	97	97	18689903.5	191384.612	Tx : Rx : Loss : Loss% :	373798076.000 373798076.000 0 .00	742	780	756.000
Trial: 1 / FS: 1280 / Iter: 7	99	99	18960336.6	194153.847	Tx : Rx : Loss : Loss% :	379206730.000 379206730.000 0 .00	742	782	756.500
Trial: 1 / FS: 1280 / Iter: 8	99	99	19095549.7	195538.429	Tx : Rx : Loss : Loss% :	381911058.000 381911058.000 0 .00	742	782	757.000
Trial: 1 / FS: 1280 / Iter: 9	100	100	19230769.2	196923.077	Tx : Rx : Loss : Loss% :	384615384.000 384615384.000 0 .00	750	795	772.500
Trial: 1 / FS: 1518 / Iter: 1	10	10	1625487.6	19739.922	Tx : Rx : Loss : Loss% :	32509752.000 32509752.000 0 .00	727	765	741.000
Trial: 1 / FS: 1518 / Iter: 2	55	55	8940181.6	108569.566	Tx : Rx : Loss : Loss% :	178803642.000 178803642.000 0 .00	730	765	741.500
Trial: 1 / FS: 1518 / Iter: 3	78	78	12597529.4	152984.397	Tx : Rx : Loss : Loss% :	251950586.000 251950586.000 0 .00	727	765	741.000
Trial: 1 / FS: 1518 / Iter: 4	89	89	14426204.8	175191.831	Tx : Rx : Loss : Loss% :	288524058.000 288524058.000 0 .00	727	765	741.000

Trial: 1 / FS: 1518 / Iter: 5	94	94	15340539.0	186295.506	Tx :	306810794.000	730	765	741.500
					Rx :	306810794.000			
					Loss :	0			
					Loss% :	.00			
Trial: 1 / FS: 1518 / Iter: 6	97	97	15797710.3	191847.394	Tx :	315954162.000	727	765	741.500
					Rx :	315954162.000			
					Loss :	0			
					Loss% :	.00			
Trial: 1 / FS: 1518 / Iter: 7	99	99	16026293.1	194623.304	Tx :	320525846.000	727	765	742.000
					Rx :	320525846.000			
					Loss :	0			
					Loss% :	.00			
Trial: 1 / FS: 1518 / Iter: 8	99	99	16140584.5	196011.258	Tx :	322811688.000	730	765	742.500
					Rx :	322811688.000			
					Loss :	0			
					Loss% :	.00			
Trial: 1 / FS: 1518 / Iter: 9	100	100	16254876.4	197399.220	Tx :	325097530.000	737	792	758.000
					Rx :	325097530.000			
					Loss :	0			
					Loss% :	.00			

RFC2544 - Throughput/Latency - Per Flow Statistics - Part 1 of 2

Trial / Framesize / Iteration	Tx Port	Rx Port	Flow Group	L2 Throughput				L1 Throughput		Throughput (frames)
				Tx Rate %	Rx Rate			Tx Rate Mbps	Rx Rate Mbps	
					%	FPS	Mbps			
Trial: 1 / FS: 64 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	100.00	100	148809523.6	76190.48			Tx : 2976190476 Rx : 2976190476 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 64 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	100.00	100	148809523.7	76190.48			Tx : 2976190476 Rx : 2976190476 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	100.00	100	84459459.4	86486.49			Tx : 1689189189 Rx : 1689189189 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	100.00	100	84459459.4	86486.49			Tx : 1689189189 Rx : 1689189189 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	100.00	100	45289855.0	92753.62			Tx : 905797101 Rx : 905797101 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	100.00	100	45289855.0	92753.62			Tx : 905797101 Rx : 905797101 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	100.00	100	23496240.6	96240.60			Tx : 469924812 Rx : 469924812 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	100.00	100	23496240.6	96240.60			Tx : 469924812 Rx : 469924812 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	100.00	100	11973180.1	98084.29			Tx : 239463602 Rx : 239463602 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	100.00	100	11973180.1	98084.29			Tx : 239463602 Rx : 239463602 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	100.00	100	9615384.6	98461.54			Tx : 192307692 Rx : 192307692 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	100.00	100	9615384.6	98461.54			Tx : 192307692 Rx : 192307692 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	100.00	100	8127438.2	98699.61			Tx : 162548765 Rx : 162548765 Loss : 0 Loss% : 0.000

Trial: 1 / FS: 1518 / Iter: 9	Ethernet - 002 Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	100.00	100	8127438.2 98699.61	Tx : 162548765
						Rx : 162548765
						Loss : 0
						Loss% : 0.000

RFC2544 - Throughput/Latency - Per Flow Statistics - Part 2 of 2

Trial / Framesize / Iteration	Tx Port	Rx Port	Flow Group	Min Latency (ns)	Max Latency (ns)	Avg Latency (ns)
Trial: 1 / FS: 64 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	810	862	830
Trial: 1 / FS: 64 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	802	855	822
Trial: 1 / FS: 128 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	812	860	829
Trial: 1 / FS: 128 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	805	857	823
Trial: 1 / FS: 256 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	815	867	834
Trial: 1 / FS: 256 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	820	870	838
Trial: 1 / FS: 512 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	802	852	820
Trial: 1 / FS: 512 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	805	855	824
Trial: 1 / FS: 1024 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	772	810	791
Trial: 1 / FS: 1024 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	765	802	784
Trial: 1 / FS: 1280 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	757	795	776
Trial: 1 / FS: 1280 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	750	787	769
Trial: 1 / FS: 1518 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	745	792	761
Trial: 1 / FS: 1518 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	737	785	755

RFC2544 - Throughput/Latency - Iteration Statistics - Part 1 of 2

Trial / Framesize / Iteration	Tx Port	Rx Port	Flow Group	L2 Throughput				L1 Throughput		Throughput (frames)	
				Tx Rate %	%	FPS	Mbps	Tx Rate Mbps	Rx Rate Mbps		
Trial: 1 / FS: 64 / Iter: 1	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	10.00	10.00	14880952.4	7619.05			Tx : 297619048 Rx : 297619048 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 1	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	10.00	10.00	14880952.4	7619.05			Tx : 297619048 Rx : 297619048 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 2	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	55.00	55.00	81845357.1	41904.82			Tx : 1636904762 Rx : 1636904762 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 2	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	55.00	55.00	81845357.0	41904.82			Tx : 1636904762 Rx : 1636904762 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 3	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	77.50	77.50	115327263.7	59047.56			Tx : 2306547619 Rx : 2306547619 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 3	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	77.50	77.50	115327263.6	59047.56			Tx : 2306547619 Rx : 2306547619 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 4	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	88.75	88.75	132068366.0	67619.00			Tx : 2641369048 Rx : 2641369048 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 4	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	88.75	88.75	132068366.0	67619.00			Tx : 2641369048 Rx : 2641369048 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 5	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	94.38	94.38	140438651.4	71904.59			Tx : 2808779762 Rx : 2808779762 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 5	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	94.38	94.38	140438651.3	71904.59			Tx : 2808779762 Rx : 2808779762 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 6	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	97.19	97.19	144624597.5	74047.79			Tx : 2892485119 Rx : 2892485119 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 6	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	97.19	97.19	144624597.5	74047.79			Tx : 2892485119 Rx : 2892485119 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 7	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	98.59	98.59	146716642.0	75118.92			Tx : 2934337798 Rx : 2934337798 Loss : 0 Loss% : 0.000	

Trial: 1 / FS: 64 / Iter: 7	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	98.59	98.59	146716642.0	75118.92	Tx : 2934337798
								Rx : 2934337798
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 64 / Iter: 8	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	99.30	99.30	147763347.8	75654.83	Tx : 2955264137
								Rx : 2955264137
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 64 / Iter: 8	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	99.30	99.30	147763347.7	75654.83	Tx : 2955264137
								Rx : 2955264137
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 64 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	100.00	100.00	148809523.6	76190.48	Tx : 2976190476
								Rx : 2976190476
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 64 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	100.00	100.00	148809523.7	76190.48	Tx : 2976190476
								Rx : 2976190476
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 1	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	10.00	10.00	8445945.9	8648.65	Tx : 168918919
								Rx : 168918919
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 1	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	10.00	10.00	8445945.9	8648.65	Tx : 168918919
								Rx : 168918919
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 2	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	55.00	55.00	46452718.0	47567.58	Tx : 929054054
								Rx : 929054054
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 2	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	55.00	55.00	46452718.0	47567.58	Tx : 929054054
								Rx : 929054054
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 3	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	77.50	77.50	65456070.3	67027.02	Tx : 1309121622
								Rx : 1309121622
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 3	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	77.50	77.50	65456070.3	67027.02	Tx : 1309121622
								Rx : 1309121622
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 4	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	88.75	88.75	74957689.9	76756.67	Tx : 1499155405
								Rx : 1499155405
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 4	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	88.75	88.75	74957689.9	76756.67	Tx : 1499155405
								Rx : 1499155405
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 5	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	94.38	94.38	79708565.6	81621.57	Tx : 1594172297
								Rx : 1594172297
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 5	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	94.38	94.38	79708565.5	81621.57	Tx : 1594172297
								Rx : 1594172297
								Loss : 0
								Loss% : 0.000

Trial: 1 / FS: 128 / Iter: 6	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	97.19	97.19	82084168.3	84054.19	Tx : 1641680743 Rx : 1641680743 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 6	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	97.19	97.19	82084168.3	84054.19	Tx : 1641680743 Rx : 1641680743 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 7	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	98.59	98.59	83271801.1	85270.32	Tx : 1665434966 Rx : 1665434966 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 7	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	98.59	98.59	83271801.1	85270.32	Tx : 1665434966 Rx : 1665434966 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 8	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	99.30	99.30	83865683.8	85878.46	Tx : 1677312078 Rx : 1677312078 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 8	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	99.30	99.30	83865683.9	85878.46	Tx : 1677312078 Rx : 1677312078 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	100.00	100.00	84459459.4	86486.49	Tx : 1689189189 Rx : 1689189189 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	100.00	100.00	84459459.4	86486.49	Tx : 1689189189 Rx : 1689189189 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 1	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	10.00	10.00	4528985.5	9275.36	Tx : 90579710 Rx : 90579710 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 1	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	10.00	10.00	4528985.5	9275.36	Tx : 90579710 Rx : 90579710 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 2	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	55.00	55.00	24909411.5	51014.48	Tx : 498188406 Rx : 498188406 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 2	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	55.00	55.00	24909411.5	51014.48	Tx : 498188406 Rx : 498188406 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 3	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	77.50	77.50	35099650.1	71884.08	Tx : 701992754 Rx : 701992754 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 3	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	77.50	77.50	35099650.1	71884.08	Tx : 701992754 Rx : 701992754 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 4	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	88.75	88.75	40194756.2	82318.86	Tx : 803894928 Rx : 803894928 Loss : 0 Loss% : 0.000

Trial: 1 / FS: 256 / Iter: 4	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	88.75	88.75	40194756.2	82318.86	Tx : 803894928 Rx : 803894928 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 5	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	94.38	94.38	42742320.6	87536.27	Tx : 854846014 Rx : 854846014 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 5	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	94.38	94.38	42742320.6	87536.27	Tx : 854846014 Rx : 854846014 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 6	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	97.19	97.19	44016052.1	90144.88	Tx : 880321558 Rx : 880321558 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 6	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	97.19	97.19	44016052.1	90144.88	Tx : 880321558 Rx : 880321558 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 7	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	98.59	98.59	44652980.1	91449.30	Tx : 893059330 Rx : 893059330 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 7	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	98.59	98.59	44652980.1	91449.30	Tx : 893059330 Rx : 893059330 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 8	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	99.30	99.30	44971374.7	92101.38	Tx : 899428216 Rx : 899428216 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 8	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	99.30	99.30	44971374.7	92101.38	Tx : 899428216 Rx : 899428216 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	100.00	100.00	45289855.0	92753.62	Tx : 905797101 Rx : 905797101 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	100.00	100.00	45289855.0	92753.62	Tx : 905797101 Rx : 905797101 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 1	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	10.00	10.00	2349624.1	9624.06	Tx : 46992481 Rx : 46992481 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 1	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	10.00	10.00	2349624.1	9624.06	Tx : 46992481 Rx : 46992481 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 2	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	55.00	55.00	12922929.4	52932.32	Tx : 258458647 Rx : 258458647 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 2	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	55.00	55.00	12922929.4	52932.32	Tx : 258458647 Rx : 258458647 Loss : 0 Loss% : 0.000

Trial: 1 / FS: 512 / Iter: 3	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	77.50	77.50	18209585.2	74586.46	Tx : 364191729
								Rx : 364191729
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 3	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	77.50	77.50	18209585.2	74586.46	Tx : 364191729
								Rx : 364191729
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 4	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	88.75	88.75	20852916.9	85413.55	Tx : 417058271
								Rx : 417058271
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 4	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	88.75	88.75	20852916.9	85413.55	Tx : 417058271
								Rx : 417058271
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 5	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	94.38	94.38	22174581.5	90827.09	Tx : 443491541
								Rx : 443491541
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 5	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	94.38	94.38	22174581.5	90827.09	Tx : 443491541
								Rx : 443491541
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 6	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	97.19	97.19	22835408.4	93533.83	Tx : 456708177
								Rx : 456708177
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 6	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	97.19	97.19	22835408.4	93533.83	Tx : 456708177
								Rx : 456708177
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 7	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	98.59	98.59	23165827.5	94887.23	Tx : 463316494
								Rx : 463316494
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 7	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	98.59	98.59	23165827.5	94887.23	Tx : 463316494
								Rx : 463316494
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 8	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	99.30	99.30	23331033.6	95563.91	Tx : 466620653
								Rx : 466620653
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 8	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	99.30	99.30	23331033.6	95563.91	Tx : 466620653
								Rx : 466620653
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	100.00	100.00	23496240.6	96240.60	Tx : 469924812
								Rx : 469924812
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	100.00	100.00	23496240.6	96240.60	Tx : 469924812
								Rx : 469924812
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 1	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	10.00	10.00	1197318.0	9808.43	Tx : 23946360
								Rx : 23946360
								Loss : 0
								Loss% : 0.000

Trial: 1 / FS: 1024 / Iter: 1	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	10.00	10.00	1197318.0	9808.43	Tx : 23946360
								Rx : 23946360
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 2	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	55.00	55.00	6585249.7	53946.37	Tx : 131704981
								Rx : 131704981
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 2	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	55.00	55.00	6585249.7	53946.37	Tx : 131704981
								Rx : 131704981
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 3	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	77.50	77.50	9279215.2	76015.33	Tx : 185584291
								Rx : 185584291
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 3	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	77.50	77.50	9279215.2	76015.33	Tx : 185584291
								Rx : 185584291
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 4	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	88.75	88.75	10626198.6	87049.82	Tx : 212523946
								Rx : 212523946
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 4	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	88.75	88.75	10626198.6	87049.82	Tx : 212523946
								Rx : 212523946
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 5	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	94.38				Tx : 0
								Rx : 0
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 5	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	94.38	94.38	11299689.4	92567.06	Tx : 225993774
								Rx : 225993774
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 6	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	97.19	97.19	11636432.4	95325.65	Tx : 232728688
								Rx : 232728688
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 6	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	97.19	97.19	11636432.4	95325.65	Tx : 232728688
								Rx : 232728688
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 7	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	98.59	98.59	11804807.5	96704.98	Tx : 236096145
								Rx : 236096145
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 7	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	98.59	98.59	11804807.5	96704.98	Tx : 236096145
								Rx : 236096145
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 8	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	99.30	99.30	11888993.9	97394.64	Tx : 237779873
								Rx : 237779873
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 8	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	99.30	99.30	11888993.9	97394.64	Tx : 237779873
								Rx : 237779873
								Loss : 0
								Loss% : 0.000

Trial: 1 / FS: 1024 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	100.00	100.00	11973180.1	98084.29	Tx : 239463602
								Rx : 239463602
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	100.00	100.00	11973180.1	98084.29	Tx : 239463602
								Rx : 239463602
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 1	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	10.00	10.00	961538.5	9846.15	Tx : 19230769
								Rx : 19230769
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 1	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	10.00	10.00	961538.5	9846.15	Tx : 19230769
								Rx : 19230769
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 2	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	55.00	55.00	5288461.8	54153.85	Tx : 105769231
								Rx : 105769231
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 2	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	55.00	55.00	5288461.8	54153.85	Tx : 105769231
								Rx : 105769231
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 3	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	77.50	77.50	7451922.7	76307.69	Tx : 149038462
								Rx : 149038462
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 3	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	77.50	77.50	7451922.7	76307.69	Tx : 149038462
								Rx : 149038462
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 4	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	88.75	88.75	8533654.8	87384.63	Tx : 170673077
								Rx : 170673077
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 4	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	88.75	88.75	8533654.8	87384.63	Tx : 170673077
								Rx : 170673077
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 5	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	94.38	94.38	9074519.5	92923.08	Tx : 181490385
								Rx : 181490385
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 5	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	94.38	94.38	9074519.5	92923.08	Tx : 181490385
								Rx : 181490385
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 6	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	97.19	97.19	9344951.7	95692.31	Tx : 186899038
								Rx : 186899038
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 6	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	97.19	97.19	9344951.7	95692.31	Tx : 186899038
								Rx : 186899038
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 7	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	98.59	98.59	9480168.3	97076.92	Tx : 189603365
								Rx : 189603365
								Loss : 0
								Loss% : 0.000

Trial: 1 / FS: 1280 / Iter: 7	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	98.59	98.59	9480168.3	97076.92	Tx : 189603365
								Rx : 189603365
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 8	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	99.30	99.30	9547774.9	97769.22	Tx : 190955529
								Rx : 190955529
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 8	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	99.30	99.30	9547774.9	97769.22	Tx : 190955529
								Rx : 190955529
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	100.00	100.00	9615384.6	98461.54	Tx : 192307692
								Rx : 192307692
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	100.00	100.00	9615384.6	98461.54	Tx : 192307692
								Rx : 192307692
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 1	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	10.00	10.00	812743.8	9869.96	Tx : 16254876
								Rx : 16254876
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 1	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	10.00	10.00	812743.8	9869.96	Tx : 16254876
								Rx : 16254876
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 2	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	55.00	55.00	4470090.8	54284.78	Tx : 89401821
								Rx : 89401821
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 2	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	55.00	55.00	4470090.8	54284.78	Tx : 89401821
								Rx : 89401821
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 3	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	77.50	77.50	6298764.7	76492.20	Tx : 125975293
								Rx : 125975293
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 3	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	77.50	77.50	6298764.7	76492.20	Tx : 125975293
								Rx : 125975293
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 4	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	88.75	88.75	7213102.4	87595.92	Tx : 144262029
								Rx : 144262029
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 4	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	88.75	88.75	7213102.4	87595.92	Tx : 144262029
								Rx : 144262029
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 5	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	94.38	94.38	7670269.5	93147.75	Tx : 153405397
								Rx : 153405397
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 5	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	94.38	94.38	7670269.5	93147.75	Tx : 153405397
								Rx : 153405397
								Loss : 0
								Loss% : 0.000

Trial: 1 / FS: 1518 / Iter: 6	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	97.19	97.19	7898855.2	95923.70	Tx : 157977081
								Rx : 157977081
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 6	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	97.19	97.19	7898855.2	95923.70	Tx : 157977081
								Rx : 157977081
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 7	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	98.59	98.59	8013146.6	97311.65	Tx : 160262923
								Rx : 160262923
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 7	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	98.59	98.59	8013146.6	97311.65	Tx : 160262923
								Rx : 160262923
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 8	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	99.30	99.30	8070292.2	98005.63	Tx : 161405844
								Rx : 161405844
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 8	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	99.30	99.30	8070292.2	98005.63	Tx : 161405844
								Rx : 161405844
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	100.00	100.00	8127438.2	98699.61	Tx : 162548765
								Rx : 162548765
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	100.00	100.00	8127438.2	98699.61	Tx : 162548765
								Rx : 162548765
								Loss : 0
								Loss% : 0.000

RFC2544 - Throughput/Latency - Iteration Statistics - Part 2 of 2

Trial / Framesize / Iteration	Tx Port	Rx Port	Flow Group	Min Latency (ns)	Max Latency (ns)	Avg Latency (ns)
Trial: 1 / FS: 64 / Iter: 1	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	805	835	814.00
Trial: 1 / FS: 64 / Iter: 1	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	797	825	806.00
Trial: 1 / FS: 64 / Iter: 2	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	797	835	810.00
Trial: 1 / FS: 64 / Iter: 2	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	790	827	803.00
Trial: 1 / FS: 64 / Iter: 3	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	797	835	811.00
Trial: 1 / FS: 64 / Iter: 3	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	790	827	804.00
Trial: 1 / FS: 64 / Iter: 4	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	800	837	812.00
Trial: 1 / FS: 64 / Iter: 4	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	792	830	805.00
Trial: 1 / FS: 64 / Iter: 5	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	800	835	813.00
Trial: 1 / FS: 64 / Iter: 5	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	792	827	806.00
Trial: 1 / FS: 64 / Iter: 6	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	800	835	814.00
Trial: 1 / FS: 64 / Iter: 6	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	792	827	807.00
Trial: 1 / FS: 64 / Iter: 7	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	800	835	814.00
Trial: 1 / FS: 64 / Iter: 7	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	792	830	807.00
Trial: 1 / FS: 64 / Iter: 8	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	800	837	815.00
Trial: 1 / FS: 64 / Iter: 8	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	792	830	808.00
Trial: 1 / FS: 64 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	810	862	830.00
Trial: 1 / FS: 64 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	802	855	822.00
Trial: 1 / FS: 128 / Iter: 1	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	807	835	814.00

Trial: 1 / FS: 128 / Iter: 1	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	797	825	806.00
Trial: 1 / FS: 128 / Iter: 2	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	800	835	813.00
Trial: 1 / FS: 128 / Iter: 2	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	795	827	807.00
Trial: 1 / FS: 128 / Iter: 3	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	802	835	812.00
Trial: 1 / FS: 128 / Iter: 3	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	795	827	805.00
Trial: 1 / FS: 128 / Iter: 4	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	802	835	813.00
Trial: 1 / FS: 128 / Iter: 4	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	795	830	806.00
Trial: 1 / FS: 128 / Iter: 5	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	805	835	813.00
Trial: 1 / FS: 128 / Iter: 5	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	797	827	807.00
Trial: 1 / FS: 128 / Iter: 6	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	805	835	814.00
Trial: 1 / FS: 128 / Iter: 6	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	797	827	807.00
Trial: 1 / FS: 128 / Iter: 7	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	805	845	815.00
Trial: 1 / FS: 128 / Iter: 7	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	797	830	808.00
Trial: 1 / FS: 128 / Iter: 8	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	805	835	815.00
Trial: 1 / FS: 128 / Iter: 8	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	797	835	808.00
Trial: 1 / FS: 128 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	812	860	829.00
Trial: 1 / FS: 128 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	805	857	823.00
Trial: 1 / FS: 256 / Iter: 1	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	810	837	818.00
Trial: 1 / FS: 256 / Iter: 1	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	802	832	811.00
Trial: 1 / FS: 256 / Iter: 2	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	810	840	818.00
Trial: 1 / FS: 256 / Iter: 2	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	802	832	811.00

Trial: 1 / FS: 256 / Iter: 3	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	810	840	818.00
Trial: 1 / FS: 256 / Iter: 3	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	802	832	811.00
Trial: 1 / FS: 256 / Iter: 4	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	810	840	818.00
Trial: 1 / FS: 256 / Iter: 4	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	802	832	811.00
Trial: 1 / FS: 256 / Iter: 5	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	810	840	818.00
Trial: 1 / FS: 256 / Iter: 5	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	802	832	812.00
Trial: 1 / FS: 256 / Iter: 6	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	810	840	819.00
Trial: 1 / FS: 256 / Iter: 6	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	805	832	812.00
Trial: 1 / FS: 256 / Iter: 7	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	810	842	819.00
Trial: 1 / FS: 256 / Iter: 7	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	805	832	813.00
Trial: 1 / FS: 256 / Iter: 8	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	810	840	820.00
Trial: 1 / FS: 256 / Iter: 8	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	812	875	824.00
Trial: 1 / FS: 256 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	815	867	834.00
Trial: 1 / FS: 256 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	820	870	838.00
Trial: 1 / FS: 512 / Iter: 1	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	795	822	804.00
Trial: 1 / FS: 512 / Iter: 1	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	797	827	806.00
Trial: 1 / FS: 512 / Iter: 2	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	795	825	804.00
Trial: 1 / FS: 512 / Iter: 2	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	797	827	806.00
Trial: 1 / FS: 512 / Iter: 3	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	795	825	804.00
Trial: 1 / FS: 512 / Iter: 3	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	797	827	806.00
Trial: 1 / FS: 512 / Iter: 4	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	795	825	804.00

Trial: 1 / FS: 512 / Iter: 4	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	800	827	807.00
Trial: 1 / FS: 512 / Iter: 5	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	795	825	804.00
Trial: 1 / FS: 512 / Iter: 5	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	797	830	807.00
Trial: 1 / FS: 512 / Iter: 6	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	795	825	804.00
Trial: 1 / FS: 512 / Iter: 6	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	797	830	807.00
Trial: 1 / FS: 512 / Iter: 7	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	795	832	805.00
Trial: 1 / FS: 512 / Iter: 7	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	800	830	808.00
Trial: 1 / FS: 512 / Iter: 8	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	795	827	805.00
Trial: 1 / FS: 512 / Iter: 8	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	797	835	808.00
Trial: 1 / FS: 512 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	802	852	820.00
Trial: 1 / FS: 512 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	805	855	824.00
Trial: 1 / FS: 1024 / Iter: 1	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	765	795	774.00
Trial: 1 / FS: 1024 / Iter: 1	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	770	795	777.00
Trial: 1 / FS: 1024 / Iter: 2	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	765	795	774.00
Trial: 1 / FS: 1024 / Iter: 2	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	770	797	777.00
Trial: 1 / FS: 1024 / Iter: 3	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	767	795	774.00
Trial: 1 / FS: 1024 / Iter: 3	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	767	797	777.00
Trial: 1 / FS: 1024 / Iter: 4	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	767	795	774.00
Trial: 1 / FS: 1024 / Iter: 4	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	767	797	777.00
Trial: 1 / FS: 1024 / Iter: 5	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001			
Trial: 1 / FS: 1024 / Iter: 5	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	787	815	795.00

Trial: 1 / FS: 1024 / Iter: 6	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	765	795	775.00
Trial: 1 / FS: 1024 / Iter: 6	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	757	815	768.00
Trial: 1 / FS: 1024 / Iter: 7	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	765	795	775.00
Trial: 1 / FS: 1024 / Iter: 7	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	757	787	768.00
Trial: 1 / FS: 1024 / Iter: 8	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	765	797	776.00
Trial: 1 / FS: 1024 / Iter: 8	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	757	790	768.00
Trial: 1 / FS: 1024 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	772	810	791.00
Trial: 1 / FS: 1024 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	765	802	784.00
Trial: 1 / FS: 1280 / Iter: 1	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	752	780	760.00
Trial: 1 / FS: 1280 / Iter: 1	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	742	772	752.00
Trial: 1 / FS: 1280 / Iter: 2	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	750	780	759.00
Trial: 1 / FS: 1280 / Iter: 2	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	745	772	752.00
Trial: 1 / FS: 1280 / Iter: 3	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	752	780	760.00
Trial: 1 / FS: 1280 / Iter: 3	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	742	772	752.00
Trial: 1 / FS: 1280 / Iter: 4	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	750	790	759.00
Trial: 1 / FS: 1280 / Iter: 4	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	745	772	752.00
Trial: 1 / FS: 1280 / Iter: 5	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	750	780	759.00
Trial: 1 / FS: 1280 / Iter: 5	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	742	782	752.00
Trial: 1 / FS: 1280 / Iter: 6	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	750	780	760.00
Trial: 1 / FS: 1280 / Iter: 6	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	742	772	752.00
Trial: 1 / FS: 1280 / Iter: 7	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	750	782	760.00

Trial: 1 / FS: 1280 / Iter: 7	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	742	775	753.00
Trial: 1 / FS: 1280 / Iter: 8	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	750	782	761.00
Trial: 1 / FS: 1280 / Iter: 8	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	742	775	753.00
Trial: 1 / FS: 1280 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	757	795	776.00
Trial: 1 / FS: 1280 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	750	787	769.00
Trial: 1 / FS: 1518 / Iter: 1	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	737	765	745.00
Trial: 1 / FS: 1518 / Iter: 1	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	727	757	737.00
Trial: 1 / FS: 1518 / Iter: 2	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	735	765	745.00
Trial: 1 / FS: 1518 / Iter: 2	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	730	757	738.00
Trial: 1 / FS: 1518 / Iter: 3	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	737	765	745.00
Trial: 1 / FS: 1518 / Iter: 3	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	727	757	737.00
Trial: 1 / FS: 1518 / Iter: 4	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	737	765	745.00
Trial: 1 / FS: 1518 / Iter: 4	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	727	757	737.00
Trial: 1 / FS: 1518 / Iter: 5	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	735	765	745.00
Trial: 1 / FS: 1518 / Iter: 5	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	730	760	738.00
Trial: 1 / FS: 1518 / Iter: 6	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	737	765	745.00
Trial: 1 / FS: 1518 / Iter: 6	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	727	757	738.00
Trial: 1 / FS: 1518 / Iter: 7	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	737	765	746.00
Trial: 1 / FS: 1518 / Iter: 7	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	727	760	738.00
Trial: 1 / FS: 1518 / Iter: 8	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	737	765	746.00
Trial: 1 / FS: 1518 / Iter: 8	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	730	760	739.00



Trial: 1 / FS: 1518 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-32C-Endpoint Set-1 - Flow Group 0001	745	792	761.00
Trial: 1 / FS: 1518 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-32C-Endpoint Set-1 - Flow Group 0002	737	785	755.00

Theoretical maximum Frame Rates (frames/second) for different frame sizes (bytes)

Speed	64	128	256	512	1024	1280	1518
10 Mbps	14881	8446	4529	2350	1198	962	813
100 Mbps	148810	84460	45290	23497	11973	9616	8128
1000 Mbps	1488096	844595	452899	234963	119732	96154	81275
10 Gbps	14880952	8445946	4528986	2349625	1197318	961539	812744
25 Gbps	37202380	21114864	11322463	5874060	2993295	2403846	2031859
40 Gbps	59523809	33783783	18115942	9398496	4789272	3846153	3250975
100 Gbps	148809523	84459459	45289855	23496240	11973180	9615384	8127438
155 Mbps (Oc - 3)	288000	145116	72840	36491	18263	14614	12324
622 Mbps (Oc - 12)	1152000	580465	291362	145965	73054	58454	49296
2488 Mbps (Oc - 48)	4608000	2321860	1165447	583860	292215	233817	197182
9952 Mbps (Oc - 192)	18432000	9287442	4661790	2335439	1168859	935270	788730