



IxNetwork Report

Test: RFC2544 - Throughput/Latency

Test Date: 09/21/2008 13:13:45

www.ixiacom.com
www.ixiacom.com/support

Table of Contents

1.	Cover	1
2.	Info	3
3.	Port Map	4
4.	Aggregate Graphs	5
5.	IterationCharts	13
6.	Aggregated Results	19
7.	Aggregated Results Per Iteration	20
8.	Per Flow Results	25
9.	Iteration Data	27
10.	Theoretical Max Rates	43

RFC2544 - Throughput/Latency - Info**Test Information****Product Information**

Product Label :	Your switch/router name here
Product Version :	Your firmware version here
Serial Number :	Your switch/router serial number here
Comments :	

Test Settings

Date Executed :	09/21/2008
Time Executed :	13:13:45
User Name :	
Number of Trials Executed :	1
Stream Duration (sec) :	20

Output Parameters


Number of Trials Passed :	N/A
Test Duration :	00:36:02

RFC2544 - Throughput/Latency - Port Map Information


Port Map :	Tx Port	Tx Speed (Mbps)	Rx Port	Rx Speed (Mbps)
	10.32.133.101:3:10	1000	10.32.133.101:3:11	1000
	10.32.133.101:3:11	1000	10.32.133.101:3:10	1000


RFC2544 - Throughput/Latency - Aggregated Graph

Total Frames Transmitted and Received



RFC2544 - Throughput/Latency - Aggregated Graph




RFC2544 - Throughput/Latency - Aggregated Graph**Aggregated Frame Loss**

Trial - Framesize - Iteration


RFC2544 - Throughput/Latency - Aggregated Graph

Aggregated Frame Loss per Frame Size




RFC2544 - Throughput/Latency - Aggregated Graph


Aggregated Frame Loss per Line Rate



RFC2544 - Throughput/Latency - Per Flow Graph




RFC2544 - Throughput/Latency - Aggregated Graph



RFC2544 - Throughput/Latency - Per Flow Graph

Tx / Rx Frame Count


■ @count_tx □ □
■ @count_rx □ □




Trial

RFC2544 - Throughput/Latency - Iteration Graph


Aggregated Frame Loss for Trial 1 and Framesize 64




Aggregated Frame Loss for Trial 1 and Framesize 128




Aggregated Frame Loss for Trial 1 and Framesize 256




Aggregated Frame Loss for Trial 1 and Framesize 512




Aggregated Frame Loss for Trial 1 and Framesize 1024




Aggregated Frame Loss for Trial 1 and Framesize 1280




Aggregated Frame Loss for Trial 1 and Framesize 1518

RFC2544 - Throughput/Latency - Iteration Graph

Tx / Rx Frames per Frame Size



RFC2544 - Throughput/Latency - Iteration Graph



RFC2544 - Throughput/Latency - Aggregated Results

Trial / Framesize / Iteration	Agg L2 Throughput				Agg L1 Throughput		Throughput (frames)		Agg Latency			
	AggTx Rate %	Agg Rx Rate			Tx Rate Mbps	Rx Rate Mbps			Min (ns)	Max (ns)	Average (ns)	
		%	FPS	Mbps								
Trial: 1 / FS: 64 / Iter: 9	100.00	100	2976190.5	1523.810			Tx : Rx : Loss : Loss% :	59523810.000 59523810.000 0 0.00	3252	4457	3295.000	
Trial: 1 / FS: 128 / Iter: 9	100.00	97	1689189.2	1675.676			Tx : Rx : Loss : Loss% :	33783784.000 33783784.000 0 0.00	3092	4582	3351.500	
Trial: 1 / FS: 256 / Iter: 9	100.00	99	905797.1	1826.087			Tx : Rx : Loss : Loss% :	18115942.000 18115942.000 0 0.00	2852	5910	3192.000	
Trial: 1 / FS: 512 / Iter: 9	100.00	99	469924.8	1909.774			Tx : Rx : Loss : Loss% :	9398496.000 9398496.000 0 0.00	3075	5895	3205.000	
Trial: 1 / FS: 1024 / Iter: 9	100.00	100	239463.6	1954.023			Tx : Rx : Loss : Loss% :	4789272.000 4789272.000 0 0.00	3222	4647	3397.000	
Trial: 1 / FS: 1280 / Iter: 9	100.00	100	192307.7	1963.077			Tx : Rx : Loss : Loss% :	3846154.000 3846154.000 0 0.00	3272	6185	3473.000	
Trial: 1 / FS: 1518 / Iter: 9	100.00	100	162548.8	1968.791			Tx : Rx : Loss : Loss% :	3250976.000 3250976.000 0 0.00	3030	5895	3185.500	

RFC2544 - Throughput/Latency - Aggregated Results

Trial / Framesize / Iteration	Agg L2 Throughput				Agg L1 Throughput		Throughput (frames)	Agg Latency			
	Agg Tx Rate %	Agg Rx Rate			Tx Rate Mbps	Rx Rate Mbps		Min (ns)	Max (ns)	Average (ns)	
		%	FPS	Mbps							
Trial: 1 / FS: 64 / Iter: 1	10	10	297619.0	152.381			Tx : 5952380.000 Rx : 5952380.000 Loss : 0 Loss% : 0.00	2775	5817	3083.500	
Trial: 1 / FS: 64 / Iter: 2	55	55	1636905.0	838.095			Tx : 32738096.000 Rx : 32738096.000 Loss : 0 Loss% : 0.00	2757	5800	3079.000	
Trial: 1 / FS: 64 / Iter: 3	78	78	2306549.4	1180.953			Tx : 46130952.000 Rx : 46130952.000 Loss : 0 Loss% : 0.00	2757	5720	3079.000	
Trial: 1 / FS: 64 / Iter: 4	89	89	2641370.1	1352.381			Tx : 52827380.000 Rx : 52827380.000 Loss : 0 Loss% : 0.00	2902	5752	3132.000	
Trial: 1 / FS: 64 / Iter: 5	94	94	2808782.2	1438.097			Tx : 56175596.000 Rx : 56175596.000 Loss : 0 Loss% : 0.00	3015	4440	3183.000	
Trial: 1 / FS: 64 / Iter: 6	97	97	2892485.4	1480.953			Tx : 57849702.000 Rx : 57849702.000 Loss : 0 Loss% : 0.00	2982	4440	3212.000	
Trial: 1 / FS: 64 / Iter: 7	99	99	2934339.6	1502.382			Tx : 58686756.000 Rx : 58686756.000 Loss : 0 Loss% : 0.00	3112	4457	3233.000	
Trial: 1 / FS: 64 / Iter: 8	99	99	2955266.9	1513.097			Tx : 59105282.000 Rx : 59105282.000 Loss : 0 Loss% : 0.00	3062	4455	3249.000	
Trial: 1 / FS: 64 / Iter: 9	100	100	2976190.5	1523.810			Tx : 59523810.000 Rx : 59523810.000 Loss : 0 Loss% : 0.00	3252	4457	3295.000	
Trial: 1 / FS: 128 / Iter: 1	10	10	168918.9	167.568			Tx : 3378378.000 Rx : 3378378.000 Loss : 0 Loss% : 0.00	2982	4455	3231.500	
Trial: 1 / FS: 128 / Iter: 2	55	54	929054.4	921.622			Tx : 18581082.000 Rx : 18581082.000 Loss : 0 Loss% : 0.00	2980	5015	3228.000	
Trial: 1 / FS: 128 / Iter: 3	78	75	1309122.1	1298.649			Tx : 26182432.000 Rx : 26182432.000 Loss : 0 Loss% : 0.00	2980	5927	3231.000	
Trial: 1 / FS: 128 / Iter: 4	89	86	1499155.5	1487.162			Tx : 29983108.000 Rx : 29983108.000 Loss : 0 Loss% : 0.00	2980	6040	3239.000	

Trial: 1 / FS: 128 / Iter: 5	94	92	1594172.3	1581.419	Tx : Rx : Loss : Loss% :	31883446.000 31883446.000 0 0.00	2997	6055	3258.000
Trial: 1 / FS: 128 / Iter: 6	97	95	1641681.2	1628.548	Tx : Rx : Loss : Loss% :	32833614.000 32833614.000 0 0.00	3012	6117	3274.000
Trial: 1 / FS: 128 / Iter: 7	99	96	1665434.9	1652.111	Tx : Rx : Loss : Loss% :	33308700.000 33308700.000 0 0.00	3030	5812	3296.000
Trial: 1 / FS: 128 / Iter: 8	99	97	1677312.6	1663.894	Tx : Rx : Loss : Loss% :	33546242.000 33546242.000 0 0.00	3092	4647	3323.000
Trial: 1 / FS: 128 / Iter: 9	100	97	1689189.2	1675.676	Tx : Rx : Loss : Loss% :	33783784.000 33783784.000 0 0.00	3092	4582	3351.500
Trial: 1 / FS: 256 / Iter: 1	10	10	90579.7	182.609	Tx : Rx : Loss : Loss% :	1811594.000 1811594.000 0 0.00	2772	4420	3083.000
Trial: 1 / FS: 256 / Iter: 2	55	54	498188.4	1004.348	Tx : Rx : Loss : Loss% :	9963768.000 9963768.000 0 0.00	2757	4440	3079.000
Trial: 1 / FS: 256 / Iter: 3	78	76	701992.8	1415.218	Tx : Rx : Loss : Loss% :	14039856.000 14039856.000 0 0.00	2755	4407	3078.500
Trial: 1 / FS: 256 / Iter: 4	89	87	803895.1	1620.653	Tx : Rx : Loss : Loss% :	16077898.000 16077898.000 0 0.00	2755	5460	3079.000
Trial: 1 / FS: 256 / Iter: 5	94	93	854846.1	1723.370	Tx : Rx : Loss : Loss% :	17096920.000 17096920.000 0 0.00	2835	5827	3110.000
Trial: 1 / FS: 256 / Iter: 6	97	96	880321.7	1774.728	Tx : Rx : Loss : Loss% :	17606432.000 17606432.000 0 0.00	2915	5832	3140.000
Trial: 1 / FS: 256 / Iter: 7	99	97	893059.6	1800.408	Tx : Rx : Loss : Loss% :	17861186.000 17861186.000 0 0.00	2980	5812	3160.500
Trial: 1 / FS: 256 / Iter: 8	99	98	899428.4	1813.248	Tx : Rx : Loss : Loss% :	17988564.000 17988564.000 0 0.00	3012	5832	3176.000
Trial: 1 / FS: 256 / Iter: 9	100	99	905797.1	1826.087	Tx : Rx : Loss : Loss% :	18115942.000 18115942.000 0 0.00	2852	5910	3192.000
Trial: 1 / FS: 512 / Iter: 1	10	10	46992.5	190.977	Tx : Rx : Loss : Loss% :	939850.000 939850.000 0 0.00	2790	3335	3090.500

Trial: 1 / FS: 512 / Iter: 2	55	55	258458.7	1050.376	Tx : Rx : Loss : Loss% :	5169172.000 5169172.000 0 0.00	2787	4182	3094.000
Trial: 1 / FS: 512 / Iter: 3	78	77	364191.8	1480.075	Tx : Rx : Loss : Loss% :	7283834.000 7283834.000 0 0.00	2787	4630	3093.500
Trial: 1 / FS: 512 / Iter: 4	89	88	417058.3	1694.925	Tx : Rx : Loss : Loss% :	8341166.000 8341166.000 0 0.00	2787	4357	3094.000
Trial: 1 / FS: 512 / Iter: 5	94	94	443491.6	1802.350	Tx : Rx : Loss : Loss% :	8869830.000 8869830.000 0 0.00	2787	4375	3094.000
Trial: 1 / FS: 512 / Iter: 6	97	96	456708.2	1856.062	Tx : Rx : Loss : Loss% :	9134164.000 9134164.000 0 0.00	2852	4295	3120.000
Trial: 1 / FS: 512 / Iter: 7	99	98	463316.5	1882.918	Tx : Rx : Loss : Loss% :	9266330.000 9266330.000 0 0.00	2837	4357	3151.000
Trial: 1 / FS: 512 / Iter: 8	99	99	466620.7	1896.346	Tx : Rx : Loss : Loss% :	9332414.000 9332414.000 0 0.00	2997	5862	3171.000
Trial: 1 / FS: 512 / Iter: 9	100	99	469924.8	1909.774	Tx : Rx : Loss : Loss% :	9398496.000 9398496.000 0 0.00	3075	5895	3205.000
Trial: 1 / FS: 1024 / Iter: 1	10	10	23946.4	195.402	Tx : Rx : Loss : Loss% :	478928.000 478928.000 0 0.00	3015	5895	3263.500
Trial: 1 / FS: 1024 / Iter: 2	55	55	131705.0	1074.713	Tx : Rx : Loss : Loss% :	2634100.000 2634100.000 0 0.00	2997	3832	3259.500
Trial: 1 / FS: 1024 / Iter: 3	78	77	185584.3	1514.368	Tx : Rx : Loss : Loss% :	3711686.000 3711686.000 0 0.00	3012	4665	3259.000
Trial: 1 / FS: 1024 / Iter: 4	89	88	212524.0	1734.195	Tx : Rx : Loss : Loss% :	4250478.000 4250478.000 0 0.00	3012	4855	3259.000
Trial: 1 / FS: 1024 / Iter: 5	94	94	225993.8	1844.109	Tx : Rx : Loss : Loss% :	4519876.000 4519876.000 0 0.00	3012	5592	3259.000
Trial: 1 / FS: 1024 / Iter: 6	97	97	232728.7	1899.066	Tx : Rx : Loss : Loss% :	4654574.000 4654574.000 0 0.00	3012	5927	3259.500
Trial: 1 / FS: 1024 / Iter: 7	99	98	236096.2	1926.545	Tx : Rx : Loss : Loss% :	4721922.000 4721922.000 0 0.00	3012	6005	3278.000

Trial: 1 / FS: 1024 / Iter: 8	99	99	237779.9	1940.284	Tx : Rx : Loss : Loss% :	4755598.000 4755598.000 0 0.00	3077	4600	3319.000
Trial: 1 / FS: 1024 / Iter: 9	100	100	239463.6	1954.023	Tx : Rx : Loss : Loss% :	4789272.000 4789272.000 0 0.00	3222	4647	3397.000
Trial: 1 / FS: 1280 / Iter: 1	10	10	19230.8	196.308	Tx : Rx : Loss : Loss% :	384616.000 384616.000 0 0.00	3127	3672	3376.000
Trial: 1 / FS: 1280 / Iter: 2	55	55	105769.2	1079.692	Tx : Rx : Loss : Loss% :	2115384.000 2115384.000 0 0.00	3125	4600	3372.000
Trial: 1 / FS: 1280 / Iter: 3	78	77	149038.5	1521.385	Tx : Rx : Loss : Loss% :	2980770.000 2980770.000 0 0.00	3125	4200	3372.000
Trial: 1 / FS: 1280 / Iter: 4	89	88	170673.1	1742.231	Tx : Rx : Loss : Loss% :	3413462.000 3413462.000 0 0.00	3125	4710	3372.000
Trial: 1 / FS: 1280 / Iter: 5	94	94	181490.4	1852.654	Tx : Rx : Loss : Loss% :	3629808.000 3629808.000 0 0.00	3125	5335	3372.000
Trial: 1 / FS: 1280 / Iter: 6	97	97	186899.0	1907.865	Tx : Rx : Loss : Loss% :	3737980.000 3737980.000 0 0.00	3125	5655	3372.000
Trial: 1 / FS: 1280 / Iter: 7	99	98	189603.4	1935.471	Tx : Rx : Loss : Loss% :	3792068.000 3792068.000 0 0.00	3125	5815	3372.000
Trial: 1 / FS: 1280 / Iter: 8	99	99	190955.5	1949.274	Tx : Rx : Loss : Loss% :	3819110.000 3819110.000 0 0.00	3125	6055	3372.000
Trial: 1 / FS: 1280 / Iter: 9	100	100	192307.7	1963.077	Tx : Rx : Loss : Loss% :	3846154.000 3846154.000 0 0.00	3272	6185	3473.000
Trial: 1 / FS: 1518 / Iter: 1	10	10	16254.9	196.879	Tx : Rx : Loss : Loss% :	325098.000 325098.000 0 0.00	2760	3320	3076.500
Trial: 1 / FS: 1518 / Iter: 2	55	55	89401.8	1082.835	Tx : Rx : Loss : Loss% :	1788036.000 1788036.000 0 0.00	2757	3320	3079.500
Trial: 1 / FS: 1518 / Iter: 3	78	77	125975.3	1525.813	Tx : Rx : Loss : Loss% :	2519506.000 2519506.000 0 0.00	2757	4022	3079.500
Trial: 1 / FS: 1518 / Iter: 4	89	89	144262.0	1747.302	Tx : Rx : Loss : Loss% :	2885240.000 2885240.000 0 0.00	2757	3320	3079.500

Trial: 1 / FS: 1518 / Iter: 5	94	94	153405.4	1858.046	Tx :	3068108.000	2757	3945	3079.500
					Rx :	3068108.000			
					Loss :	0			
					Loss% :	0.00			
Trial: 1 / FS: 1518 / Iter: 6	97	97	157977.1	1913.418	Tx :	3159542.000	2757	4232	3079.500
					Rx :	3159542.000			
					Loss :	0			
					Loss% :	0.00			
Trial: 1 / FS: 1518 / Iter: 7	99	98	160262.9	1941.105	Tx :	3205258.000	2805	5735	3096.000
					Rx :	3205258.000			
					Loss :	0			
					Loss% :	0.00			
Trial: 1 / FS: 1518 / Iter: 8	99	99	161405.8	1954.948	Tx :	3228116.000	2872	5720	3120.500
					Rx :	3228116.000			
					Loss :	0			
					Loss% :	0.00			
Trial: 1 / FS: 1518 / Iter: 9	100	100	162548.8	1968.791	Tx :	3250976.000	3030	5895	3185.500
					Rx :	3250976.000			
					Loss :	0			
					Loss% :	0.00			

RFC2544 - Throughput/Latency - Per Flow Statistics - Part 1 of 2

Trial / Framesize / Iteration	Tx Port	Rx Port	Flow Group	L2 Throughput				L1 Throughput		Throughput (frames)
				Tx Rate %	Rx Rate			Tx Rate Mbps	Rx Rate Mbps	
					%	FPS	Mbps			
Trial: 1 / FS: 64 / Iter: 9	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	100.00	100	1488095.2	761.91			Tx : 29761905 Rx : 29761905 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 64 / Iter: 9	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	100.00	100	1488095.2	761.91			Tx : 29761905 Rx : 29761905 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 9	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	100.00	97	844594.6	837.84			Tx : 16891892 Rx : 16891892 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 9	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	100.00	97	844594.6	837.84			Tx : 16891892 Rx : 16891892 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 9	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	100.00	99	452898.5	913.04			Tx : 9057971 Rx : 9057971 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 9	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	100.00	99	452898.5	913.04			Tx : 9057971 Rx : 9057971 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 9	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	100.00	99	234962.4	954.89			Tx : 4699248 Rx : 4699248 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 9	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	100.00	99	234962.4	954.89			Tx : 4699248 Rx : 4699248 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 9	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	100.00	100	119731.8	977.01			Tx : 2394636 Rx : 2394636 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 9	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	100.00	100	119731.8	977.01			Tx : 2394636 Rx : 2394636 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 9	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	100.00	100	96153.8	981.54			Tx : 1923077 Rx : 1923077 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 9	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	100.00	100	96153.8	981.54			Tx : 1923077 Rx : 1923077 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 9	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	100.00	100	81274.4	984.40			Tx : 1625488 Rx : 1625488 Loss : 0 Loss% : 0.000

Trial: 1 / FS: 1518 / Iter: 9	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	100.00	100	81274.4	984.40	Tx : 1625488
								Rx : 1625488
								Loss : 0
								Loss% : 0.000

RFC2544 - Throughput/Latency - Per Flow Statistics - Part 2 of 2

Trial / Framesize / Iteration	Tx Port	Rx Port	Flow Group	Min Latency (ns)	Max Latency (ns)	Avg Latency (ns)
Trial: 1 / FS: 64 / Iter: 9	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	3270	4457	3300
Trial: 1 / FS: 64 / Iter: 9	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	3252	4455	3290
Trial: 1 / FS: 128 / Iter: 9	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	3110	4582	3356
Trial: 1 / FS: 128 / Iter: 9	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	3092	4580	3347
Trial: 1 / FS: 256 / Iter: 9	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	2857	5802	3198
Trial: 1 / FS: 256 / Iter: 9	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	2852	5910	3186
Trial: 1 / FS: 512 / Iter: 9	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	3077	5895	3210
Trial: 1 / FS: 512 / Iter: 9	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	3075	5812	3200
Trial: 1 / FS: 1024 / Iter: 9	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	3237	4615	3402
Trial: 1 / FS: 1024 / Iter: 9	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	3222	4647	3392
Trial: 1 / FS: 1280 / Iter: 9	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	3287	6167	3477
Trial: 1 / FS: 1280 / Iter: 9	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	3272	6185	3469
Trial: 1 / FS: 1518 / Iter: 9	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	3047	5865	3191
Trial: 1 / FS: 1518 / Iter: 9	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	3030	5895	3180

RFC2544 - Throughput/Latency - Iteration Statistics - Part 1 of 2

Trial / Framesize / Iteration	Tx Port	Rx Port	Flow Group	L2 Throughput				L1 Throughput		Throughput (frames)			
				Tx Rate %	Rx Rate			Tx Rate Mbps	Rx Rate Mbps				
					%	FPS	Mbps						
Trial: 1 / FS: 64 / Iter: 1	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	10.00	10.00	148809.5	76.19			Tx : 2976190	Rx : 2976190	Loss : 0	Loss% : 0.000
Trial: 1 / FS: 64 / Iter: 1	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	10.00	10.00	148809.5	76.19			Tx : 2976190	Rx : 2976190	Loss : 0	Loss% : 0.000
Trial: 1 / FS: 64 / Iter: 2	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	55.00	55.00	818452.5	419.05			Tx : 16369048	Rx : 16369048	Loss : 0	Loss% : 0.000
Trial: 1 / FS: 64 / Iter: 2	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	55.00	55.00	818452.5	419.05			Tx : 16369048	Rx : 16369048	Loss : 0	Loss% : 0.000
Trial: 1 / FS: 64 / Iter: 3	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	77.50	77.50	1153274.7	590.48			Tx : 23065476	Rx : 23065476	Loss : 0	Loss% : 0.000
Trial: 1 / FS: 64 / Iter: 3	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	77.50	77.50	1153274.7	590.48			Tx : 23065476	Rx : 23065476	Loss : 0	Loss% : 0.000
Trial: 1 / FS: 64 / Iter: 4	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	88.75	88.75	1320685.0	676.19			Tx : 26413690	Rx : 26413690	Loss : 0	Loss% : 0.000
Trial: 1 / FS: 64 / Iter: 4	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	88.75	88.75	1320685.0	676.19			Tx : 26413690	Rx : 26413690	Loss : 0	Loss% : 0.000
Trial: 1 / FS: 64 / Iter: 5	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	94.38	94.38	1404391.1	719.05			Tx : 28087798	Rx : 28087798	Loss : 0	Loss% : 0.000
Trial: 1 / FS: 64 / Iter: 5	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	94.38	94.38	1404391.1	719.05			Tx : 28087798	Rx : 28087798	Loss : 0	Loss% : 0.000
Trial: 1 / FS: 64 / Iter: 6	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	97.19	97.19	1446242.7	740.48			Tx : 28924851	Rx : 28924851	Loss : 0	Loss% : 0.000
Trial: 1 / FS: 64 / Iter: 6	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	97.19	97.19	1446242.7	740.48			Tx : 28924851	Rx : 28924851	Loss : 0	Loss% : 0.000
Trial: 1 / FS: 64 / Iter: 7	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	98.59	98.59	1467169.8	751.19			Tx : 29343378	Rx : 29343378	Loss : 0	Loss% : 0.000

Trial: 1 / FS: 64 / Iter: 7	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	98.59	98.59	1467169.8	751.19	Tx : Rx : Loss : Loss% :	29343378 29343378 0 0.000
Trial: 1 / FS: 64 / Iter: 8	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	99.30	99.30	1477633.5	756.55	Tx : Rx : Loss : Loss% :	29552641 29552641 0 0.000
Trial: 1 / FS: 64 / Iter: 8	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	99.30	99.30	1477633.5	756.55	Tx : Rx : Loss : Loss% :	29552641 29552641 0 0.000
Trial: 1 / FS: 64 / Iter: 9	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	100.00	100.00	1488095.2	761.91	Tx : Rx : Loss : Loss% :	29761905 29761905 0 0.000
Trial: 1 / FS: 64 / Iter: 9	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	100.00	100.00	1488095.2	761.91	Tx : Rx : Loss : Loss% :	29761905 29761905 0 0.000
Trial: 1 / FS: 128 / Iter: 1	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	10.00	9.73	84459.5	83.78	Tx : Rx : Loss : Loss% :	1689189 1689189 0 0.000
Trial: 1 / FS: 128 / Iter: 1	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	10.00	9.73	84459.5	83.78	Tx : Rx : Loss : Loss% :	1689189 1689189 0 0.000
Trial: 1 / FS: 128 / Iter: 2	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	55.00	53.51	464527.2	460.81	Tx : Rx : Loss : Loss% :	9290541 9290541 0 0.000
Trial: 1 / FS: 128 / Iter: 2	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	55.00	53.51	464527.2	460.81	Tx : Rx : Loss : Loss% :	9290541 9290541 0 0.000
Trial: 1 / FS: 128 / Iter: 3	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	77.50	75.41	654561.0	649.33	Tx : Rx : Loss : Loss% :	13091216 13091216 0 0.000
Trial: 1 / FS: 128 / Iter: 3	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	77.50	75.41	654561.0	649.33	Tx : Rx : Loss : Loss% :	13091216 13091216 0 0.000
Trial: 1 / FS: 128 / Iter: 4	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	88.75	86.35	749577.8	743.58	Tx : Rx : Loss : Loss% :	14991554 14991554 0 0.000
Trial: 1 / FS: 128 / Iter: 4	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	88.75	86.35	749577.8	743.58	Tx : Rx : Loss : Loss% :	14991554 14991554 0 0.000
Trial: 1 / FS: 128 / Iter: 5	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	94.38	91.82	797086.2	790.71	Tx : Rx : Loss : Loss% :	15941723 15941723 0 0.000
Trial: 1 / FS: 128 / Iter: 5	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	94.38	91.82	797086.2	790.71	Tx : Rx : Loss : Loss% :	15941723 15941723 0 0.000

Trial: 1 / FS: 128 / Iter: 6	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	97.19	94.56	820840.6	814.27	Tx : Rx : Loss : Loss% :	16416807 16416807 0 0.000
Trial: 1 / FS: 128 / Iter: 6	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	97.19	94.56	820840.6	814.27	Tx : Rx : Loss : Loss% :	16416807 16416807 0 0.000
Trial: 1 / FS: 128 / Iter: 7	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	98.59	95.93	832717.5	826.06	Tx : Rx : Loss : Loss% :	16654350 16654350 0 0.000
Trial: 1 / FS: 128 / Iter: 7	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	98.59	95.93	832717.5	826.06	Tx : Rx : Loss : Loss% :	16654350 16654350 0 0.000
Trial: 1 / FS: 128 / Iter: 8	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	99.30	96.61	838656.3	831.95	Tx : Rx : Loss : Loss% :	16773121 16773121 0 0.000
Trial: 1 / FS: 128 / Iter: 8	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	99.30	96.61	838656.3	831.95	Tx : Rx : Loss : Loss% :	16773121 16773121 0 0.000
Trial: 1 / FS: 128 / Iter: 9	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	100.00	97.30	844594.6	837.84	Tx : Rx : Loss : Loss% :	16891892 16891892 0 0.000
Trial: 1 / FS: 128 / Iter: 9	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	100.00	97.30	844594.6	837.84	Tx : Rx : Loss : Loss% :	16891892 16891892 0 0.000
Trial: 1 / FS: 256 / Iter: 1	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	10.00	9.86	45289.9	91.30	Tx : Rx : Loss : Loss% :	905797 905797 0 0.000
Trial: 1 / FS: 256 / Iter: 1	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	10.00	9.86	45289.9	91.30	Tx : Rx : Loss : Loss% :	905797 905797 0 0.000
Trial: 1 / FS: 256 / Iter: 2	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	55.00	54.20	249094.2	502.17	Tx : Rx : Loss : Loss% :	4981884 4981884 0 0.000
Trial: 1 / FS: 256 / Iter: 2	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	55.00	54.20	249094.2	502.17	Tx : Rx : Loss : Loss% :	4981884 4981884 0 0.000
Trial: 1 / FS: 256 / Iter: 3	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	77.50	76.38	350996.4	707.61	Tx : Rx : Loss : Loss% :	7019928 7019928 0 0.000
Trial: 1 / FS: 256 / Iter: 3	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	77.50	76.38	350996.4	707.61	Tx : Rx : Loss : Loss% :	7019928 7019928 0 0.000
Trial: 1 / FS: 256 / Iter: 4	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	88.75	87.46	401947.6	810.33	Tx : Rx : Loss : Loss% :	8038949 8038949 0 0.000

Trial: 1 / FS: 256 / Iter: 4	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	88.75	87.46	401947.6	810.33	Tx : Rx : Loss : Loss% :	8038949 8038949 0 0.000
Trial: 1 / FS: 256 / Iter: 5	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	94.38	93.01	427423.1	861.69	Tx : Rx : Loss : Loss% :	8548460 8548460 0 0.000
Trial: 1 / FS: 256 / Iter: 5	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	94.38	93.01	427423.1	861.69	Tx : Rx : Loss : Loss% :	8548460 8548460 0 0.000
Trial: 1 / FS: 256 / Iter: 6	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	97.19	95.78	440160.8	887.36	Tx : Rx : Loss : Loss% :	8803216 8803216 0 0.000
Trial: 1 / FS: 256 / Iter: 6	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	97.19	95.78	440160.8	887.36	Tx : Rx : Loss : Loss% :	8803216 8803216 0 0.000
Trial: 1 / FS: 256 / Iter: 7	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	98.59	97.17	446529.8	900.20	Tx : Rx : Loss : Loss% :	8930593 8930593 0 0.000
Trial: 1 / FS: 256 / Iter: 7	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	98.59	97.17	446529.8	900.20	Tx : Rx : Loss : Loss% :	8930593 8930593 0 0.000
Trial: 1 / FS: 256 / Iter: 8	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	99.30	97.86	449714.2	906.62	Tx : Rx : Loss : Loss% :	8994282 8994282 0 0.000
Trial: 1 / FS: 256 / Iter: 8	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	99.30	97.86	449714.2	906.62	Tx : Rx : Loss : Loss% :	8994282 8994282 0 0.000
Trial: 1 / FS: 256 / Iter: 9	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	100.00	98.55	452898.5	913.04	Tx : Rx : Loss : Loss% :	9057971 9057971 0 0.000
Trial: 1 / FS: 256 / Iter: 9	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	100.00	98.55	452898.5	913.04	Tx : Rx : Loss : Loss% :	9057971 9057971 0 0.000
Trial: 1 / FS: 512 / Iter: 1	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	10.00	9.93	23496.2	95.49	Tx : Rx : Loss : Loss% :	469925 469925 0 0.000
Trial: 1 / FS: 512 / Iter: 1	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	10.00	9.93	23496.2	95.49	Tx : Rx : Loss : Loss% :	469925 469925 0 0.000
Trial: 1 / FS: 512 / Iter: 2	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	55.00	54.59	129229.3	525.19	Tx : Rx : Loss : Loss% :	2584586 2584586 0 0.000
Trial: 1 / FS: 512 / Iter: 2	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	55.00	54.59	129229.3	525.19	Tx : Rx : Loss : Loss% :	2584586 2584586 0 0.000

Trial: 1 / FS: 512 / Iter: 3	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	77.50	76.92	182095.9	740.04	Tx : Rx : Loss : Loss% :	3641917 3641917 0 0.000
Trial: 1 / FS: 512 / Iter: 3	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	77.50	76.92	182095.9	740.04	Tx : Rx : Loss : Loss% :	3641917 3641917 0 0.000
Trial: 1 / FS: 512 / Iter: 4	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	88.75	88.08	208529.1	847.46	Tx : Rx : Loss : Loss% :	4170583 4170583 0 0.000
Trial: 1 / FS: 512 / Iter: 4	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	88.75	88.08	208529.1	847.46	Tx : Rx : Loss : Loss% :	4170583 4170583 0 0.000
Trial: 1 / FS: 512 / Iter: 5	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	94.38	93.67	221745.8	901.18	Tx : Rx : Loss : Loss% :	4434915 4434915 0 0.000
Trial: 1 / FS: 512 / Iter: 5	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	94.38	93.67	221745.8	901.18	Tx : Rx : Loss : Loss% :	4434915 4434915 0 0.000
Trial: 1 / FS: 512 / Iter: 6	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	97.19	96.46	228354.1	928.03	Tx : Rx : Loss : Loss% :	4567082 4567082 0 0.000
Trial: 1 / FS: 512 / Iter: 6	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	97.19	96.46	228354.1	928.03	Tx : Rx : Loss : Loss% :	4567082 4567082 0 0.000
Trial: 1 / FS: 512 / Iter: 7	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	98.59	97.85	231658.3	941.46	Tx : Rx : Loss : Loss% :	4633165 4633165 0 0.000
Trial: 1 / FS: 512 / Iter: 7	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	98.59	97.85	231658.3	941.46	Tx : Rx : Loss : Loss% :	4633165 4633165 0 0.000
Trial: 1 / FS: 512 / Iter: 8	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	99.30	98.55	233310.3	948.17	Tx : Rx : Loss : Loss% :	4666207 4666207 0 0.000
Trial: 1 / FS: 512 / Iter: 8	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	99.30	98.55	233310.3	948.17	Tx : Rx : Loss : Loss% :	4666207 4666207 0 0.000
Trial: 1 / FS: 512 / Iter: 9	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	100.00	99.25	234962.4	954.89	Tx : Rx : Loss : Loss% :	4699248 4699248 0 0.000
Trial: 1 / FS: 512 / Iter: 9	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	100.00	99.25	234962.4	954.89	Tx : Rx : Loss : Loss% :	4699248 4699248 0 0.000
Trial: 1 / FS: 1024 / Iter: 1	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	10.00	9.96	11973.2	97.70	Tx : Rx : Loss : Loss% :	239464 239464 0 0.000

Trial: 1 / FS: 1024 / Iter: 1	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	10.00	9.96	11973.2	97.70	Tx : Rx : Loss : Loss% :	239464 239464 0 0.000
Trial: 1 / FS: 1024 / Iter: 2	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	55.00	54.79	65852.5	537.36	Tx : Rx : Loss : Loss% :	1317050 1317050 0 0.000
Trial: 1 / FS: 1024 / Iter: 2	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	55.00	54.79	65852.5	537.36	Tx : Rx : Loss : Loss% :	1317050 1317050 0 0.000
Trial: 1 / FS: 1024 / Iter: 3	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	77.50	77.20	92792.2	757.18	Tx : Rx : Loss : Loss% :	1855843 1855843 0 0.000
Trial: 1 / FS: 1024 / Iter: 3	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	77.50	77.20	92792.2	757.18	Tx : Rx : Loss : Loss% :	1855843 1855843 0 0.000
Trial: 1 / FS: 1024 / Iter: 4	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	88.75	88.41	106262.0	867.10	Tx : Rx : Loss : Loss% :	2125239 2125239 0 0.000
Trial: 1 / FS: 1024 / Iter: 4	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	88.75	88.41	106262.0	867.10	Tx : Rx : Loss : Loss% :	2125239 2125239 0 0.000
Trial: 1 / FS: 1024 / Iter: 5	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	94.38	94.01	112996.9	922.06	Tx : Rx : Loss : Loss% :	2259938 2259938 0 0.000
Trial: 1 / FS: 1024 / Iter: 5	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	94.38	94.01	112996.9	922.06	Tx : Rx : Loss : Loss% :	2259938 2259938 0 0.000
Trial: 1 / FS: 1024 / Iter: 6	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	97.19	96.82	116364.3	949.53	Tx : Rx : Loss : Loss% :	2327287 2327287 0 0.000
Trial: 1 / FS: 1024 / Iter: 6	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	97.19	96.82	116364.3	949.53	Tx : Rx : Loss : Loss% :	2327287 2327287 0 0.000
Trial: 1 / FS: 1024 / Iter: 7	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	98.59	98.22	118048.1	963.27	Tx : Rx : Loss : Loss% :	2360961 2360961 0 0.000
Trial: 1 / FS: 1024 / Iter: 7	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	98.59	98.22	118048.1	963.27	Tx : Rx : Loss : Loss% :	2360961 2360961 0 0.000
Trial: 1 / FS: 1024 / Iter: 8	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	99.30	98.92	118889.9	970.14	Tx : Rx : Loss : Loss% :	2377799 2377799 0 0.000
Trial: 1 / FS: 1024 / Iter: 8	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	99.30	98.92	118889.9	970.14	Tx : Rx : Loss : Loss% :	2377799 2377799 0 0.000

Trial: 1 / FS: 1024 / Iter: 9	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	100.00	99.62	119731.8	977.01	Tx : Rx : Loss : Loss% :	2394636 2394636 0 0.000
Trial: 1 / FS: 1024 / Iter: 9	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	100.00	99.62	119731.8	977.01	Tx : Rx : Loss : Loss% :	2394636 2394636 0 0.000
Trial: 1 / FS: 1280 / Iter: 1	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	10.00	9.97	9615.4	98.15	Tx : Rx : Loss : Loss% :	192308 192308 0 0.000
Trial: 1 / FS: 1280 / Iter: 1	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	10.00	9.97	9615.4	98.15	Tx : Rx : Loss : Loss% :	192308 192308 0 0.000
Trial: 1 / FS: 1280 / Iter: 2	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	55.00	54.83	52884.6	539.85	Tx : Rx : Loss : Loss% :	1057692 1057692 0 0.000
Trial: 1 / FS: 1280 / Iter: 2	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	55.00	54.83	52884.6	539.85	Tx : Rx : Loss : Loss% :	1057692 1057692 0 0.000
Trial: 1 / FS: 1280 / Iter: 3	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	77.50	77.26	74519.2	760.69	Tx : Rx : Loss : Loss% :	1490385 1490385 0 0.000
Trial: 1 / FS: 1280 / Iter: 3	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	77.50	77.26	74519.2	760.69	Tx : Rx : Loss : Loss% :	1490385 1490385 0 0.000
Trial: 1 / FS: 1280 / Iter: 4	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	88.75	88.48	85336.5	871.12	Tx : Rx : Loss : Loss% :	1706731 1706731 0 0.000
Trial: 1 / FS: 1280 / Iter: 4	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	88.75	88.48	85336.5	871.12	Tx : Rx : Loss : Loss% :	1706731 1706731 0 0.000
Trial: 1 / FS: 1280 / Iter: 5	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	94.38	94.09	90745.2	926.33	Tx : Rx : Loss : Loss% :	1814904 1814904 0 0.000
Trial: 1 / FS: 1280 / Iter: 5	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	94.38	94.09	90745.2	926.33	Tx : Rx : Loss : Loss% :	1814904 1814904 0 0.000
Trial: 1 / FS: 1280 / Iter: 6	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	97.19	96.89	93449.5	953.93	Tx : Rx : Loss : Loss% :	1868990 1868990 0 0.000
Trial: 1 / FS: 1280 / Iter: 6	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	97.19	96.89	93449.5	953.93	Tx : Rx : Loss : Loss% :	1868990 1868990 0 0.000
Trial: 1 / FS: 1280 / Iter: 7	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	98.59	98.29	94801.7	967.74	Tx : Rx : Loss : Loss% :	1896034 1896034 0 0.000

Trial: 1 / FS: 1280 / Iter: 7	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	98.59	98.29	94801.7	967.74	Tx : Rx : Loss : Loss% :	1896034 1896034 0 0.000
Trial: 1 / FS: 1280 / Iter: 8	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	99.30	98.99	95477.8	974.64	Tx : Rx : Loss : Loss% :	1909555 1909555 0 0.000
Trial: 1 / FS: 1280 / Iter: 8	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	99.30	98.99	95477.8	974.64	Tx : Rx : Loss : Loss% :	1909555 1909555 0 0.000
Trial: 1 / FS: 1280 / Iter: 9	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	100.00	99.69	96153.8	981.54	Tx : Rx : Loss : Loss% :	1923077 1923077 0 0.000
Trial: 1 / FS: 1280 / Iter: 9	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	100.00	99.69	96153.8	981.54	Tx : Rx : Loss : Loss% :	1923077 1923077 0 0.000
Trial: 1 / FS: 1518 / Iter: 1	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	10.00	9.97	8127.4	98.44	Tx : Rx : Loss : Loss% :	162549 162549 0 0.000
Trial: 1 / FS: 1518 / Iter: 1	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	10.00	9.97	8127.4	98.44	Tx : Rx : Loss : Loss% :	162549 162549 0 0.000
Trial: 1 / FS: 1518 / Iter: 2	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	55.00	54.86	44700.9	541.42	Tx : Rx : Loss : Loss% :	894018 894018 0 0.000
Trial: 1 / FS: 1518 / Iter: 2	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	55.00	54.86	44700.9	541.42	Tx : Rx : Loss : Loss% :	894018 894018 0 0.000
Trial: 1 / FS: 1518 / Iter: 3	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	77.50	77.30	62987.6	762.91	Tx : Rx : Loss : Loss% :	1259753 1259753 0 0.000
Trial: 1 / FS: 1518 / Iter: 3	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	77.50	77.30	62987.6	762.91	Tx : Rx : Loss : Loss% :	1259753 1259753 0 0.000
Trial: 1 / FS: 1518 / Iter: 4	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	88.75	88.52	72131.0	873.65	Tx : Rx : Loss : Loss% :	1442620 1442620 0 0.000
Trial: 1 / FS: 1518 / Iter: 4	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	88.75	88.52	72131.0	873.65	Tx : Rx : Loss : Loss% :	1442620 1442620 0 0.000
Trial: 1 / FS: 1518 / Iter: 5	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	94.38	94.13	76702.7	929.02	Tx : Rx : Loss : Loss% :	1534054 1534054 0 0.000
Trial: 1 / FS: 1518 / Iter: 5	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	94.38	94.13	76702.7	929.02	Tx : Rx : Loss : Loss% :	1534054 1534054 0 0.000

Trial: 1 / FS: 1518 / Iter: 6	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	97.19	96.94	78988.5	956.71	Tx : Rx : Loss : Loss% :	1579771 1579771 0 0.000
Trial: 1 / FS: 1518 / Iter: 6	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	97.19	96.94	78988.5	956.71	Tx : Rx : Loss : Loss% :	1579771 1579771 0 0.000
Trial: 1 / FS: 1518 / Iter: 7	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	98.59	98.34	80131.5	970.55	Tx : Rx : Loss : Loss% :	1602629 1602629 0 0.000
Trial: 1 / FS: 1518 / Iter: 7	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	98.59	98.34	80131.5	970.55	Tx : Rx : Loss : Loss% :	1602629 1602629 0 0.000
Trial: 1 / FS: 1518 / Iter: 8	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	99.30	99.04	80702.9	977.47	Tx : Rx : Loss : Loss% :	1614058 1614058 0 0.000
Trial: 1 / FS: 1518 / Iter: 8	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	99.30	99.04	80702.9	977.47	Tx : Rx : Loss : Loss% :	1614058 1614058 0 0.000
Trial: 1 / FS: 1518 / Iter: 9	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	100.00	99.74	81274.4	984.40	Tx : Rx : Loss : Loss% :	1625488 1625488 0 0.000
Trial: 1 / FS: 1518 / Iter: 9	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	100.00	99.74	81274.4	984.40	Tx : Rx : Loss : Loss% :	1625488 1625488 0 0.000

RFC2544 - Throughput/Latency - Iteration Statistics - Part 2 of 2

Trial / Framesize / Iteration	Tx Port	Rx Port	Flow Group	Min Latency (ns)	Max Latency (ns)	Avg Latency (ns)
Trial: 1 / FS: 64 / Iter: 1	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	2777	5817	3089.00
Trial: 1 / FS: 64 / Iter: 1	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	2775	4357	3078.00
Trial: 1 / FS: 64 / Iter: 2	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	2775	5800	3084.00
Trial: 1 / FS: 64 / Iter: 2	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	2757	5110	3074.00
Trial: 1 / FS: 64 / Iter: 3	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	2775	5720	3084.00
Trial: 1 / FS: 64 / Iter: 3	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	2757	5302	3074.00
Trial: 1 / FS: 64 / Iter: 4	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	2917	5752	3137.00
Trial: 1 / FS: 64 / Iter: 4	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	2902	5590	3127.00
Trial: 1 / FS: 64 / Iter: 5	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	3030	4440	3188.00
Trial: 1 / FS: 64 / Iter: 5	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	3015	4390	3178.00
Trial: 1 / FS: 64 / Iter: 6	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	2982	4440	3217.00
Trial: 1 / FS: 64 / Iter: 6	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	2982	4407	3207.00
Trial: 1 / FS: 64 / Iter: 7	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	3127	4457	3238.00
Trial: 1 / FS: 64 / Iter: 7	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	3112	4422	3228.00
Trial: 1 / FS: 64 / Iter: 8	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	3065	4455	3254.00
Trial: 1 / FS: 64 / Iter: 8	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	3062	4455	3244.00
Trial: 1 / FS: 64 / Iter: 9	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	3270	4457	3300.00
Trial: 1 / FS: 64 / Iter: 9	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	3252	4455	3290.00
Trial: 1 / FS: 128 / Iter: 1	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	2997	3527	3236.00

Trial: 1 / FS: 128 / Iter: 1	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	2982	4455	3227.00
Trial: 1 / FS: 128 / Iter: 2	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	2982	5015	3233.00
Trial: 1 / FS: 128 / Iter: 2	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	2980	4902	3223.00
Trial: 1 / FS: 128 / Iter: 3	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	2997	5880	3236.00
Trial: 1 / FS: 128 / Iter: 3	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	2980	5927	3226.00
Trial: 1 / FS: 128 / Iter: 4	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	2997	5910	3244.00
Trial: 1 / FS: 128 / Iter: 4	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	2980	6040	3234.00
Trial: 1 / FS: 128 / Iter: 5	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	3015	6055	3263.00
Trial: 1 / FS: 128 / Iter: 5	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	2997	6020	3253.00
Trial: 1 / FS: 128 / Iter: 6	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	3030	5847	3279.00
Trial: 1 / FS: 128 / Iter: 6	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	3012	6117	3269.00
Trial: 1 / FS: 128 / Iter: 7	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	3045	5797	3301.00
Trial: 1 / FS: 128 / Iter: 7	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	3030	5812	3291.00
Trial: 1 / FS: 128 / Iter: 8	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	3110	4647	3328.00
Trial: 1 / FS: 128 / Iter: 8	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	3092	4597	3318.00
Trial: 1 / FS: 128 / Iter: 9	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	3110	4582	3356.00
Trial: 1 / FS: 128 / Iter: 9	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	3092	4580	3347.00
Trial: 1 / FS: 256 / Iter: 1	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	2792	3322	3090.00
Trial: 1 / FS: 256 / Iter: 1	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	2772	4420	3076.00
Trial: 1 / FS: 256 / Iter: 2	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	2775	4440	3085.00
Trial: 1 / FS: 256 / Iter: 2	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	2757	3670	3073.00

Trial: 1 / FS: 256 / Iter: 3	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	2775	4407	3085.00
Trial: 1 / FS: 256 / Iter: 3	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	2755	4310	3072.00
Trial: 1 / FS: 256 / Iter: 4	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	2775	5222	3085.00
Trial: 1 / FS: 256 / Iter: 4	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	2755	5460	3073.00
Trial: 1 / FS: 256 / Iter: 5	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	2840	5575	3116.00
Trial: 1 / FS: 256 / Iter: 5	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	2835	5827	3104.00
Trial: 1 / FS: 256 / Iter: 6	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	2935	5832	3146.00
Trial: 1 / FS: 256 / Iter: 6	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	2915	5685	3134.00
Trial: 1 / FS: 256 / Iter: 7	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	3000	5802	3167.00
Trial: 1 / FS: 256 / Iter: 7	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	2980	5812	3154.00
Trial: 1 / FS: 256 / Iter: 8	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	3032	5832	3182.00
Trial: 1 / FS: 256 / Iter: 8	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	3012	5765	3170.00
Trial: 1 / FS: 256 / Iter: 9	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	2857	5802	3198.00
Trial: 1 / FS: 256 / Iter: 9	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	2852	5910	3186.00
Trial: 1 / FS: 512 / Iter: 1	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	2807	3335	3096.00
Trial: 1 / FS: 512 / Iter: 1	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	2790	3332	3085.00
Trial: 1 / FS: 512 / Iter: 2	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	2805	4182	3099.00
Trial: 1 / FS: 512 / Iter: 2	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	2787	4052	3089.00
Trial: 1 / FS: 512 / Iter: 3	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	2805	4280	3099.00
Trial: 1 / FS: 512 / Iter: 3	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	2787	4630	3088.00
Trial: 1 / FS: 512 / Iter: 4	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	2805	4357	3099.00

Trial: 1 / FS: 512 / Iter: 4	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	2787	3910	3089.00
Trial: 1 / FS: 512 / Iter: 5	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	2805	4182	3099.00
Trial: 1 / FS: 512 / Iter: 5	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	2787	4375	3089.00
Trial: 1 / FS: 512 / Iter: 6	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	2855	4295	3125.00
Trial: 1 / FS: 512 / Iter: 6	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	2852	4260	3115.00
Trial: 1 / FS: 512 / Iter: 7	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	2840	4357	3156.00
Trial: 1 / FS: 512 / Iter: 7	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	2837	4310	3146.00
Trial: 1 / FS: 512 / Iter: 8	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	3012	5862	3176.00
Trial: 1 / FS: 512 / Iter: 8	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	2997	4357	3166.00
Trial: 1 / FS: 512 / Iter: 9	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	3077	5895	3210.00
Trial: 1 / FS: 512 / Iter: 9	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	3075	5812	3200.00
Trial: 1 / FS: 1024 / Iter: 1	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	3032	3560	3269.00
Trial: 1 / FS: 1024 / Iter: 1	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	3015	5895	3258.00
Trial: 1 / FS: 1024 / Iter: 2	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	3030	3560	3264.00
Trial: 1 / FS: 1024 / Iter: 2	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	2997	3832	3255.00
Trial: 1 / FS: 1024 / Iter: 3	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	3030	4665	3264.00
Trial: 1 / FS: 1024 / Iter: 3	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	3012	4087	3254.00
Trial: 1 / FS: 1024 / Iter: 4	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	3030	4855	3264.00
Trial: 1 / FS: 1024 / Iter: 4	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	3012	4740	3254.00
Trial: 1 / FS: 1024 / Iter: 5	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	3030	5415	3264.00
Trial: 1 / FS: 1024 / Iter: 5	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	3012	5592	3254.00

Trial: 1 / FS: 1024 / Iter: 6	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	3030	5927	3264.00
Trial: 1 / FS: 1024 / Iter: 6	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	3012	5687	3255.00
Trial: 1 / FS: 1024 / Iter: 7	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	3030	5815	3283.00
Trial: 1 / FS: 1024 / Iter: 7	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	3012	6005	3273.00
Trial: 1 / FS: 1024 / Iter: 8	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	3095	4600	3324.00
Trial: 1 / FS: 1024 / Iter: 8	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	3077	4520	3314.00
Trial: 1 / FS: 1024 / Iter: 9	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	3237	4615	3402.00
Trial: 1 / FS: 1024 / Iter: 9	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	3222	4647	3392.00
Trial: 1 / FS: 1280 / Iter: 1	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	3145	3672	3382.00
Trial: 1 / FS: 1280 / Iter: 1	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	3127	3670	3370.00
Trial: 1 / FS: 1280 / Iter: 2	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	3142	4600	3377.00
Trial: 1 / FS: 1280 / Iter: 2	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	3125	3672	3367.00
Trial: 1 / FS: 1280 / Iter: 3	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	3142	4200	3377.00
Trial: 1 / FS: 1280 / Iter: 3	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	3125	3672	3367.00
Trial: 1 / FS: 1280 / Iter: 4	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	3127	4647	3377.00
Trial: 1 / FS: 1280 / Iter: 4	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	3125	4710	3367.00
Trial: 1 / FS: 1280 / Iter: 5	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	3142	5272	3377.00
Trial: 1 / FS: 1280 / Iter: 5	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	3125	5335	3367.00
Trial: 1 / FS: 1280 / Iter: 6	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	3142	5655	3377.00
Trial: 1 / FS: 1280 / Iter: 6	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	3125	5512	3367.00
Trial: 1 / FS: 1280 / Iter: 7	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	3142	5815	3377.00

Trial: 1 / FS: 1280 / Iter: 7	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	3125	5750	3367.00
Trial: 1 / FS: 1280 / Iter: 8	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	3142	5832	3377.00
Trial: 1 / FS: 1280 / Iter: 8	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	3125	6055	3367.00
Trial: 1 / FS: 1280 / Iter: 9	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	3287	6167	3477.00
Trial: 1 / FS: 1280 / Iter: 9	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	3272	6185	3469.00
Trial: 1 / FS: 1518 / Iter: 1	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	2775	3320	3081.00
Trial: 1 / FS: 1518 / Iter: 1	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	2760	3305	3072.00
Trial: 1 / FS: 1518 / Iter: 2	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	2775	3320	3085.00
Trial: 1 / FS: 1518 / Iter: 2	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	2757	3320	3074.00
Trial: 1 / FS: 1518 / Iter: 3	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	2775	3320	3085.00
Trial: 1 / FS: 1518 / Iter: 3	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	2757	4022	3074.00
Trial: 1 / FS: 1518 / Iter: 4	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	2775	3320	3085.00
Trial: 1 / FS: 1518 / Iter: 4	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	2757	3320	3074.00
Trial: 1 / FS: 1518 / Iter: 5	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	2775	3945	3085.00
Trial: 1 / FS: 1518 / Iter: 5	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	2757	3622	3074.00
Trial: 1 / FS: 1518 / Iter: 6	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	2775	4232	3085.00
Trial: 1 / FS: 1518 / Iter: 6	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	2757	3895	3074.00
Trial: 1 / FS: 1518 / Iter: 7	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	2822	5447	3101.00
Trial: 1 / FS: 1518 / Iter: 7	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	2805	5735	3091.00
Trial: 1 / FS: 1518 / Iter: 8	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	2887	5720	3126.00
Trial: 1 / FS: 1518 / Iter: 8	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	2872	5622	3115.00



Trial: 1 / FS: 1518 / Iter: 9	3-10	3-11	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0001	3047	5865	3191.00
Trial: 1 / FS: 1518 / Iter: 9	3-11	3-10	QT-Rfc2544Tput #1-Endpoint Set-1 - Flow Group 0002	3030	5895	3180.00

Theoretical maximum Frame Rates (frames/second) for different frame sizes (bytes)

Speed	64	128	256	512	1024	1280	1518
10 Mbps	14881	8446	4529	2350	1198	962	813
100 Mbps	148810	84460	45290	23497	11973	9616	8128
1000 Mbps	1488096	844595	452899	234963	119732	96154	81275
10 Gbps	14880952	8445946	4528986	2349625	1197318	961539	812744
25 Gbps	37202380	21114864	11322463	5874060	2993295	2403846	2031859
40 Gbps	59523809	33783783	18115942	9398496	4789272	3846153	3250975
100 Gbps	148809523	84459459	45289855	23496240	11973180	9615384	8127438
155 Mbps (Oc - 3)	288000	145116	72840	36491	18263	14614	12324
622 Mbps (Oc - 12)	1152000	580465	291362	145965	73054	58454	49296
2488 Mbps (Oc - 48)	4608000	2321860	1165447	583860	292215	233817	197182
9952 Mbps (Oc - 192)	18432000	9287442	4661790	2335439	1168859	935270	788730