



IxNetwork Report

Test: RFC2544 - Throughput/Latency

Test Date: 07/13/2020 13:25:34

www.ixiacom.com
www.ixiacom.com/support

Table of Contents

1.	Cover	1
2.	Info	3
3.	Port Map	4
4.	Aggregate Graphs	5
5.	IterationCharts	13
6.	Aggregated Results	19
7.	Aggregated Results Per Iteration	20
8.	Per Flow Results	25
9.	Iteration Data	27
10.	Theoretical Max Rates	43

RFC2544 - Throughput/Latency - Info**Test Information****Product Information**

Product Label :	N8550-48B8C
Product Version :	Compiled Jul 5 2020
Serial Number :	732656X2009046
Comments :	

Test Settings

Date Executed :	07/13/2020
Time Executed :	13:25:34
User Name :	
Number of Trials Executed :	1
Stream Duration (sec) :	20

Output Parameters

Number of Trials Passed :	N/A
Test Duration :	00:49:15


RFC2544 - Throughput/Latency - Port Map Information

Port Map :	Tx Port	Tx Speed (Mbps)	Rx Port	Rx Speed (Mbps)
	10.32.133.101:6:17	25000	10.32.133.101:6:18	25000
	10.32.133.101:6:18	25000	10.32.133.101:6:17	25000

RFC2544 - Throughput/Latency - Aggregated Graph


Total Frames Transmitted and Received

Tx Frames
Rx Frames




Trial - Framesize - Iteration

RFC2544 - Throughput/Latency - Aggregated Graph




RFC2544 - Throughput/Latency - Aggregated Graph

Aggregated Frame Loss




RFC2544 - Throughput/Latency - Aggregated Graph

Aggregated Frame Loss per Frame Size




RFC2544 - Throughput/Latency - Aggregated Graph


Aggregated Frame Loss per Line Rate



RFC2544 - Throughput/Latency - Per Flow Graph





RFC2544 - Throughput/Latency - Aggregated Graph



RFC2544 - Throughput/Latency - Per Flow Graph


Tx / Rx Frame Count




Trial



RFC2544 - Throughput/Latency - Iteration Graph

Aggregated Frame Loss for Trial 1 and Framesize 64




Aggregated Frame Loss for Trial 1 and Framesize 128





Aggregated Frame Loss for Trial 1 and Framesize 256**Aggregated Frame Loss for Trial 1 and Framesize 512**

Aggregated Frame Loss for Trial 1 and Framesize 1024




Aggregated Frame Loss for Trial 1 and Framesize 1280




Aggregated Frame Loss for Trial 1 and Framesize 1518

RFC2544 - Throughput/Latency - Iteration Graph

Tx / Rx Frames per Frame Size



RFC2544 - Throughput/Latency - Iteration Graph



RFC2544 - Throughput/Latency - Aggregated Results

Trial / Framesize / Iteration	Agg L2 Throughput				Agg L1 Throughput		Throughput (frames)		Agg Latency			
	AggTx Rate %	Agg Rx Rate			Tx Rate Mbps	Rx Rate Mbps			Min (ns)	Max (ns)	Average (ns)	
		%	FPS	Mbps								
Trial: 1 / FS: 64 / Iter: 9	100.00	100	74404761.8	38095.238			Tx : Rx : Loss : Loss% :	1488095238.000 1488095238.000 0 0.00	827	910	839.000	
Trial: 1 / FS: 128 / Iter: 9	100.00	100	42229729.7	43243.243			Tx : Rx : Loss : Loss% :	844594594.000 844594594.000 0 0.00	825	912	839.500	
Trial: 1 / FS: 256 / Iter: 9	100.00	100	22644927.5	46376.812			Tx : Rx : Loss : Loss% :	452898550.000 452898550.000 0 0.00	822	860	829.000	
Trial: 1 / FS: 512 / Iter: 9	100.00	100	11748120.3	48120.301			Tx : Rx : Loss : Loss% :	234962406.000 234962406.000 0 0.00	740	787	752.500	
Trial: 1 / FS: 1024 / Iter: 9	100.00	100	5986590.0	49042.146			Tx : Rx : Loss : Loss% :	119731800.000 119731800.000 0 0.00	580	667	596.500	
Trial: 1 / FS: 1280 / Iter: 9	100.00	100	4807692.3	49230.769			Tx : Rx : Loss : Loss% :	96153846.000 96153846.000 0 0.00	512	595	524.500	
Trial: 1 / FS: 1518 / Iter: 9	100.00	100	4063719.1	49349.805			Tx : Rx : Loss : Loss% :	81274382.000 81274382.000 0 0.00	440	520	451.000	

RFC2544 - Throughput/Latency - Aggregated Results

Trial / Framesize / Iteration	Agg L2 Throughput				Agg L1 Throughput		Throughput (frames)	Agg Latency			
	AggTx Rate %	Agg Rx Rate			Tx Rate Mbps	Rx Rate Mbps		Min (ns)	Max (ns)	Average (ns)	
		%	FPS	Mbps							
Trial: 1 / FS: 64 / Iter: 1	10	10	7440476.2	3809.524			Tx : 148809524.000 Rx : 148809524.000 Loss : 0 Loss% : 0.00	817	882	830.500	
Trial: 1 / FS: 64 / Iter: 2	55	55	40922613.1	20952.378			Tx : 818452380.000 Rx : 818452380.000 Loss : 0 Loss% : 0.00	815	892	830.000	
Trial: 1 / FS: 64 / Iter: 3	78	78	57663631.8	29523.779			Tx : 1153273810.000 Rx : 1153273810.000 Loss : 0 Loss% : 0.00	815	900	830.000	
Trial: 1 / FS: 64 / Iter: 4	89	89	66034183.0	33809.502			Tx : 1320684524.000 Rx : 1320684524.000 Loss : 0 Loss% : 0.00	817	847	831.000	
Trial: 1 / FS: 64 / Iter: 5	94	94	70219518.3	35952.393			Tx : 1404389880.000 Rx : 1404389880.000 Loss : 0 Loss% : 0.00	817	897	832.000	
Trial: 1 / FS: 64 / Iter: 6	97	97	72312094.4	37023.792			Tx : 1446242560.000 Rx : 1446242560.000 Loss : 0 Loss% : 0.00	820	862	833.000	
Trial: 1 / FS: 64 / Iter: 7	99	99	73358531.2	37559.568			Tx : 1467168898.000 Rx : 1467168898.000 Loss : 0 Loss% : 0.00	822	902	833.500	
Trial: 1 / FS: 64 / Iter: 8	99	99	73881673.8	37827.417			Tx : 1477632068.000 Rx : 1477632068.000 Loss : 0 Loss% : 0.00	822	847	834.000	
Trial: 1 / FS: 64 / Iter: 9	100	100	74404761.8	38095.238			Tx : 1488095238.000 Rx : 1488095238.000 Loss : 0 Loss% : 0.00	827	910	839.000	
Trial: 1 / FS: 128 / Iter: 1	10	10	4222973.0	4324.324			Tx : 84459460.000 Rx : 84459460.000 Loss : 0 Loss% : 0.00	815	845	829.500	
Trial: 1 / FS: 128 / Iter: 2	55	55	23226359.0	23783.792			Tx : 464527028.000 Rx : 464527028.000 Loss : 0 Loss% : 0.00	815	890	829.500	
Trial: 1 / FS: 128 / Iter: 3	78	78	32728035.1	33513.508			Tx : 654560810.000 Rx : 654560810.000 Loss : 0 Loss% : 0.00	815	845	829.500	
Trial: 1 / FS: 128 / Iter: 4	89	89	37478899.8	38378.393			Tx : 749577702.000 Rx : 749577702.000 Loss : 0 Loss% : 0.00	815	892	830.000	

Trial: 1 / FS: 128 / Iter: 5	94	94	39854282.8	40810.786	Tx : Rx : Loss : Loss% :	797086148.000 797086148.000 0 0.00	815	902	831.000
Trial: 1 / FS: 128 / Iter: 6	97	97	41042018.4	42027.027	Tx : Rx : Loss : Loss% :	820840372.000 820840372.000 0 0.00	817	897	832.000
Trial: 1 / FS: 128 / Iter: 7	99	99	41635900.5	42635.162	Tx : Rx : Loss : Loss% :	832717484.000 832717484.000 0 0.00	820	905	833.000
Trial: 1 / FS: 128 / Iter: 8	99	99	41932773.2	42939.160	Tx : Rx : Loss : Loss% :	838656038.000 838656038.000 0 0.00	822	862	834.000
Trial: 1 / FS: 128 / Iter: 9	100	100	42229729.7	43243.243	Tx : Rx : Loss : Loss% :	844594594.000 844594594.000 0 0.00	825	912	839.500
Trial: 1 / FS: 256 / Iter: 1	10	10	2264492.8	4637.681	Tx : Rx : Loss : Loss% :	45289856.000 45289856.000 0 0.00	802	835	820.500
Trial: 1 / FS: 256 / Iter: 2	55	55	12454711.8	25507.250	Tx : Rx : Loss : Loss% :	249094202.000 249094202.000 0 0.00	802	835	820.500
Trial: 1 / FS: 256 / Iter: 3	78	78	17549813.0	35942.017	Tx : Rx : Loss : Loss% :	350996376.000 350996376.000 0 0.00	802	835	820.500
Trial: 1 / FS: 256 / Iter: 4	89	89	20097378.1	41159.430	Tx : Rx : Loss : Loss% :	401947464.000 401947464.000 0 0.00	802	887	820.500
Trial: 1 / FS: 256 / Iter: 5	94	94	21371142.4	43768.100	Tx : Rx : Loss : Loss% :	427423008.000 427423008.000 0 0.00	802	852	821.500
Trial: 1 / FS: 256 / Iter: 6	97	97	22008045.0	45072.476	Tx : Rx : Loss : Loss% :	440160778.000 440160778.000 0 0.00	807	885	822.500
Trial: 1 / FS: 256 / Iter: 7	99	99	22326490.0	45724.652	Tx : Rx : Loss : Loss% :	446529664.000 446529664.000 0 0.00	810	850	823.500
Trial: 1 / FS: 256 / Iter: 8	99	99	22485707.1	46050.728	Tx : Rx : Loss : Loss% :	449714108.000 449714108.000 0 0.00	810	892	824.500
Trial: 1 / FS: 256 / Iter: 9	100	100	22644927.5	46376.812	Tx : Rx : Loss : Loss% :	452898550.000 452898550.000 0 0.00	822	860	829.000
Trial: 1 / FS: 512 / Iter: 1	10	10	1174812.0	4812.030	Tx : Rx : Loss : Loss% :	23496240.000 23496240.000 0 0.00	727	760	743.000

Trial: 1 / FS: 512 / Iter: 2	55	55	6461466.3	26466.166	Tx : Rx : Loss : Loss% :	129229324.000 129229324.000 0 0.00	727	760	743.000
Trial: 1 / FS: 512 / Iter: 3	78	78	9104792.6	37293.231	Tx : Rx : Loss : Loss% :	182095864.000 182095864.000 0 0.00	727	805	741.500
Trial: 1 / FS: 512 / Iter: 4	89	89	10426458.4	42706.774	Tx : Rx : Loss : Loss% :	208529136.000 208529136.000 0 0.00	727	785	743.000
Trial: 1 / FS: 512 / Iter: 5	94	94	11087290.8	45413.543	Tx : Rx : Loss : Loss% :	221745770.000 221745770.000 0 0.00	727	772	743.000
Trial: 1 / FS: 512 / Iter: 6	97	97	11417704.2	46766.916	Tx : Rx : Loss : Loss% :	228354088.000 228354088.000 0 0.00	727	805	744.000
Trial: 1 / FS: 512 / Iter: 7	99	99	11582913.8	47443.615	Tx : Rx : Loss : Loss% :	231658248.000 231658248.000 0 0.00	730	777	745.000
Trial: 1 / FS: 512 / Iter: 8	99	99	11665516.8	47781.957	Tx : Rx : Loss : Loss% :	233310326.000 233310326.000 0 0.00	732	812	746.000
Trial: 1 / FS: 512 / Iter: 9	100	100	11748120.3	48120.301	Tx : Rx : Loss : Loss% :	234962406.000 234962406.000 0 0.00	740	787	752.500
Trial: 1 / FS: 1024 / Iter: 1	10	10	598659.0	4904.215	Tx : Rx : Loss : Loss% :	11973180.000 11973180.000 0 0.00	572	605	588.000
Trial: 1 / FS: 1024 / Iter: 2	55	55	3292624.4	26973.179	Tx : Rx : Loss : Loss% :	65852490.000 65852490.000 0 0.00	572	605	588.000
Trial: 1 / FS: 1024 / Iter: 3	78	78	4639607.6	38007.666	Tx : Rx : Loss : Loss% :	92792146.000 92792146.000 0 0.00	572	605	588.000
Trial: 1 / FS: 1024 / Iter: 4	89	89	5313098.2	43524.900	Tx : Rx : Loss : Loss% :	106261974.000 106261974.000 0 0.00	572	605	588.000
Trial: 1 / FS: 1024 / Iter: 5	94	94	5649844.7	46283.528	Tx : Rx : Loss : Loss% :	112996886.000 112996886.000 0 0.00	572	637	588.000
Trial: 1 / FS: 1024 / Iter: 6	97	97	5818217.5	47662.838	Tx : Rx : Loss : Loss% :	116364344.000 116364344.000 0 0.00	572	620	588.500
Trial: 1 / FS: 1024 / Iter: 7	99	99	5902403.8	48352.492	Tx : Rx : Loss : Loss% :	118048072.000 118048072.000 0 0.00	575	657	589.000

Trial: 1 / FS: 1024 / Iter: 8	99	99	5944497.0	48697.319	Tx : Rx : Loss : Loss% :	118889936.000 118889936.000 0 0.00	577	657	590.000
Trial: 1 / FS: 1024 / Iter: 9	100	100	5986590.0	49042.146	Tx : Rx : Loss : Loss% :	119731800.000 119731800.000 0 0.00	580	667	596.500
Trial: 1 / FS: 1280 / Iter: 1	10	10	480769.2	4923.077	Tx : Rx : Loss : Loss% :	9615384.000 9615384.000 0 0.00	500	530	513.500
Trial: 1 / FS: 1280 / Iter: 2	55	55	2644230.6	27076.922	Tx : Rx : Loss : Loss% :	52884616.000 52884616.000 0 0.00	497	530	513.500
Trial: 1 / FS: 1280 / Iter: 3	78	78	3725961.4	38153.844	Tx : Rx : Loss : Loss% :	74519230.000 74519230.000 0 0.00	497	570	513.500
Trial: 1 / FS: 1280 / Iter: 4	89	89	4266826.7	43692.305	Tx : Rx : Loss : Loss% :	85336538.000 85336538.000 0 0.00	497	530	513.500
Trial: 1 / FS: 1280 / Iter: 5	94	94	4537259.8	46461.540	Tx : Rx : Loss : Loss% :	90745192.000 90745192.000 0 0.00	497	572	513.500
Trial: 1 / FS: 1280 / Iter: 6	97	97	4672475.9	47846.153	Tx : Rx : Loss : Loss% :	93449520.000 93449520.000 0 0.00	497	530	513.500
Trial: 1 / FS: 1280 / Iter: 7	99	99	4740084.2	48538.462	Tx : Rx : Loss : Loss% :	94801682.000 94801682.000 0 0.00	497	577	514.500
Trial: 1 / FS: 1280 / Iter: 8	99	99	4773888.3	48884.616	Tx : Rx : Loss : Loss% :	95477764.000 95477764.000 0 0.00	502	535	515.000
Trial: 1 / FS: 1280 / Iter: 9	100	100	4807692.3	49230.769	Tx : Rx : Loss : Loss% :	96153846.000 96153846.000 0 0.00	512	595	524.500
Trial: 1 / FS: 1518 / Iter: 1	10	10	406371.9	4934.980	Tx : Rx : Loss : Loss% :	8127438.000 8127438.000 0 0.00	427	457	442.000
Trial: 1 / FS: 1518 / Iter: 2	55	55	2235045.6	27142.394	Tx : Rx : Loss : Loss% :	44700910.000 44700910.000 0 0.00	427	460	442.000
Trial: 1 / FS: 1518 / Iter: 3	78	78	3149382.3	38246.099	Tx : Rx : Loss : Loss% :	62987646.000 62987646.000 0 0.00	420	477	442.000
Trial: 1 / FS: 1518 / Iter: 4	89	89	3606550.7	43797.951	Tx : Rx : Loss : Loss% :	72131014.000 72131014.000 0 0.00	417	502	443.500

Trial: 1 / FS: 1518 / Iter: 5	94	94	3835134.8	46573.876	Tx : Rx : Loss : Loss% :	76702698.000 76702698.000 0 0.00	427	485	442.000
Trial: 1 / FS: 1518 / Iter: 6	97	97	3949427.0	47961.841	Tx : Rx : Loss : Loss% :	78988540.000 78988540.000 0 0.00	427	460	442.000
Trial: 1 / FS: 1518 / Iter: 7	99	99	4006573.3	48655.826	Tx : Rx : Loss : Loss% :	80131462.000 80131462.000 0 0.00	427	507	442.500
Trial: 1 / FS: 1518 / Iter: 8	99	99	4035146.1	49002.815	Tx : Rx : Loss : Loss% :	80702922.000 80702922.000 0 0.00	430	460	443.000
Trial: 1 / FS: 1518 / Iter: 9	100	100	4063719.1	49349.805	Tx : Rx : Loss : Loss% :	81274382.000 81274382.000 0 0.00	440	520	451.000

RFC2544 - Throughput/Latency - Per Flow Statistics - Part 1 of 2

Trial / Framesize / Iteration	Tx Port	Rx Port	Flow Group	Tx Rate %	L2 Throughput			L1 Throughput		Throughput (frames)
					%	FPS	Mbps	Tx Rate Mbps	Rx Rate Mbps	
Trial: 1 / FS: 64 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	100.00	100	37202380.9	19047.62			Tx : 744047619 Rx : 744047619 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 64 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	100.00	100	37202380.9	19047.62			Tx : 744047619 Rx : 744047619 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	100.00	100	21114864.9	21621.62			Tx : 422297297 Rx : 422297297 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	100.00	100	21114864.8	21621.62			Tx : 422297297 Rx : 422297297 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	100.00	100	11322463.8	23188.41			Tx : 226449275 Rx : 226449275 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	100.00	100	11322463.8	23188.41			Tx : 226449275 Rx : 226449275 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	100.00	100	5874060.1	24060.15			Tx : 117481203 Rx : 117481203 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	100.00	100	5874060.1	24060.15			Tx : 117481203 Rx : 117481203 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	100.00	100	2993295.0	24521.07			Tx : 59865900 Rx : 59865900 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	100.00	100	2993295.0	24521.07			Tx : 59865900 Rx : 59865900 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	100.00	100	2403846.2	24615.39			Tx : 48076923 Rx : 48076923 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	100.00	100	2403846.2	24615.39			Tx : 48076923 Rx : 48076923 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	100.00	100	2031859.6	24674.90			Tx : 40637191 Rx : 40637191 Loss : 0 Loss% : 0.000

Trial: 1 / FS: 1518 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	100.00	100	2031859.6	24674.90	Tx : 40637191
								Rx : 40637191
								Loss : 0
								Loss% : 0.000

RFC2544 - Throughput/Latency - Per Flow Statistics - Part 2 of 2

Trial / Framesize / Iteration	Tx Port	Rx Port	Flow Group	Min Latency (ns)	Max Latency (ns)	Avg Latency (ns)
Trial: 1 / FS: 64 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	827	910	840
Trial: 1 / FS: 64 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	830	907	838
Trial: 1 / FS: 128 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	830	905	838
Trial: 1 / FS: 128 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	825	912	841
Trial: 1 / FS: 256 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	822	860	828
Trial: 1 / FS: 256 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	825	860	830
Trial: 1 / FS: 512 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	740	782	751
Trial: 1 / FS: 512 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	747	787	754
Trial: 1 / FS: 1024 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	580	662	596
Trial: 1 / FS: 1024 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	590	667	597
Trial: 1 / FS: 1280 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	512	595	524
Trial: 1 / FS: 1280 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	517	595	525
Trial: 1 / FS: 1518 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	440	520	449
Trial: 1 / FS: 1518 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	442	520	453

RFC2544 - Throughput/Latency - Iteration Statistics - Part 1 of 2

Trial / Framesize / Iteration	Tx Port	Rx Port	Flow Group	L2 Throughput				L1 Throughput		Throughput (frames)		
				Tx Rate %	Rx Rate			Tx Rate Mbps	Rx Rate Mbps			
					%	FPS	Mbps					
Trial: 1 / FS: 64 / Iter: 1	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	10.00	10.00	3720238.1	1904.76			Tx : 74404762 Rx : 74404762 Loss : 0 Loss% : 0.000		
Trial: 1 / FS: 64 / Iter: 1	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	10.00	10.00	3720238.1	1904.76			Tx : 74404762 Rx : 74404762 Loss : 0 Loss% : 0.000		
Trial: 1 / FS: 64 / Iter: 2	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	55.00	55.00	20461306.6	10476.19			Tx : 409226190 Rx : 409226190 Loss : 0 Loss% : 0.000		
Trial: 1 / FS: 64 / Iter: 2	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	55.00	55.00	20461306.5	10476.19			Tx : 409226190 Rx : 409226190 Loss : 0 Loss% : 0.000		
Trial: 1 / FS: 64 / Iter: 3	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	77.50	77.50	28831815.9	14761.89			Tx : 576636905 Rx : 576636905 Loss : 0 Loss% : 0.000		
Trial: 1 / FS: 64 / Iter: 3	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	77.50	77.50	28831815.9	14761.89			Tx : 576636905 Rx : 576636905 Loss : 0 Loss% : 0.000		
Trial: 1 / FS: 64 / Iter: 4	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	88.75	88.75	33017091.5	16904.75			Tx : 660342262 Rx : 660342262 Loss : 0 Loss% : 0.000		
Trial: 1 / FS: 64 / Iter: 4	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	88.75	88.75	33017091.5	16904.75			Tx : 660342262 Rx : 660342262 Loss : 0 Loss% : 0.000		
Trial: 1 / FS: 64 / Iter: 5	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	94.38	94.38	35109759.2	17976.20			Tx : 702194940 Rx : 702194940 Loss : 0 Loss% : 0.000		
Trial: 1 / FS: 64 / Iter: 5	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	94.38	94.38	35109759.1	17976.20			Tx : 702194940 Rx : 702194940 Loss : 0 Loss% : 0.000		
Trial: 1 / FS: 64 / Iter: 6	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	97.19	97.19	36156047.2	18511.90			Tx : 723121280 Rx : 723121280 Loss : 0 Loss% : 0.000		
Trial: 1 / FS: 64 / Iter: 6	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	97.19	97.19	36156047.2	18511.90			Tx : 723121280 Rx : 723121280 Loss : 0 Loss% : 0.000		
Trial: 1 / FS: 64 / Iter: 7	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	98.59	98.59	36679265.6	18779.78			Tx : 733584449 Rx : 733584449 Loss : 0 Loss% : 0.000		

Trial: 1 / FS: 64 / Iter: 7	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	98.59	98.59	36679265.6	18779.78	Tx : 733584449 Rx : 733584449 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 64 / Iter: 8	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	99.30	99.30	36940836.9	18913.71	Tx : 738816034 Rx : 738816034 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 64 / Iter: 8	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	99.30	99.30	36940836.9	18913.71	Tx : 738816034 Rx : 738816034 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 64 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	100.00	100.00	37202380.9	19047.62	Tx : 744047619 Rx : 744047619 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 64 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	100.00	100.00	37202380.9	19047.62	Tx : 744047619 Rx : 744047619 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 1	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	10.00	10.00	2111486.5	2162.16	Tx : 42229730 Rx : 42229730 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 1	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	10.00	10.00	2111486.5	2162.16	Tx : 42229730 Rx : 42229730 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 2	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	55.00	55.00	11613179.5	11891.90	Tx : 232263514 Rx : 232263514 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 2	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	55.00	55.00	11613179.5	11891.90	Tx : 232263514 Rx : 232263514 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 3	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	77.50	77.50	16364017.6	16756.75	Tx : 327280405 Rx : 327280405 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 3	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	77.50	77.50	16364017.6	16756.75	Tx : 327280405 Rx : 327280405 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 4	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	88.75	88.75	18739449.9	19189.20	Tx : 374788851 Rx : 374788851 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 4	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	88.75	88.75	18739449.9	19189.20	Tx : 374788851 Rx : 374788851 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 5	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	94.38	94.38	19927141.4	20405.39	Tx : 398543074 Rx : 398543074 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 5	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	94.38	94.38	19927141.4	20405.39	Tx : 398543074 Rx : 398543074 Loss : 0 Loss% : 0.000

Trial: 1 / FS: 128 / Iter: 6	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	97.19	97.19	20521009.2	21013.51	Tx : 410420186
								Rx : 410420186
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 6	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	97.19	97.19	20521009.2	21013.51	Tx : 410420186
								Rx : 410420186
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 7	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	98.59	98.59	20817950.3	21317.58	Tx : 416358742
								Rx : 416358742
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 7	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	98.59	98.59	20817950.3	21317.58	Tx : 416358742
								Rx : 416358742
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 8	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	99.30	99.30	20966386.6	21469.58	Tx : 419328019
								Rx : 419328019
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 8	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	99.30	99.30	20966386.6	21469.58	Tx : 419328019
								Rx : 419328019
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	100.00	100.00	21114864.9	21621.62	Tx : 422297297
								Rx : 422297297
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	100.00	100.00	21114864.8	21621.62	Tx : 422297297
								Rx : 422297297
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 1	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	10.00	10.00	1132246.4	2318.84	Tx : 22644928
								Rx : 22644928
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 1	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	10.00	10.00	1132246.4	2318.84	Tx : 22644928
								Rx : 22644928
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 2	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	55.00	55.00	6227355.9	12753.63	Tx : 124547101
								Rx : 124547101
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 2	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	55.00	55.00	6227355.9	12753.63	Tx : 124547101
								Rx : 124547101
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 3	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	77.50	77.50	8774906.5	17971.01	Tx : 175498188
								Rx : 175498188
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 3	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	77.50	77.50	8774906.5	17971.01	Tx : 175498188
								Rx : 175498188
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 4	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	88.75	88.75	10048689.0	20579.72	Tx : 200973732
								Rx : 200973732
								Loss : 0
								Loss% : 0.000

Trial: 1 / FS: 256 / Iter: 4	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	88.75	88.75	10048689.0	20579.72	Tx : 200973732
								Rx : 200973732
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 5	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	94.38	94.38	10685571.2	21884.05	Tx : 213711504
								Rx : 213711504
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 5	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	94.38	94.38	10685571.2	21884.05	Tx : 213711504
								Rx : 213711504
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 6	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	97.19	97.19	11004022.5	22536.24	Tx : 220080389
								Rx : 220080389
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 6	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	97.19	97.19	11004022.5	22536.24	Tx : 220080389
								Rx : 220080389
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 7	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	98.59	98.59	11163245.0	22862.33	Tx : 223264832
								Rx : 223264832
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 7	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	98.59	98.59	11163245.0	22862.33	Tx : 223264832
								Rx : 223264832
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 8	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	99.30	99.30	11242853.5	23025.36	Tx : 224857054
								Rx : 224857054
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 8	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	99.30	99.30	11242853.5	23025.36	Tx : 224857054
								Rx : 224857054
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	100.00	100.00	11322463.8	23188.41	Tx : 226449275
								Rx : 226449275
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	100.00	100.00	11322463.8	23188.41	Tx : 226449275
								Rx : 226449275
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 1	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	10.00	10.00	587406.0	2406.02	Tx : 11748120
								Rx : 11748120
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 1	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	10.00	10.00	587406.0	2406.02	Tx : 11748120
								Rx : 11748120
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 2	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	55.00	55.00	3230733.2	13233.08	Tx : 64614662
								Rx : 64614662
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 2	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	55.00	55.00	3230733.2	13233.08	Tx : 64614662
								Rx : 64614662
								Loss : 0
								Loss% : 0.000

Trial: 1 / FS: 512 / Iter: 3	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	77.50	77.50	4552396.3	18646.62	Tx : 91047932
								Rx : 91047932
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 3	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	77.50	77.50	4552396.3	18646.62	Tx : 91047932
								Rx : 91047932
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 4	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	88.75	88.75	5213229.2	21353.39	Tx : 104264568
								Rx : 104264568
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 4	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	88.75	88.75	5213229.2	21353.39	Tx : 104264568
								Rx : 104264568
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 5	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	94.38	94.38	5543645.4	22706.77	Tx : 110872885
								Rx : 110872885
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 5	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	94.38	94.38	5543645.4	22706.77	Tx : 110872885
								Rx : 110872885
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 6	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	97.19	97.19	5708852.1	23383.46	Tx : 114177044
								Rx : 114177044
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 6	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	97.19	97.19	5708852.1	23383.46	Tx : 114177044
								Rx : 114177044
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 7	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	98.59	98.59	5791456.9	23721.81	Tx : 115829124
								Rx : 115829124
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 7	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	98.59	98.59	5791456.9	23721.81	Tx : 115829124
								Rx : 115829124
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 8	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	99.30	99.30	5832758.4	23890.98	Tx : 116655163
								Rx : 116655163
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 8	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	99.30	99.30	5832758.4	23890.98	Tx : 116655163
								Rx : 116655163
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	100.00	100.00	5874060.1	24060.15	Tx : 117481203
								Rx : 117481203
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	100.00	100.00	5874060.1	24060.15	Tx : 117481203
								Rx : 117481203
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 1	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	10.00	10.00	299329.5	2452.11	Tx : 5986590
								Rx : 5986590
								Loss : 0
								Loss% : 0.000

Trial: 1 / FS: 1024 / Iter: 1	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	10.00	10.00	299329.5	2452.11	Tx : 5986590
								Rx : 5986590
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 2	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	55.00	55.00	1646312.2	13486.59	Tx : 32926245
								Rx : 32926245
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 2	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	55.00	55.00	1646312.2	13486.59	Tx : 32926245
								Rx : 32926245
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 3	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	77.50	77.50	2319803.8	19003.83	Tx : 46396073
								Rx : 46396073
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 3	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	77.50	77.50	2319803.8	19003.83	Tx : 46396073
								Rx : 46396073
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 4	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	88.75	88.75	2656549.1	21762.45	Tx : 53130987
								Rx : 53130987
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 4	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	88.75	88.75	2656549.1	21762.45	Tx : 53130987
								Rx : 53130987
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 5	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	94.38	94.38	2824922.3	23141.76	Tx : 56498443
								Rx : 56498443
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 5	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	94.38	94.38	2824922.3	23141.76	Tx : 56498443
								Rx : 56498443
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 6	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	97.19	97.19	2909108.8	23831.42	Tx : 58182172
								Rx : 58182172
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 6	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	97.19	97.19	2909108.8	23831.42	Tx : 58182172
								Rx : 58182172
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 7	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	98.59	98.59	2951201.9	24176.25	Tx : 59024036
								Rx : 59024036
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 7	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	98.59	98.59	2951201.9	24176.25	Tx : 59024036
								Rx : 59024036
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 8	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	99.30	99.30	2972248.5	24348.66	Tx : 59444968
								Rx : 59444968
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 8	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	99.30	99.30	2972248.5	24348.66	Tx : 59444968
								Rx : 59444968
								Loss : 0
								Loss% : 0.000

Trial: 1 / FS: 1024 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	100.00	100.00	2993295.0	24521.07	Tx : 59865900
								Rx : 59865900
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	100.00	100.00	2993295.0	24521.07	Tx : 59865900
								Rx : 59865900
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 1	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	10.00	10.00	240384.6	2461.54	Tx : 4807692
								Rx : 4807692
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 1	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	10.00	10.00	240384.6	2461.54	Tx : 4807692
								Rx : 4807692
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 2	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	55.00	55.00	1322115.3	13538.46	Tx : 26442308
								Rx : 26442308
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 2	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	55.00	55.00	1322115.3	13538.46	Tx : 26442308
								Rx : 26442308
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 3	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	77.50	77.50	1862980.7	19076.92	Tx : 37259615
								Rx : 37259615
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 3	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	77.50	77.50	1862980.7	19076.92	Tx : 37259615
								Rx : 37259615
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 4	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	88.75	88.75	2133413.3	21846.15	Tx : 42668269
								Rx : 42668269
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 4	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	88.75	88.75	2133413.3	21846.15	Tx : 42668269
								Rx : 42668269
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 5	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	94.38	94.38	2268629.9	23230.77	Tx : 45372596
								Rx : 45372596
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 5	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	94.38	94.38	2268629.9	23230.77	Tx : 45372596
								Rx : 45372596
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 6	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	97.19	97.19	2336237.9	23923.08	Tx : 46724760
								Rx : 46724760
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 6	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	97.19	97.19	2336237.9	23923.08	Tx : 46724760
								Rx : 46724760
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 7	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	98.59	98.59	2370042.1	24269.23	Tx : 47400841
								Rx : 47400841
								Loss : 0
								Loss% : 0.000

Trial: 1 / FS: 1280 / Iter: 7	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	98.59	98.59	2370042.1	24269.23	Tx : 47400841
								Rx : 47400841
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 8	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	99.30	99.30	2386944.2	24442.31	Tx : 47738882
								Rx : 47738882
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 8	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	99.30	99.30	2386944.2	24442.31	Tx : 47738882
								Rx : 47738882
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	100.00	100.00	2403846.2	24615.39	Tx : 48076923
								Rx : 48076923
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	100.00	100.00	2403846.2	24615.39	Tx : 48076923
								Rx : 48076923
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 1	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	10.00	10.00	203186.0	2467.49	Tx : 4063719
								Rx : 4063719
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 1	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	10.00	10.00	203186.0	2467.49	Tx : 4063719
								Rx : 4063719
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 2	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	55.00	55.00	1117522.8	13571.20	Tx : 22350455
								Rx : 22350455
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 2	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	55.00	55.00	1117522.8	13571.20	Tx : 22350455
								Rx : 22350455
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 3	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	77.50	77.50	1574691.2	19123.05	Tx : 31493823
								Rx : 31493823
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 3	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	77.50	77.50	1574691.2	19123.05	Tx : 31493823
								Rx : 31493823
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 4	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	88.75	88.75	1803275.3	21898.98	Tx : 36065507
								Rx : 36065507
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 4	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	88.75	88.75	1803275.3	21898.98	Tx : 36065507
								Rx : 36065507
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 5	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	94.38	94.38	1917567.4	23286.94	Tx : 38351349
								Rx : 38351349
								Loss : 0
								Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 5	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	94.38	94.38	1917567.4	23286.94	Tx : 38351349
								Rx : 38351349
								Loss : 0
								Loss% : 0.000

Trial: 1 / FS: 1518 / Iter: 6	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	97.19	97.19	1974713.5	23980.92	Tx : 39494270 Rx : 39494270 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 6	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	97.19	97.19	1974713.5	23980.92	Tx : 39494270 Rx : 39494270 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 7	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	98.59	98.59	2003286.6	24327.91	Tx : 40065731 Rx : 40065731 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 7	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	98.59	98.59	2003286.6	24327.91	Tx : 40065731 Rx : 40065731 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 8	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	99.30	99.30	2017573.1	24501.41	Tx : 40351461 Rx : 40351461 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 8	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	99.30	99.30	2017573.1	24501.41	Tx : 40351461 Rx : 40351461 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	100.00	100.00	2031859.6	24674.90	Tx : 40637191 Rx : 40637191 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	100.00	100.00	2031859.6	24674.90	Tx : 40637191 Rx : 40637191 Loss : 0 Loss% : 0.000

RFC2544 - Throughput/Latency - Iteration Statistics - Part 2 of 2

Trial / Framesize / Iteration	Tx Port	Rx Port	Flow Group	Min Latency (ns)	Max Latency (ns)	Avg Latency (ns)
Trial: 1 / FS: 64 / Iter: 1	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	817	845	830.00
Trial: 1 / FS: 64 / Iter: 1	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	817	882	831.00
Trial: 1 / FS: 64 / Iter: 2	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	815	870	829.00
Trial: 1 / FS: 64 / Iter: 2	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	815	892	831.00
Trial: 1 / FS: 64 / Iter: 3	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	815	897	829.00
Trial: 1 / FS: 64 / Iter: 3	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	817	900	831.00
Trial: 1 / FS: 64 / Iter: 4	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	817	845	830.00
Trial: 1 / FS: 64 / Iter: 4	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	817	847	832.00
Trial: 1 / FS: 64 / Iter: 5	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	817	897	831.00
Trial: 1 / FS: 64 / Iter: 5	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	820	897	833.00
Trial: 1 / FS: 64 / Iter: 6	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	820	860	832.00
Trial: 1 / FS: 64 / Iter: 6	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	822	862	834.00
Trial: 1 / FS: 64 / Iter: 7	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	822	900	832.00
Trial: 1 / FS: 64 / Iter: 7	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	825	902	835.00
Trial: 1 / FS: 64 / Iter: 8	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	822	845	832.00
Trial: 1 / FS: 64 / Iter: 8	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	825	847	836.00
Trial: 1 / FS: 64 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	827	910	840.00
Trial: 1 / FS: 64 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	830	907	838.00
Trial: 1 / FS: 128 / Iter: 1	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	815	842	828.00

Trial: 1 / FS: 128 / Iter: 1	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	817	845	831.00
Trial: 1 / FS: 128 / Iter: 2	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	815	890	828.00
Trial: 1 / FS: 128 / Iter: 2	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	817	860	831.00
Trial: 1 / FS: 128 / Iter: 3	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	815	842	828.00
Trial: 1 / FS: 128 / Iter: 3	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	817	845	831.00
Trial: 1 / FS: 128 / Iter: 4	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	815	892	829.00
Trial: 1 / FS: 128 / Iter: 4	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	817	892	831.00
Trial: 1 / FS: 128 / Iter: 5	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	815	902	830.00
Trial: 1 / FS: 128 / Iter: 5	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	820	900	832.00
Trial: 1 / FS: 128 / Iter: 6	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	817	895	831.00
Trial: 1 / FS: 128 / Iter: 6	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	820	897	833.00
Trial: 1 / FS: 128 / Iter: 7	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	820	905	832.00
Trial: 1 / FS: 128 / Iter: 7	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	822	902	834.00
Trial: 1 / FS: 128 / Iter: 8	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	822	857	833.00
Trial: 1 / FS: 128 / Iter: 8	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	827	862	835.00
Trial: 1 / FS: 128 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	830	905	838.00
Trial: 1 / FS: 128 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	825	912	841.00
Trial: 1 / FS: 256 / Iter: 1	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	802	832	819.00
Trial: 1 / FS: 256 / Iter: 1	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	807	835	822.00
Trial: 1 / FS: 256 / Iter: 2	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	802	832	819.00
Trial: 1 / FS: 256 / Iter: 2	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	807	835	822.00

Trial: 1 / FS: 256 / Iter: 3	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	802	832	819.00
Trial: 1 / FS: 256 / Iter: 3	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	807	835	822.00
Trial: 1 / FS: 256 / Iter: 4	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	802	867	819.00
Trial: 1 / FS: 256 / Iter: 4	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	807	887	822.00
Trial: 1 / FS: 256 / Iter: 5	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	802	847	820.00
Trial: 1 / FS: 256 / Iter: 5	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	807	852	823.00
Trial: 1 / FS: 256 / Iter: 6	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	807	885	821.00
Trial: 1 / FS: 256 / Iter: 6	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	810	880	824.00
Trial: 1 / FS: 256 / Iter: 7	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	810	847	822.00
Trial: 1 / FS: 256 / Iter: 7	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	812	850	825.00
Trial: 1 / FS: 256 / Iter: 8	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	810	892	823.00
Trial: 1 / FS: 256 / Iter: 8	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	815	890	826.00
Trial: 1 / FS: 256 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	822	860	828.00
Trial: 1 / FS: 256 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	825	860	830.00
Trial: 1 / FS: 512 / Iter: 1	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	727	757	741.00
Trial: 1 / FS: 512 / Iter: 1	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	732	760	745.00
Trial: 1 / FS: 512 / Iter: 2	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	727	757	741.00
Trial: 1 / FS: 512 / Iter: 2	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	730	760	745.00
Trial: 1 / FS: 512 / Iter: 3	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	727	805	741.00
Trial: 1 / FS: 512 / Iter: 3	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	727	760	742.00
Trial: 1 / FS: 512 / Iter: 4	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	727	785	741.00

Trial: 1 / FS: 512 / Iter: 4	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	730	777	745.00
Trial: 1 / FS: 512 / Iter: 5	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	727	762	741.00
Trial: 1 / FS: 512 / Iter: 5	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	730	772	745.00
Trial: 1 / FS: 512 / Iter: 6	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	727	805	742.00
Trial: 1 / FS: 512 / Iter: 6	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	730	802	746.00
Trial: 1 / FS: 512 / Iter: 7	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	730	777	743.00
Trial: 1 / FS: 512 / Iter: 7	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	735	772	747.00
Trial: 1 / FS: 512 / Iter: 8	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	732	805	744.00
Trial: 1 / FS: 512 / Iter: 8	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	735	812	748.00
Trial: 1 / FS: 512 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	740	782	751.00
Trial: 1 / FS: 512 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	747	787	754.00
Trial: 1 / FS: 1024 / Iter: 1	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	572	602	586.00
Trial: 1 / FS: 1024 / Iter: 1	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	577	605	590.00
Trial: 1 / FS: 1024 / Iter: 2	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	572	602	586.00
Trial: 1 / FS: 1024 / Iter: 2	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	577	605	590.00
Trial: 1 / FS: 1024 / Iter: 3	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	572	605	586.00
Trial: 1 / FS: 1024 / Iter: 3	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	577	605	590.00
Trial: 1 / FS: 1024 / Iter: 4	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	572	602	586.00
Trial: 1 / FS: 1024 / Iter: 4	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	577	605	590.00
Trial: 1 / FS: 1024 / Iter: 5	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	572	632	586.00
Trial: 1 / FS: 1024 / Iter: 5	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	577	637	590.00

Trial: 1 / FS: 1024 / Iter: 6	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	572	612	587.00
Trial: 1 / FS: 1024 / Iter: 6	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	577	620	590.00
Trial: 1 / FS: 1024 / Iter: 7	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	575	647	587.00
Trial: 1 / FS: 1024 / Iter: 7	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	577	657	591.00
Trial: 1 / FS: 1024 / Iter: 8	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	577	657	588.00
Trial: 1 / FS: 1024 / Iter: 8	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	580	652	592.00
Trial: 1 / FS: 1024 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	580	662	596.00
Trial: 1 / FS: 1024 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	590	667	597.00
Trial: 1 / FS: 1280 / Iter: 1	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	500	530	512.00
Trial: 1 / FS: 1280 / Iter: 1	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	502	530	515.00
Trial: 1 / FS: 1280 / Iter: 2	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	497	530	512.00
Trial: 1 / FS: 1280 / Iter: 2	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	502	530	515.00
Trial: 1 / FS: 1280 / Iter: 3	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	497	570	512.00
Trial: 1 / FS: 1280 / Iter: 3	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	502	530	515.00
Trial: 1 / FS: 1280 / Iter: 4	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	497	530	512.00
Trial: 1 / FS: 1280 / Iter: 4	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	502	530	515.00
Trial: 1 / FS: 1280 / Iter: 5	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	497	572	512.00
Trial: 1 / FS: 1280 / Iter: 5	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	502	557	515.00
Trial: 1 / FS: 1280 / Iter: 6	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	497	530	512.00
Trial: 1 / FS: 1280 / Iter: 6	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	502	530	515.00
Trial: 1 / FS: 1280 / Iter: 7	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	497	577	513.00

Trial: 1 / FS: 1280 / Iter: 7	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	502	567	516.00
Trial: 1 / FS: 1280 / Iter: 8	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	502	535	514.00
Trial: 1 / FS: 1280 / Iter: 8	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	502	532	516.00
Trial: 1 / FS: 1280 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	512	595	524.00
Trial: 1 / FS: 1280 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	517	595	525.00
Trial: 1 / FS: 1518 / Iter: 1	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	427	452	441.00
Trial: 1 / FS: 1518 / Iter: 1	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	427	457	443.00
Trial: 1 / FS: 1518 / Iter: 2	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	427	452	441.00
Trial: 1 / FS: 1518 / Iter: 2	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	427	460	443.00
Trial: 1 / FS: 1518 / Iter: 3	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	420	475	441.00
Trial: 1 / FS: 1518 / Iter: 3	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	422	477	443.00
Trial: 1 / FS: 1518 / Iter: 4	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	417	497	442.00
Trial: 1 / FS: 1518 / Iter: 4	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	422	502	445.00
Trial: 1 / FS: 1518 / Iter: 5	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	427	485	441.00
Trial: 1 / FS: 1518 / Iter: 5	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	427	477	443.00
Trial: 1 / FS: 1518 / Iter: 6	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	427	452	441.00
Trial: 1 / FS: 1518 / Iter: 6	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	427	460	443.00
Trial: 1 / FS: 1518 / Iter: 7	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	427	497	441.00
Trial: 1 / FS: 1518 / Iter: 7	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	430	507	444.00
Trial: 1 / FS: 1518 / Iter: 8	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	430	455	442.00
Trial: 1 / FS: 1518 / Iter: 8	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	430	460	444.00



Trial: 1 / FS: 1518 / Iter: 9	Ethernet - 001	Ethernet - 002	N8550-48B8C-Endpoint Set-1 - Flow Group 0001	440	520	449.00
Trial: 1 / FS: 1518 / Iter: 9	Ethernet - 002	Ethernet - 001	N8550-48B8C-Endpoint Set-1 - Flow Group 0002	442	520	453.00

Theoretical maximum Frame Rates (frames/second) for different frame sizes (bytes)

Speed	64	128	256	512	1024	1280	1518
10 Mbps	14881	8446	4529	2350	1198	962	813
100 Mbps	148810	84460	45290	23497	11973	9616	8128
1000 Mbps	1488096	844595	452899	234963	119732	96154	81275
10 Gbps	14880952	8445946	4528986	2349625	1197318	961539	812744
25 Gbps	37202380	21114864	11322463	5874060	2993295	2403846	2031859
40 Gbps	59523809	33783783	18115942	9398496	4789272	3846153	3250975
100 Gbps	148809523	84459459	45289855	23496240	11973180	9615384	8127438
155 Mbps (Oc - 3)	288000	145116	72840	36491	18263	14614	12324
622 Mbps (Oc - 12)	1152000	580465	291362	145965	73054	58454	49296
2488 Mbps (Oc - 48)	4608000	2321860	1165447	583860	292215	233817	197182
9952 Mbps (Oc - 192)	18432000	9287442	4661790	2335439	1168859	935270	788730