



IxNetwork Report

Test: RFC2544 - Throughput/Latency

Test Date: 04/28/2021 09:48:39

www.ixiacom.com
www.ixiacom.com/support

Table of Contents

1.	Cover	1
2.	Info	3
3.	Port Map	4
4.	Aggregate Graphs	5
5.	IterationCharts	13
6.	Aggregated Results	19
7.	Per Flow Results	20
8.	Iteration Data	22
9.	Theoretical Max Rates	38

RFC2544 - Throughput/Latency - Info**Test Information****Product Information**

Product Label : S5800-48MBQ
Product Version :
Serial Number :
Comments :

Test Settings

Date Executed : 04/28/2021
Time Executed : 09:48:39
User Name :
Number of Trials Executed : 1
Stream Duration (sec) : 20

Output Parameters


Number of Trials Passed : N/A
Test Duration : 00:35:59

RFC2544 - Throughput/Latency - Port Map Information


Port Map :	Tx Port	Tx Speed (Mbps)	Rx Port	Rx Speed (Mbps)
	10.32.133.101:3:11	1000	10.32.133.101:3:12	1000
	10.32.133.101:3:12	1000	10.32.133.101:3:11	1000

RFC2544 - Throughput/Latency - Aggregated Graph

Total Frames Transmitted and Received




RFC2544 - Throughput/Latency - Aggregated Graph



RFC2544 - Throughput/Latency - Aggregated Graph


Aggregated Frame Loss



Trial - Framesize - Iteration


RFC2544 - Throughput/Latency - Aggregated Graph

Aggregated Frame Loss per Frame Size




RFC2544 - Throughput/Latency - Aggregated Graph

Aggregated Frame Loss per Line Rate




RFC2544 - Throughput/Latency - Per Flow Graph





RFC2544 - Throughput/Latency - Aggregated Graph

Aggregated Latency



RFC2544 - Throughput/Latency - Per Flow Graph


Tx / Rx Frame Count




Trial



RFC2544 - Throughput/Latency - Iteration Graph

Aggregated Frame Loss for Trial 1 and Framesize 64




Aggregated Frame Loss for Trial 1 and Framesize 128





Aggregated Frame Loss for Trial 1 and Framesize 256**Aggregated Frame Loss for Trial 1 and Framesize 512**

Aggregated Frame Loss for Trial 1 and Framesize 1024




Aggregated Frame Loss for Trial 1 and Framesize 1280




Aggregated Frame Loss for Trial 1 and Framesize 1518

RFC2544 - Throughput/Latency - Iteration Graph

Tx / Rx Frames per Frame Size



RFC2544 - Throughput/Latency - Iteration Graph



RFC2544 - Throughput/Latency - Aggregated Results

Trial / Framesize / Iteration	Agg L2 Throughput				Agg L1 Throughput		Throughput (frames)		Agg Latency			
	Agg Tx Rate %	Agg Rx Rate			Tx Rate Mbps	Rx Rate Mbps			Min (ns)	Max (ns)	Average (ns)	
		%	FPS	Mbps								
Trial: 1 / FS: 64 / Iter: 9	100.00	100	2976190.5	1523.810			Tx : 59523810.000 Rx : 59523810.000 Loss : 0 Loss% : 0.00	3607	3802	3725.500		
Trial: 1 / FS: 128 / Iter: 9	100.00	100	1689189.2	1729.730			Tx : 33783784.000 Rx : 33783784.000 Loss : 0 Loss% : 0.00	3652	3800	3727.000		
Trial: 1 / FS: 256 / Iter: 9	100.00	100	905797.1	1855.072			Tx : 18115942.000 Rx : 18115942.000 Loss : 0 Loss% : 0.00	3430	3610	3526.500		
Trial: 1 / FS: 512 / Iter: 9	100.00	100	469924.8	1924.812			Tx : 9398496.000 Rx : 9398496.000 Loss : 0 Loss% : 0.00	3412	3637	3533.500		
Trial: 1 / FS: 1024 / Iter: 9	100.00	100	239463.6	1961.686			Tx : 4789272.000 Rx : 4789272.000 Loss : 0 Loss% : 0.00	3445	3625	3533.000		
Trial: 1 / FS: 1280 / Iter: 9	100.00	100	192307.7	1969.231			Tx : 3846154.000 Rx : 3846154.000 Loss : 0 Loss% : 0.00	3445	3640	3533.500		
Trial: 1 / FS: 1518 / Iter: 9	100.00	100	162548.8	1973.992			Tx : 3250976.000 Rx : 3250976.000 Loss : 0 Loss% : 0.00	3445	3657	3546.500		

RFC2544 - Throughput/Latency - Per Flow Statistics - Part 1 of 2

Trial / Framesize / Iteration	Tx Port	Rx Port	Flow Group	Tx Rate %	L2 Throughput			L1 Throughput		Throughput (frames)
					%	FPS	Mbps	Tx Rate Mbps	Rx Rate Mbps	
Trial: 1 / FS: 64 / Iter: 9	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	100.00	100	1488095.2	761.91			Tx : 29761905 Rx : 29761905 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 64 / Iter: 9	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	100.00	100	1488095.2	761.91			Tx : 29761905 Rx : 29761905 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 9	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	100.00	100	844594.6	864.87			Tx : 16891892 Rx : 16891892 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 9	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	100.00	100	844594.6	864.87			Tx : 16891892 Rx : 16891892 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 9	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	100.00	100	452898.6	927.54			Tx : 9057971 Rx : 9057971 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 9	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	100.00	100	452898.5	927.54			Tx : 9057971 Rx : 9057971 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 9	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	100.00	100	234962.4	962.41			Tx : 4699248 Rx : 4699248 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 9	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	100.00	100	234962.4	962.41			Tx : 4699248 Rx : 4699248 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 9	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	100.00	100	119731.8	980.84			Tx : 2394636 Rx : 2394636 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 9	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	100.00	100	119731.8	980.84			Tx : 2394636 Rx : 2394636 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 9	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	100.00	100	96153.8	984.62			Tx : 1923077 Rx : 1923077 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 9	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	100.00	100	96153.8	984.62			Tx : 1923077 Rx : 1923077 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 9	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	100.00	100	81274.4	987.00			Tx : 1625488 Rx : 1625488 Loss : 0 Loss% : 0.000

Trial: 1 / FS: 1518 / Iter: 9	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	100.00	100	81274.4	987.00	Tx : 1625488
								Rx : 1625488
								Loss : 0
								Loss% : 0.000

RFC2544 - Throughput/Latency - Per Flow Statistics - Part 2 of 2

Trial / Framesize / Iteration	Tx Port	Rx Port	Flow Group	Min Latency (ns)	Max Latency (ns)	Avg Latency (ns)
Trial: 1 / FS: 64 / Iter: 9	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3637	3782	3721
Trial: 1 / FS: 64 / Iter: 9	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3607	3802	3730
Trial: 1 / FS: 128 / Iter: 9	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3652	3797	3722
Trial: 1 / FS: 128 / Iter: 9	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3655	3800	3732
Trial: 1 / FS: 256 / Iter: 9	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3430	3592	3515
Trial: 1 / FS: 256 / Iter: 9	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3462	3610	3538
Trial: 1 / FS: 512 / Iter: 9	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3412	3605	3531
Trial: 1 / FS: 512 / Iter: 9	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3462	3637	3536
Trial: 1 / FS: 1024 / Iter: 9	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3445	3590	3531
Trial: 1 / FS: 1024 / Iter: 9	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3447	3625	3535
Trial: 1 / FS: 1280 / Iter: 9	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3445	3590	3530
Trial: 1 / FS: 1280 / Iter: 9	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3462	3640	3537
Trial: 1 / FS: 1518 / Iter: 9	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3445	3622	3540
Trial: 1 / FS: 1518 / Iter: 9	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3477	3657	3553

RFC2544 - Throughput/Latency - Iteration Statistics - Part 1 of 2

Trial / Framesize / Iteration	Tx Port	Rx Port	Flow Group	L2 Throughput				L1 Throughput		Throughput (frames)	
				Tx Rate %	%	FPS	Mbps	Tx Rate Mbps	Rx Rate Mbps		
Trial: 1 / FS: 64 / Iter: 1	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	10.00	10.00	148809.5	76.19			Tx : 2976190 Rx : 2976190 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 1	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	10.00	10.00	148809.5	76.19			Tx : 2976190 Rx : 2976190 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 2	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	55.00	55.00	818452.5	419.05			Tx : 16369048 Rx : 16369048 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 2	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	55.00	55.00	818452.5	419.05			Tx : 16369048 Rx : 16369048 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 3	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	77.50	77.50	1153274.7	590.48			Tx : 23065476 Rx : 23065476 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 3	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	77.50	77.50	1153274.7	590.48			Tx : 23065476 Rx : 23065476 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 4	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	88.75	88.75	1320685.0	676.19			Tx : 26413690 Rx : 26413690 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 4	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	88.75	88.75	1320685.0	676.19			Tx : 26413690 Rx : 26413690 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 5	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	94.38	94.38	1404391.1	719.05			Tx : 28087798 Rx : 28087798 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 5	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	94.38	94.38	1404391.1	719.05			Tx : 28087798 Rx : 28087798 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 6	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	97.19	97.19	1446242.7	740.48			Tx : 28924851 Rx : 28924851 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 6	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	97.19	97.19	1446242.7	740.48			Tx : 28924851 Rx : 28924851 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 7	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	98.59	98.59	1467169.8	751.19			Tx : 29343378 Rx : 29343378 Loss : 0 Loss% : 0.000	

Trial: 1 / FS: 64 / Iter: 7	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	98.59	98.59	1467169.8	751.19	Tx : 29343378 Rx : 29343378 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 64 / Iter: 8	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	99.30	99.30	1477633.5	756.55	Tx : 29552641 Rx : 29552641 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 64 / Iter: 8	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	99.30	99.30	1477633.5	756.55	Tx : 29552641 Rx : 29552641 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 64 / Iter: 9	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	100.00	100.00	1488095.2	761.91	Tx : 29761905 Rx : 29761905 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 64 / Iter: 9	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	100.00	100.00	1488095.2	761.91	Tx : 29761905 Rx : 29761905 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 1	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	10.00	10.00	84459.5	86.49	Tx : 1689189 Rx : 1689189 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 1	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	10.00	10.00	84459.5	86.49	Tx : 1689189 Rx : 1689189 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 2	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	55.00	55.00	464527.2	475.68	Tx : 9290541 Rx : 9290541 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 2	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	55.00	55.00	464527.2	475.68	Tx : 9290541 Rx : 9290541 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 3	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	77.50	77.50	654561.0	670.27	Tx : 13091216 Rx : 13091216 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 3	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	77.50	77.50	654561.0	670.27	Tx : 13091216 Rx : 13091216 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 4	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	88.75	88.75	749577.8	767.57	Tx : 14991554 Rx : 14991554 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 4	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	88.75	88.75	749577.8	767.57	Tx : 14991554 Rx : 14991554 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 5	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	94.38	94.38	797086.2	816.22	Tx : 15941723 Rx : 15941723 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 5	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	94.38	94.38	797086.2	816.22	Tx : 15941723 Rx : 15941723 Loss : 0 Loss% : 0.000

Trial: 1 / FS: 128 / Iter: 6	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	97.19	97.19	820840.6	840.54	Tx : 16416807 Rx : 16416807 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 6	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	97.19	97.19	820840.6	840.54	Tx : 16416807 Rx : 16416807 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 7	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	98.59	98.59	832717.5	852.70	Tx : 16654350 Rx : 16654350 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 7	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	98.59	98.59	832717.5	852.70	Tx : 16654350 Rx : 16654350 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 8	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	99.30	99.30	838656.3	858.78	Tx : 16773121 Rx : 16773121 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 8	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	99.30	99.30	838656.3	858.78	Tx : 16773121 Rx : 16773121 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 9	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	100.00	100.00	844594.6	864.87	Tx : 16891892 Rx : 16891892 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 9	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	100.00	100.00	844594.6	864.87	Tx : 16891892 Rx : 16891892 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 1	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	10.00	10.00	45289.9	92.75	Tx : 905797 Rx : 905797 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 1	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	10.00	10.00	45289.9	92.75	Tx : 905797 Rx : 905797 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 2	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	55.00	55.00	249094.2	510.15	Tx : 4981884 Rx : 4981884 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 2	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	55.00	55.00	249094.2	510.15	Tx : 4981884 Rx : 4981884 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 3	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	77.50	77.50	350996.4	718.84	Tx : 7019928 Rx : 7019928 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 3	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	77.50	77.50	350996.4	718.84	Tx : 7019928 Rx : 7019928 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 4	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	88.75	88.75	401947.6	823.19	Tx : 8038949 Rx : 8038949 Loss : 0 Loss% : 0.000

Trial: 1 / FS: 256 / Iter: 4	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	88.75	88.75	401947.6	823.19	Tx : 8038949 Rx : 8038949 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 5	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	94.38	94.38	427423.1	875.36	Tx : 8548460 Rx : 8548460 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 5	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	94.38	94.38	427423.1	875.36	Tx : 8548460 Rx : 8548460 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 6	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	97.19	97.19	440160.8	901.45	Tx : 8803216 Rx : 8803216 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 6	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	97.19	97.19	440160.8	901.45	Tx : 8803216 Rx : 8803216 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 7	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	98.59	98.59	446529.8	914.49	Tx : 8930593 Rx : 8930593 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 7	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	98.59	98.59	446529.8	914.49	Tx : 8930593 Rx : 8930593 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 8	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	99.30	99.30	449714.2	921.02	Tx : 8994282 Rx : 8994282 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 8	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	99.30	99.30	449714.2	921.02	Tx : 8994282 Rx : 8994282 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 9	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	100.00	100.00	452898.6	927.54	Tx : 9057971 Rx : 9057971 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 9	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	100.00	100.00	452898.5	927.54	Tx : 9057971 Rx : 9057971 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 1	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	10.00	10.00	23496.2	96.24	Tx : 469925 Rx : 469925 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 1	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	10.00	10.00	23496.2	96.24	Tx : 469925 Rx : 469925 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 2	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	55.00	55.00	129229.3	529.32	Tx : 2584586 Rx : 2584586 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 2	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	55.00	55.00	129229.3	529.32	Tx : 2584586 Rx : 2584586 Loss : 0 Loss% : 0.000

Trial: 1 / FS: 512 / Iter: 3	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	77.50	77.50	182095.9	745.87	Tx : 3641917 Rx : 3641917 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 3	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	77.50	77.50	182095.9	745.87	Tx : 3641917 Rx : 3641917 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 4	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	88.75	88.75	208529.1	854.14	Tx : 4170583 Rx : 4170583 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 4	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	88.75	88.75	208529.1	854.14	Tx : 4170583 Rx : 4170583 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 5	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	94.38	94.38	221745.8	908.27	Tx : 4434915 Rx : 4434915 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 5	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	94.38	94.38	221745.8	908.27	Tx : 4434915 Rx : 4434915 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 6	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	97.19	97.19	228354.1	935.34	Tx : 4567082 Rx : 4567082 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 6	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	97.19	97.19	228354.1	935.34	Tx : 4567082 Rx : 4567082 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 7	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	98.59	98.59	231658.3	948.87	Tx : 4633165 Rx : 4633165 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 7	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	98.59	98.59	231658.3	948.87	Tx : 4633165 Rx : 4633165 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 8	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	99.30	99.30	233310.3	955.64	Tx : 4666207 Rx : 4666207 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 8	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	99.30	99.30	233310.3	955.64	Tx : 4666207 Rx : 4666207 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 9	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	100.00	100.00	234962.4	962.41	Tx : 4699248 Rx : 4699248 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 9	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	100.00	100.00	234962.4	962.41	Tx : 4699248 Rx : 4699248 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 1	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	10.00	10.00	11973.2	98.08	Tx : 239464 Rx : 239464 Loss : 0 Loss% : 0.000

Trial: 1 / FS: 1024 / Iter: 1	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	10.00	10.00	11973.2	98.08	Tx : 239464 Rx : 239464 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 2	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	55.00	55.00	65852.5	539.46	Tx : 1317050 Rx : 1317050 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 2	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	55.00	55.00	65852.5	539.46	Tx : 1317050 Rx : 1317050 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 3	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	77.50	77.50	92792.2	760.15	Tx : 1855843 Rx : 1855843 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 3	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	77.50	77.50	92792.2	760.15	Tx : 1855843 Rx : 1855843 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 4	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	88.75	88.75	106262.0	870.50	Tx : 2125239 Rx : 2125239 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 4	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	88.75	88.75	106262.0	870.50	Tx : 2125239 Rx : 2125239 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 5	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	94.38	94.38	112996.9	925.67	Tx : 2259938 Rx : 2259938 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 5	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	94.38	94.38	112996.9	925.67	Tx : 2259938 Rx : 2259938 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 6	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	97.19	97.19	116364.3	953.26	Tx : 2327287 Rx : 2327287 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 6	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	97.19	97.19	116364.3	953.26	Tx : 2327287 Rx : 2327287 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 7	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	98.59	98.59	118048.1	967.05	Tx : 2360961 Rx : 2360961 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 7	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	98.59	98.59	118048.1	967.05	Tx : 2360961 Rx : 2360961 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 8	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	99.30	99.30	118889.9	973.95	Tx : 2377799 Rx : 2377799 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 8	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	99.30	99.30	118889.9	973.95	Tx : 2377799 Rx : 2377799 Loss : 0 Loss% : 0.000

Trial: 1 / FS: 1024 / Iter: 9	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	100.00	100.00	119731.8	980.84	Tx : 2394636 Rx : 2394636 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 9	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	100.00	100.00	119731.8	980.84	Tx : 2394636 Rx : 2394636 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 1	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	10.00	10.00	9615.4	98.46	Tx : 192308 Rx : 192308 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 1	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	10.00	10.00	9615.4	98.46	Tx : 192308 Rx : 192308 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 2	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	55.00	55.00	52884.6	541.54	Tx : 1057692 Rx : 1057692 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 2	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	55.00	55.00	52884.6	541.54	Tx : 1057692 Rx : 1057692 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 3	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	77.50	77.50	74519.2	763.08	Tx : 1490385 Rx : 1490385 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 3	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	77.50	77.50	74519.2	763.08	Tx : 1490385 Rx : 1490385 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 4	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	88.75	88.75	85336.5	873.85	Tx : 1706731 Rx : 1706731 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 4	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	88.75	88.75	85336.5	873.85	Tx : 1706731 Rx : 1706731 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 5	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	94.38	94.38	90745.2	929.23	Tx : 1814904 Rx : 1814904 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 5	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	94.38	94.38	90745.2	929.23	Tx : 1814904 Rx : 1814904 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 6	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	97.19	97.19	93449.5	956.92	Tx : 1868990 Rx : 1868990 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 6	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	97.19	97.19	93449.5	956.92	Tx : 1868990 Rx : 1868990 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 7	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	98.59	98.59	94801.7	970.77	Tx : 1896034 Rx : 1896034 Loss : 0 Loss% : 0.000

Trial: 1 / FS: 1280 / Iter: 7	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	98.59	98.59	94801.7	970.77	Tx : Rx : Loss : Loss% :	1896034 1896034 0 0.000
Trial: 1 / FS: 1280 / Iter: 8	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	99.30	99.30	95477.8	977.69	Tx : Rx : Loss : Loss% :	1909555 1909555 0 0.000
Trial: 1 / FS: 1280 / Iter: 8	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	99.30	99.30	95477.8	977.69	Tx : Rx : Loss : Loss% :	1909555 1909555 0 0.000
Trial: 1 / FS: 1280 / Iter: 9	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	100.00	100.00	96153.8	984.62	Tx : Rx : Loss : Loss% :	1923077 1923077 0 0.000
Trial: 1 / FS: 1280 / Iter: 9	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	100.00	100.00	96153.8	984.62	Tx : Rx : Loss : Loss% :	1923077 1923077 0 0.000
Trial: 1 / FS: 1518 / Iter: 1	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	10.00	10.00	8127.4	98.70	Tx : Rx : Loss : Loss% :	162549 162549 0 0.000
Trial: 1 / FS: 1518 / Iter: 1	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	10.00	10.00	8127.4	98.70	Tx : Rx : Loss : Loss% :	162549 162549 0 0.000
Trial: 1 / FS: 1518 / Iter: 2	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	55.00	55.00	44700.9	542.85	Tx : Rx : Loss : Loss% :	894018 894018 0 0.000
Trial: 1 / FS: 1518 / Iter: 2	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	55.00	55.00	44700.9	542.85	Tx : Rx : Loss : Loss% :	894018 894018 0 0.000
Trial: 1 / FS: 1518 / Iter: 3	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	77.50	77.50	62987.6	764.92	Tx : Rx : Loss : Loss% :	1259753 1259753 0 0.000
Trial: 1 / FS: 1518 / Iter: 3	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	77.50	77.50	62987.6	764.92	Tx : Rx : Loss : Loss% :	1259753 1259753 0 0.000
Trial: 1 / FS: 1518 / Iter: 4	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	88.75	88.75	72131.0	875.96	Tx : Rx : Loss : Loss% :	1442620 1442620 0 0.000
Trial: 1 / FS: 1518 / Iter: 4	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	88.75	88.75	72131.0	875.96	Tx : Rx : Loss : Loss% :	1442620 1442620 0 0.000
Trial: 1 / FS: 1518 / Iter: 5	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	94.38	94.38	76702.7	931.48	Tx : Rx : Loss : Loss% :	1534054 1534054 0 0.000
Trial: 1 / FS: 1518 / Iter: 5	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	94.38	94.38	76702.7	931.48	Tx : Rx : Loss : Loss% :	1534054 1534054 0 0.000

Trial: 1 / FS: 1518 / Iter: 6	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	97.19	97.19	78988.5	959.24	Tx : 1579771	
								Rx : 1579771	
								Loss : 0	
								Loss% : 0.000	
Trial: 1 / FS: 1518 / Iter: 6	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	97.19	97.19	78988.5	959.24	Tx : 1579771	
								Rx : 1579771	
								Loss : 0	
								Loss% : 0.000	
Trial: 1 / FS: 1518 / Iter: 7	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	98.59	98.59	80131.5	973.12	Tx : 1602629	
								Rx : 1602629	
								Loss : 0	
								Loss% : 0.000	
Trial: 1 / FS: 1518 / Iter: 7	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	98.59	98.59	80131.5	973.12	Tx : 1602629	
								Rx : 1602629	
								Loss : 0	
								Loss% : 0.000	
Trial: 1 / FS: 1518 / Iter: 8	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	99.30	99.30	80702.9	980.06	Tx : 1614058	
								Rx : 1614058	
								Loss : 0	
								Loss% : 0.000	
Trial: 1 / FS: 1518 / Iter: 8	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	99.30	99.30	80702.9	980.06	Tx : 1614058	
								Rx : 1614058	
								Loss : 0	
								Loss% : 0.000	
Trial: 1 / FS: 1518 / Iter: 9	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	100.00	100.00	81274.4	987.00	Tx : 1625488	
								Rx : 1625488	
								Loss : 0	
								Loss% : 0.000	
Trial: 1 / FS: 1518 / Iter: 9	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	100.00	100.00	81274.4	987.00	Tx : 1625488	
								Rx : 1625488	
								Loss : 0	
								Loss% : 0.000	

RFC2544 - Throughput/Latency - Iteration Statistics - Part 2 of 2

Trial / Framesize / Iteration	Tx Port	Rx Port	Flow Group	Min Latency (ns)	Max Latency (ns)	Avg Latency (ns)
Trial: 1 / FS: 64 / Iter: 1	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3557	3750	3657.00
Trial: 1 / FS: 64 / Iter: 1	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3575	3750	3649.00
Trial: 1 / FS: 64 / Iter: 2	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3572	3750	3653.00
Trial: 1 / FS: 64 / Iter: 2	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3575	3752	3653.00
Trial: 1 / FS: 64 / Iter: 3	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3572	3750	3654.00
Trial: 1 / FS: 64 / Iter: 3	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3575	3752	3654.00
Trial: 1 / FS: 64 / Iter: 4	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3557	3750	3653.00
Trial: 1 / FS: 64 / Iter: 4	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3557	3752	3657.00
Trial: 1 / FS: 64 / Iter: 5	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3557	3750	3654.00
Trial: 1 / FS: 64 / Iter: 5	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3557	3752	3659.00
Trial: 1 / FS: 64 / Iter: 6	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3572	3750	3660.00
Trial: 1 / FS: 64 / Iter: 6	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3557	3752	3665.00
Trial: 1 / FS: 64 / Iter: 7	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3572	3750	3666.00
Trial: 1 / FS: 64 / Iter: 7	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3575	3752	3672.00
Trial: 1 / FS: 64 / Iter: 8	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3572	3750	3671.00
Trial: 1 / FS: 64 / Iter: 8	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3590	3752	3678.00
Trial: 1 / FS: 64 / Iter: 9	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3637	3782	3721.00
Trial: 1 / FS: 64 / Iter: 9	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3607	3802	3730.00
Trial: 1 / FS: 128 / Iter: 1	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3590	3750	3658.00

Trial: 1 / FS: 128 / Iter: 1	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3560	3737	3653.00
Trial: 1 / FS: 128 / Iter: 2	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3572	6005	3653.00
Trial: 1 / FS: 128 / Iter: 2	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3557	6057	3656.00
Trial: 1 / FS: 128 / Iter: 3	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3572	3750	3653.00
Trial: 1 / FS: 128 / Iter: 3	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3557	3737	3656.00
Trial: 1 / FS: 128 / Iter: 4	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3572	3750	3653.00
Trial: 1 / FS: 128 / Iter: 4	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3557	3737	3656.00
Trial: 1 / FS: 128 / Iter: 5	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3555	3750	3653.00
Trial: 1 / FS: 128 / Iter: 5	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3557	3752	3657.00
Trial: 1 / FS: 128 / Iter: 6	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3555	3750	3653.00
Trial: 1 / FS: 128 / Iter: 6	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3557	3752	3659.00
Trial: 1 / FS: 128 / Iter: 7	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3555	3750	3659.00
Trial: 1 / FS: 128 / Iter: 7	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3557	3752	3666.00
Trial: 1 / FS: 128 / Iter: 8	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3555	3750	3665.00
Trial: 1 / FS: 128 / Iter: 8	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3575	3752	3673.00
Trial: 1 / FS: 128 / Iter: 9	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3652	3797	3722.00
Trial: 1 / FS: 128 / Iter: 9	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3655	3800	3732.00
Trial: 1 / FS: 256 / Iter: 1	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3400	3527	3455.00
Trial: 1 / FS: 256 / Iter: 1	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3385	3545	3471.00
Trial: 1 / FS: 256 / Iter: 2	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3382	3560	3460.00
Trial: 1 / FS: 256 / Iter: 2	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3367	3547	3467.00

Trial: 1 / FS: 256 / Iter: 3	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3382	3557	3461.00
Trial: 1 / FS: 256 / Iter: 3	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3367	3547	3467.00
Trial: 1 / FS: 256 / Iter: 4	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3382	3560	3461.00
Trial: 1 / FS: 256 / Iter: 4	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3367	3547	3467.00
Trial: 1 / FS: 256 / Iter: 5	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3382	6292	3461.00
Trial: 1 / FS: 256 / Iter: 5	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3367	6312	3467.00
Trial: 1 / FS: 256 / Iter: 6	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3382	6375	3460.00
Trial: 1 / FS: 256 / Iter: 6	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3367	6377	3467.00
Trial: 1 / FS: 256 / Iter: 7	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3382	3560	3461.00
Trial: 1 / FS: 256 / Iter: 7	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3367	3547	3468.00
Trial: 1 / FS: 256 / Iter: 8	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3382	3575	3467.00
Trial: 1 / FS: 256 / Iter: 8	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3382	3547	3474.00
Trial: 1 / FS: 256 / Iter: 9	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3430	3592	3515.00
Trial: 1 / FS: 256 / Iter: 9	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3462	3610	3538.00
Trial: 1 / FS: 512 / Iter: 1	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3397	3557	3469.00
Trial: 1 / FS: 512 / Iter: 1	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3400	3545	3467.00
Trial: 1 / FS: 512 / Iter: 2	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3380	3557	3464.00
Trial: 1 / FS: 512 / Iter: 2	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3397	3560	3469.00
Trial: 1 / FS: 512 / Iter: 3	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3380	3557	3464.00
Trial: 1 / FS: 512 / Iter: 3	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3397	3575	3469.00
Trial: 1 / FS: 512 / Iter: 4	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3380	5910	3464.00

Trial: 1 / FS: 512 / Iter: 4	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3397	5895	3469.00
Trial: 1 / FS: 512 / Iter: 5	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3380	6162	3464.00
Trial: 1 / FS: 512 / Iter: 5	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3397	6167	3470.00
Trial: 1 / FS: 512 / Iter: 6	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3380	3557	3464.00
Trial: 1 / FS: 512 / Iter: 6	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3397	3577	3469.00
Trial: 1 / FS: 512 / Iter: 7	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3380	3572	3464.00
Trial: 1 / FS: 512 / Iter: 7	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3397	3577	3470.00
Trial: 1 / FS: 512 / Iter: 8	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3380	3557	3465.00
Trial: 1 / FS: 512 / Iter: 8	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3397	3575	3471.00
Trial: 1 / FS: 512 / Iter: 9	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3412	3605	3531.00
Trial: 1 / FS: 512 / Iter: 9	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3462	3637	3536.00
Trial: 1 / FS: 1024 / Iter: 1	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3397	3557	3470.00
Trial: 1 / FS: 1024 / Iter: 1	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3400	3560	3468.00
Trial: 1 / FS: 1024 / Iter: 2	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3380	3557	3466.00
Trial: 1 / FS: 1024 / Iter: 2	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3397	3577	3471.00
Trial: 1 / FS: 1024 / Iter: 3	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3380	3557	3466.00
Trial: 1 / FS: 1024 / Iter: 3	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3397	3577	3471.00
Trial: 1 / FS: 1024 / Iter: 4	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3380	3557	3466.00
Trial: 1 / FS: 1024 / Iter: 4	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3397	3577	3471.00
Trial: 1 / FS: 1024 / Iter: 5	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3380	3557	3466.00
Trial: 1 / FS: 1024 / Iter: 5	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3397	3577	3471.00

Trial: 1 / FS: 1024 / Iter: 6	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3380	3557	3466.00
Trial: 1 / FS: 1024 / Iter: 6	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3397	3577	3471.00
Trial: 1 / FS: 1024 / Iter: 7	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3380	3557	3466.00
Trial: 1 / FS: 1024 / Iter: 7	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3397	3577	3471.00
Trial: 1 / FS: 1024 / Iter: 8	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3380	3557	3466.00
Trial: 1 / FS: 1024 / Iter: 8	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3397	3577	3472.00
Trial: 1 / FS: 1024 / Iter: 9	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3445	3590	3531.00
Trial: 1 / FS: 1024 / Iter: 9	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3447	3625	3535.00
Trial: 1 / FS: 1280 / Iter: 1	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3397	3557	3471.00
Trial: 1 / FS: 1280 / Iter: 1	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3400	3542	3468.00
Trial: 1 / FS: 1280 / Iter: 2	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3380	3560	3467.00
Trial: 1 / FS: 1280 / Iter: 2	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3400	3577	3472.00
Trial: 1 / FS: 1280 / Iter: 3	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3380	3560	3467.00
Trial: 1 / FS: 1280 / Iter: 3	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3400	3577	3472.00
Trial: 1 / FS: 1280 / Iter: 4	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3380	3557	3467.00
Trial: 1 / FS: 1280 / Iter: 4	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3400	3577	3472.00
Trial: 1 / FS: 1280 / Iter: 5	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3380	3560	3467.00
Trial: 1 / FS: 1280 / Iter: 5	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3400	3577	3472.00
Trial: 1 / FS: 1280 / Iter: 6	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3380	3560	3467.00
Trial: 1 / FS: 1280 / Iter: 6	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3400	3577	3472.00
Trial: 1 / FS: 1280 / Iter: 7	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3380	3557	3467.00

Trial: 1 / FS: 1280 / Iter: 7	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3400	3577	3472.00
Trial: 1 / FS: 1280 / Iter: 8	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3380	3557	3467.00
Trial: 1 / FS: 1280 / Iter: 8	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3400	3577	3472.00
Trial: 1 / FS: 1280 / Iter: 9	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3445	3590	3530.00
Trial: 1 / FS: 1280 / Iter: 9	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3462	3640	3537.00
Trial: 1 / FS: 1518 / Iter: 1	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3382	3557	3482.00
Trial: 1 / FS: 1518 / Iter: 1	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3415	3592	3486.00
Trial: 1 / FS: 1518 / Iter: 2	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3395	3575	3481.00
Trial: 1 / FS: 1518 / Iter: 2	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3415	3595	3490.00
Trial: 1 / FS: 1518 / Iter: 3	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3382	3575	3481.00
Trial: 1 / FS: 1518 / Iter: 3	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3415	3595	3490.00
Trial: 1 / FS: 1518 / Iter: 4	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3382	3575	3482.00
Trial: 1 / FS: 1518 / Iter: 4	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3415	3595	3491.00
Trial: 1 / FS: 1518 / Iter: 5	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3380	3572	3482.00
Trial: 1 / FS: 1518 / Iter: 5	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3415	3595	3491.00
Trial: 1 / FS: 1518 / Iter: 6	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3380	3572	3481.00
Trial: 1 / FS: 1518 / Iter: 6	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3415	3595	3490.00
Trial: 1 / FS: 1518 / Iter: 7	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3382	6277	3481.00
Trial: 1 / FS: 1518 / Iter: 7	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3415	6245	3490.00
Trial: 1 / FS: 1518 / Iter: 8	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3382	6340	3482.00
Trial: 1 / FS: 1518 / Iter: 8	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3415	6392	3491.00



Trial: 1 / FS: 1518 / Iter: 9	Ethernet - 001	Ethernet - 002	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0001	3445	3622	3540.00
Trial: 1 / FS: 1518 / Iter: 9	Ethernet - 002	Ethernet - 001	QT-Rfc2544Tput-Endpoint Set-1 - Flow Group 0002	3477	3657	3553.00

Theoretical maximum Frame Rates (frames/second) for different frame sizes (bytes)

Speed	64	128	256	512	1024	1280	1518
10 Mbps	14881	8446	4529	2350	1198	962	813
100 Mbps	148810	84460	45290	23497	11973	9616	8128
1000 Mbps	1488096	844595	452899	234963	119732	96154	81275
10 Gbps	14880952	8445946	4528986	2349625	1197318	961539	812744
25 Gbps	37202380	21114864	11322463	5874060	2993295	2403846	2031859
40 Gbps	59523809	33783783	18115942	9398496	4789272	3846153	3250975
100 Gbps	148809523	84459459	45289855	23496240	11973180	9615384	8127438
155 Mbps (Oc - 3)	288000	145116	72840	36491	18263	14614	12324
622 Mbps (Oc - 12)	1152000	580465	291362	145965	73054	58454	49296
2488 Mbps (Oc - 48)	4608000	2321860	1165447	583860	292215	233817	197182
9952 Mbps (Oc - 192)	18432000	9287442	4661790	2335439	1168859	935270	788730