



IxNetwork Report

Test: RFC2544 - Throughput/Latency

Test Date: 10/14/2020 16:35:18

www.ixiacom.com
www.ixiacom.com/support

Table of Contents

1.	Cover	1
2.	Info	3
3.	Port Map	4
4.	Aggregate Graphs	5
5.	IterationCharts	13
6.	Aggregated Results	19
7.	Aggregated Results Per Iteration	20
8.	Per Flow Results	25
9.	Iteration Data	27
10.	Theoretical Max Rates	36

RFC2544 - Throughput/Latency - Info**Test Information****Product Information**

Product Label :	S5900-24S4T2Q
Product Version :	2.2.0D
Serial Number :	CG1908020295N0026
Comments :	

Test Settings

Date Executed :	10/14/2020
Time Executed :	16:35:18
User Name :	FS.COM
Number of Trials Executed :	1
Stream Duration (sec) :	20

Output Parameters


Number of Trials Passed :	N/A
Test Duration :	00:35:23

RFC2544 - Throughput/Latency - Port Map Information


Port Map :	Tx Port	Tx Speed (Mbps)	Rx Port	Rx Speed (Mbps)
	10.32.133.101:3:3	10000	10.32.133.101:3:4	10000


RFC2544 - Throughput/Latency - Aggregated Graph

Total Frames Transmitted and Received



RFC2544 - Throughput/Latency - Aggregated Graph




RFC2544 - Throughput/Latency - Aggregated Graph**Aggregated Frame Loss**

Trial - Framesize - Iteration


RFC2544 - Throughput/Latency - Aggregated Graph

Aggregated Frame Loss per Frame Size




RFC2544 - Throughput/Latency - Aggregated Graph


Aggregated Frame Loss per Line Rate



RFC2544 - Throughput/Latency - Per Flow Graph





RFC2544 - Throughput/Latency - Aggregated Graph



RFC2544 - Throughput/Latency - Per Flow Graph


Tx / Rx Frame Count




Trial



RFC2544 - Throughput/Latency - Iteration Graph



Aggregated Frame Loss for Trial 1 and Framesize 64




Aggregated Frame Loss for Trial 1 and Framesize 128




Aggregated Frame Loss for Trial 1 and Framesize 256**Aggregated Frame Loss for Trial 1 and Framesize 512**

Aggregated Frame Loss for Trial 1 and Framesize 1024**Aggregated Frame Loss for Trial 1 and Framesize 1280**


Aggregated Frame Loss for Trial 1 and Framesize 1518

RFC2544 - Throughput/Latency - Iteration Graph

Tx / Rx Frames per Frame Size



RFC2544 - Throughput/Latency - Iteration Graph



RFC2544 - Throughput/Latency - Aggregated Results

Trial / Framesize / Iteration	Agg L2 Throughput				Agg L1 Throughput		Throughput (frames)		Agg Latency			
	AggTx Rate %	Agg Rx Rate			Tx Rate Mbps	Rx Rate Mbps			Min (ns)	Max (ns)	Average (ns)	
		%	FPS	Mbps								
Trial: 1 / FS: 64 / Iter: 9	100.00	100	14880952.4	7619.048			Tx : Rx : Loss : Loss% :	297619048.000 297619048.000 0 0.00	815	922	850.000	
Trial: 1 / FS: 128 / Iter: 9	100.00	100	8445945.9	8648.649			Tx : Rx : Loss : Loss% :	168918919.000 168918919.000 0 0.00	852	987	915.000	
Trial: 1 / FS: 256 / Iter: 9	100.00	100	4528985.5	9275.362			Tx : Rx : Loss : Loss% :	90579710.000 90579710.000 0 0.00	862	987	915.000	
Trial: 1 / FS: 512 / Iter: 9	100.00	100	2349624.1	9624.060			Tx : Rx : Loss : Loss% :	46992481.000 46992481.000 0 0.00	862	987	913.000	
Trial: 1 / FS: 1024 / Iter: 9	100.00	100	1197318.0	9808.429			Tx : Rx : Loss : Loss% :	23946360.000 23946360.000 0 0.00	850	985	909.000	
Trial: 1 / FS: 1280 / Iter: 9	100.00	100	961538.5	9846.154			Tx : Rx : Loss : Loss% :	19230769.000 19230769.000 0 0.00	895	995	913.000	
Trial: 1 / FS: 1518 / Iter: 9	100.00	100	812743.8	9869.961			Tx : Rx : Loss : Loss% :	16254876.000 16254876.000 0 0.00	895	982	909.000	

RFC2544 - Throughput/Latency - Aggregated Results

Trial / Framesize / Iteration	Agg L2 Throughput				Agg L1 Throughput		Throughput (frames)	Agg Latency			
	AggTx Rate %	Agg Rx Rate			Tx Rate Mbps	Rx Rate Mbps		Min (ns)	Max (ns)	Average (ns)	
		%	FPS	Mbps							
Trial: 1 / FS: 64 / Iter: 1	10	10	1488095.2	761.905			Tx : 29761905.000 Rx : 29761905.000 Loss : 0 Loss% : 0.00	757	855	810.000	
Trial: 1 / FS: 64 / Iter: 2	55	55	8184561.9	4190.496			Tx : 163690476.000 Rx : 163690476.000 Loss : 0 Loss% : 0.00	757	912	810.000	
Trial: 1 / FS: 64 / Iter: 3	78	78	11532778.3	5904.782			Tx : 230654762.000 Rx : 230654762.000 Loss : 0 Loss% : 0.00	775	900	815.000	
Trial: 1 / FS: 64 / Iter: 4	89	89	13206904.7	6761.935			Tx : 264136905.000 Rx : 264136905.000 Loss : 0 Loss% : 0.00	790	900	820.000	
Trial: 1 / FS: 64 / Iter: 5	94	94	14044019.2	7190.538			Tx : 280877976.000 Rx : 280877976.000 Loss : 0 Loss% : 0.00	797	912	826.000	
Trial: 1 / FS: 64 / Iter: 6	97	97	14462459.7	7404.779			Tx : 289248512.000 Rx : 289248512.000 Loss : 0 Loss% : 0.00	802	915	830.000	
Trial: 1 / FS: 64 / Iter: 7	99	99	14671832.4	7511.978			Tx : 293433780.000 Rx : 293433780.000 Loss : 0 Loss% : 0.00	810	915	834.000	
Trial: 1 / FS: 64 / Iter: 8	99	99	14776334.8	7565.483			Tx : 295526414.000 Rx : 295526414.000 Loss : 0 Loss% : 0.00	807	912	837.000	
Trial: 1 / FS: 64 / Iter: 9	100	100	14880952.4	7619.048			Tx : 297619048.000 Rx : 297619048.000 Loss : 0 Loss% : 0.00	815	922	850.000	
Trial: 1 / FS: 128 / Iter: 1	10	10	844594.6	864.865			Tx : 16891892.000 Rx : 16891892.000 Loss : 0 Loss% : 0.00	760	857	811.000	
Trial: 1 / FS: 128 / Iter: 2	55	55	4645271.8	4756.758			Tx : 92905405.000 Rx : 92905405.000 Loss : 0 Loss% : 0.00	760	902	811.000	
Trial: 1 / FS: 128 / Iter: 3	78	78	6545640.5	6702.736			Tx : 130912162.000 Rx : 130912162.000 Loss : 0 Loss% : 0.00	762	965	851.000	
Trial: 1 / FS: 128 / Iter: 4	89	89	7495812.9	7675.712			Tx : 149915541.000 Rx : 149915541.000 Loss : 0 Loss% : 0.00	835	967	874.000	

Trial: 1 / FS: 128 / Iter: 5	94	94	7970906.2	8162.208	Tx : Rx : Loss : Loss% :	159417230.000 159417230.000 0 0.00	835	972	875.000
Trial: 1 / FS: 128 / Iter: 6	97	97	8208443.1	8405.446	Tx : Rx : Loss : Loss% :	164168074.000 164168074.000 0 0.00	835	960	878.000
Trial: 1 / FS: 128 / Iter: 7	99	99	8327207.2	8527.060	Tx : Rx : Loss : Loss% :	166543497.000 166543497.000 0 0.00	845	970	885.000
Trial: 1 / FS: 128 / Iter: 8	99	99	8386568.4	8587.846	Tx : Rx : Loss : Loss% :	167731208.000 167731208.000 0 0.00	867	980	896.000
Trial: 1 / FS: 128 / Iter: 9	100	100	8445945.9	8648.649	Tx : Rx : Loss : Loss% :	168918919.000 168918919.000 0 0.00	852	987	915.000
Trial: 1 / FS: 256 / Iter: 1	10	10	452898.6	927.536	Tx : Rx : Loss : Loss% :	9057971.000 9057971.000 0 0.00	822	920	874.000
Trial: 1 / FS: 256 / Iter: 2	55	55	2490946.0	5101.457	Tx : Rx : Loss : Loss% :	49818841.000 49818841.000 0 0.00	822	930	874.000
Trial: 1 / FS: 256 / Iter: 3	78	78	3509965.0	7188.408	Tx : Rx : Loss : Loss% :	70199275.000 70199275.000 0 0.00	822	922	874.000
Trial: 1 / FS: 256 / Iter: 4	89	89	4019481.9	8231.899	Tx : Rx : Loss : Loss% :	80389493.000 80389493.000 0 0.00	830	937	875.000
Trial: 1 / FS: 256 / Iter: 5	94	94	4274232.1	8753.627	Tx : Rx : Loss : Loss% :	85484601.000 85484601.000 0 0.00	835	950	882.000
Trial: 1 / FS: 256 / Iter: 6	97	97	4401620.4	9014.518	Tx : Rx : Loss : Loss% :	88032156.000 88032156.000 0 0.00	850	967	888.000
Trial: 1 / FS: 256 / Iter: 7	99	99	4465298.0	9144.930	Tx : Rx : Loss : Loss% :	89305933.000 89305933.000 0 0.00	862	965	893.000
Trial: 1 / FS: 256 / Iter: 8	99	99	4497145.4	9210.154	Tx : Rx : Loss : Loss% :	89942822.000 89942822.000 0 0.00	862	977	896.000
Trial: 1 / FS: 256 / Iter: 9	100	100	4528985.5	9275.362	Tx : Rx : Loss : Loss% :	90579710.000 90579710.000 0 0.00	862	987	915.000
Trial: 1 / FS: 512 / Iter: 1	10	10	234962.4	962.406	Tx : Rx : Loss : Loss% :	4699248.000 4699248.000 0 0.00	822	920	869.000

Trial: 1 / FS: 512 / Iter: 2	55	55	1292293.6	5293.235	Tx : Rx : Loss : Loss% :	25845865.000 25845865.000 0 0.00	822	920	869.000
Trial: 1 / FS: 512 / Iter: 3	78	78	1820959.8	7458.651	Tx : Rx : Loss : Loss% :	36419173.000 36419173.000 0 0.00	822	920	869.000
Trial: 1 / FS: 512 / Iter: 4	89	89	2085291.7	8541.355	Tx : Rx : Loss : Loss% :	41705827.000 41705827.000 0 0.00	825	942	870.000
Trial: 1 / FS: 512 / Iter: 5	94	94	2217460.1	9082.716	Tx : Rx : Loss : Loss% :	44349154.000 44349154.000 0 0.00	830	967	872.000
Trial: 1 / FS: 512 / Iter: 6	97	97	2283540.8	9353.383	Tx : Rx : Loss : Loss% :	45670818.000 45670818.000 0 0.00	832	962	876.000
Trial: 1 / FS: 512 / Iter: 7	99	99	2316582.8	9488.723	Tx : Rx : Loss : Loss% :	46331649.000 46331649.000 0 0.00	845	965	882.000
Trial: 1 / FS: 512 / Iter: 8	99	99	2333105.5	9556.400	Tx : Rx : Loss : Loss% :	46662065.000 46662065.000 0 0.00	857	972	888.000
Trial: 1 / FS: 512 / Iter: 9	100	100	2349624.1	9624.060	Tx : Rx : Loss : Loss% :	46992481.000 46992481.000 0 0.00	862	987	913.000
Trial: 1 / FS: 1024 / Iter: 1	10	10	119731.8	980.843	Tx : Rx : Loss : Loss% :	2394636.000 2394636.000 0 0.00	822	920	869.000
Trial: 1 / FS: 1024 / Iter: 2	55	55	658525.0	5394.637	Tx : Rx : Loss : Loss% :	13170498.000 13170498.000 0 0.00	822	920	869.000
Trial: 1 / FS: 1024 / Iter: 3	78	78	927921.5	7601.533	Tx : Rx : Loss : Loss% :	18558429.000 18558429.000 0 0.00	822	920	869.000
Trial: 1 / FS: 1024 / Iter: 4	89	89	1062619.9	8704.982	Tx : Rx : Loss : Loss% :	21252395.000 21252395.000 0 0.00	822	920	869.000
Trial: 1 / FS: 1024 / Iter: 5	94	94	1129969.4	9256.710	Tx : Rx : Loss : Loss% :	22599377.000 22599377.000 0 0.00	822	920	869.000
Trial: 1 / FS: 1024 / Iter: 6	97	97	1163643.8	9532.570	Tx : Rx : Loss : Loss% :	23272869.000 23272869.000 0 0.00	822	935	870.000
Trial: 1 / FS: 1024 / Iter: 7	99	99	1180480.8	9670.498	Tx : Rx : Loss : Loss% :	23609614.000 23609614.000 0 0.00	825	970	871.000

Trial: 1 / FS: 1024 / Iter: 8	99	99	1188899.4	9739.464	Tx : Rx : Loss : Loss% :	23777987.000 23777987.000 0 0.00	835	967	877.000
Trial: 1 / FS: 1024 / Iter: 9	100	100	1197318.0	9808.429	Tx : Rx : Loss : Loss% :	23946360.000 23946360.000 0 0.00	850	985	909.000
Trial: 1 / FS: 1280 / Iter: 1	10	10	96153.8	984.615	Tx : Rx : Loss : Loss% :	1923077.000 1923077.000 0 0.00	822	932	874.000
Trial: 1 / FS: 1280 / Iter: 2	55	55	528846.3	5415.386	Tx : Rx : Loss : Loss% :	10576923.000 10576923.000 0 0.00	822	932	874.000
Trial: 1 / FS: 1280 / Iter: 3	78	78	745192.5	7630.771	Tx : Rx : Loss : Loss% :	14903846.000 14903846.000 0 0.00	822	932	874.000
Trial: 1 / FS: 1280 / Iter: 4	89	89	853365.8	8738.465	Tx : Rx : Loss : Loss% :	17067308.000 17067308.000 0 0.00	822	967	874.000
Trial: 1 / FS: 1280 / Iter: 5	94	94	907452.0	9292.308	Tx : Rx : Loss : Loss% :	18149038.000 18149038.000 0 0.00	822	932	874.000
Trial: 1 / FS: 1280 / Iter: 6	97	97	934495.5	9569.234	Tx : Rx : Loss : Loss% :	18689904.000 18689904.000 0 0.00	835	955	877.000
Trial: 1 / FS: 1280 / Iter: 7	99	99	948016.8	9707.692	Tx : Rx : Loss : Loss% :	18960337.000 18960337.000 0 0.00	850	952	882.000
Trial: 1 / FS: 1280 / Iter: 8	99	99	954777.8	9776.925	Tx : Rx : Loss : Loss% :	19095553.000 19095553.000 0 0.00	837	955	887.000
Trial: 1 / FS: 1280 / Iter: 9	100	100	961538.5	9846.154	Tx : Rx : Loss : Loss% :	19230769.000 19230769.000 0 0.00	895	995	913.000
Trial: 1 / FS: 1518 / Iter: 1	10	10	81274.4	986.996	Tx : Rx : Loss : Loss% :	1625488.000 1625488.000 0 0.00	825	922	872.000
Trial: 1 / FS: 1518 / Iter: 2	55	55	447009.2	5428.479	Tx : Rx : Loss : Loss% :	8940182.000 8940182.000 0 0.00	825	962	872.000
Trial: 1 / FS: 1518 / Iter: 3	78	78	629876.6	7649.222	Tx : Rx : Loss : Loss% :	12597529.000 12597529.000 0 0.00	825	935	872.000
Trial: 1 / FS: 1518 / Iter: 4	89	89	721310.4	8759.594	Tx : Rx : Loss : Loss% :	14426203.000 14426203.000 0 0.00	825	922	872.000

Trial: 1 / FS: 1518 / Iter: 5	94	94	767027.4	9314.781	Tx :	15340540.000	825	922	872.000
					Rx :	15340540.000			
					Loss :	0			
					Loss% :	0.00			
Trial: 1 / FS: 1518 / Iter: 6	97	97	789885.5	9592.370	Tx :	15797708.000	825	942	873.000
					Rx :	15797708.000			
					Loss :	0			
					Loss% :	0.00			
Trial: 1 / FS: 1518 / Iter: 7	99	99	801314.7	9731.165	Tx :	16026292.000	842	947	879.000
					Rx :	16026292.000			
					Loss :	0			
					Loss% :	0.00			
Trial: 1 / FS: 1518 / Iter: 8	99	99	807029.2	9800.563	Tx :	16140584.000	850	955	884.000
					Rx :	16140584.000			
					Loss :	0			
					Loss% :	0.00			
Trial: 1 / FS: 1518 / Iter: 9	100	100	812743.8	9869.961	Tx :	16254876.000	895	982	909.000
					Rx :	16254876.000			
					Loss :	0			
					Loss% :	0.00			

RFC2544 - Throughput/Latency - Per Flow Statistics - Part 1 of 2

Trial / Framesize / Iteration	Tx Port	Rx Port	Flow Group	L2 Throughput				L1 Throughput		Throughput (frames)
				Tx Rate %	Rx Rate			Tx Rate Mbps	Rx Rate Mbps	
					%	FPS	Mbps			
Trial: 1 / FS: 64 / Iter: 9	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	100.00	100	14880952.4	7619.05			Tx : 297619048 Rx : 297619048 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 9	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	100.00	100	8445945.9	8648.65			Tx : 168918919 Rx : 168918919 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 9	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	100.00	100	4528985.5	9275.36			Tx : 90579710 Rx : 90579710 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 9	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	100.00	100	2349624.1	9624.06			Tx : 46992481 Rx : 46992481 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 9	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	100.00	100	1197318.0	9808.43			Tx : 23946360 Rx : 23946360 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 9	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	100.00	100	961538.5	9846.15			Tx : 19230769 Rx : 19230769 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 9	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	100.00	100	812743.8	9869.96			Tx : 16254876 Rx : 16254876 Loss : 0 Loss% : 0.000

RFC2544 - Throughput/Latency - Per Flow Statistics - Part 2 of 2

Trial / Framesize / Iteration	Tx Port	Rx Port	Flow Group	Min Latency (ns)	Max Latency (ns)	Avg Latency (ns)
Trial: 1 / FS: 64 / Iter: 9	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	815	922	850
Trial: 1 / FS: 128 / Iter: 9	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	852	987	915
Trial: 1 / FS: 256 / Iter: 9	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	862	987	915
Trial: 1 / FS: 512 / Iter: 9	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	862	987	913
Trial: 1 / FS: 1024 / Iter: 9	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	850	985	909
Trial: 1 / FS: 1280 / Iter: 9	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	895	995	913
Trial: 1 / FS: 1518 / Iter: 9	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	895	982	909

RFC2544 - Throughput/Latency - Iteration Statistics - Part 1 of 2

Trial / Framesize / Iteration	Tx Port	Rx Port	Flow Group	L2 Throughput				L1 Throughput		Throughput (frames)		
				Tx Rate %	Rx Rate			Tx Rate Mbps	Rx Rate Mbps			
					%	FPS	Mbps					
Trial: 1 / FS: 64 / Iter: 1	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	10.00	10.00	1488095.2	761.91			Tx : 29761905 Rx : 29761905 Loss : 0 Loss% : 0.000		
Trial: 1 / FS: 64 / Iter: 2	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	55.00	55.00	8184561.9	4190.50			Tx : 163690476 Rx : 163690476 Loss : 0 Loss% : 0.000		
Trial: 1 / FS: 64 / Iter: 3	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	77.50	77.50	11532778.3	5904.78			Tx : 230654762 Rx : 230654762 Loss : 0 Loss% : 0.000		
Trial: 1 / FS: 64 / Iter: 4	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	88.75	88.75	13206904.7	6761.94			Tx : 264136905 Rx : 264136905 Loss : 0 Loss% : 0.000		
Trial: 1 / FS: 64 / Iter: 5	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	94.38	94.38	14044019.2	7190.54			Tx : 280877976 Rx : 280877976 Loss : 0 Loss% : 0.000		
Trial: 1 / FS: 64 / Iter: 6	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	97.19	97.19	14462459.7	7404.78			Tx : 289248512 Rx : 289248512 Loss : 0 Loss% : 0.000		
Trial: 1 / FS: 64 / Iter: 7	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	98.59	98.59	14671832.4	7511.98			Tx : 293433780 Rx : 293433780 Loss : 0 Loss% : 0.000		
Trial: 1 / FS: 64 / Iter: 8	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	99.30	99.30	14776334.8	7565.48			Tx : 295526414 Rx : 295526414 Loss : 0 Loss% : 0.000		
Trial: 1 / FS: 64 / Iter: 9	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	100.00	100.00	14880952.4	7619.05			Tx : 297619048 Rx : 297619048 Loss : 0 Loss% : 0.000		
Trial: 1 / FS: 128 / Iter: 1	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	10.00	10.00	844594.6	864.87			Tx : 16891892 Rx : 16891892 Loss : 0 Loss% : 0.000		
Trial: 1 / FS: 128 / Iter: 2	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	55.00	55.00	4645271.8	4756.76			Tx : 92905405 Rx : 92905405 Loss : 0 Loss% : 0.000		
Trial: 1 / FS: 128 / Iter: 3	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	77.50	77.50	6545640.5	6702.74			Tx : 130912162 Rx : 130912162 Loss : 0 Loss% : 0.000		
Trial: 1 / FS: 128 / Iter: 4	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	88.75	88.75	7495812.9	7675.71			Tx : 149915541 Rx : 149915541 Loss : 0 Loss% : 0.000		

Trial: 1 / FS: 128 / Iter: 5	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	94.38	94.38	7970906.2	8162.21	Tx : 159417230 Rx : 159417230 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 6	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	97.19	97.19	8208443.1	8405.45	Tx : 164168074 Rx : 164168074 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 7	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	98.59	98.59	8327207.2	8527.06	Tx : 166543497 Rx : 166543497 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 8	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	99.30	99.30	8386568.4	8587.85	Tx : 167731208 Rx : 167731208 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 128 / Iter: 9	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	100.00	100.00	8445945.9	8648.65	Tx : 168918919 Rx : 168918919 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 1	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	10.00	10.00	452898.6	927.54	Tx : 9057971 Rx : 9057971 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 2	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	55.00	55.00	2490946.0	5101.46	Tx : 49818841 Rx : 49818841 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 3	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	77.50	77.50	3509965.0	7188.41	Tx : 70199275 Rx : 70199275 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 4	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	88.75	88.75	4019481.9	8231.90	Tx : 80389493 Rx : 80389493 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 5	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	94.38	94.38	4274232.1	8753.63	Tx : 85484601 Rx : 85484601 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 6	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	97.19	97.19	4401620.4	9014.52	Tx : 88032156 Rx : 88032156 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 7	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	98.59	98.59	4465298.0	9144.93	Tx : 89305933 Rx : 89305933 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 8	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	99.30	99.30	4497145.4	9210.15	Tx : 89942822 Rx : 89942822 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 256 / Iter: 9	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	100.00	100.00	4528985.5	9275.36	Tx : 90579710 Rx : 90579710 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 1	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	10.00	10.00	234962.4	962.41	Tx : 4699248 Rx : 4699248 Loss : 0 Loss% : 0.000

Trial: 1 / FS: 512 / Iter: 2	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	55.00	55.00	1292293.6	5293.24	Tx : 25845865 Rx : 25845865 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 3	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	77.50	77.50	1820959.8	7458.65	Tx : 36419173 Rx : 36419173 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 4	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	88.75	88.75	2085291.7	8541.36	Tx : 41705827 Rx : 41705827 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 5	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	94.38	94.38	2217460.1	9082.72	Tx : 44349154 Rx : 44349154 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 6	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	97.19	97.19	2283540.8	9353.38	Tx : 45670818 Rx : 45670818 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 7	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	98.59	98.59	2316582.8	9488.72	Tx : 46331649 Rx : 46331649 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 8	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	99.30	99.30	2333105.5	9556.40	Tx : 46662065 Rx : 46662065 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 512 / Iter: 9	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	100.00	100.00	2349624.1	9624.06	Tx : 46992481 Rx : 46992481 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 1	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	10.00	10.00	119731.8	980.84	Tx : 2394636 Rx : 2394636 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 2	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	55.00	55.00	658525.0	5394.64	Tx : 13170498 Rx : 13170498 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 3	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	77.50	77.50	927921.5	7601.53	Tx : 18558429 Rx : 18558429 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 4	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	88.75	88.75	1062619.9	8704.98	Tx : 21252395 Rx : 21252395 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 5	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	94.38	94.38	1129969.4	9256.71	Tx : 22599377 Rx : 22599377 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 6	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	97.19	97.19	1163643.8	9532.57	Tx : 23272869 Rx : 23272869 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 7	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	98.59	98.59	1180480.8	9670.50	Tx : 23609614 Rx : 23609614 Loss : 0 Loss% : 0.000

Trial: 1 / FS: 1024 / Iter: 8	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	99.30	99.30	1188899.4	9739.46	Tx : 23777987 Rx : 23777987 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1024 / Iter: 9	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	100.00	100.00	1197318.0	9808.43	Tx : 23946360 Rx : 23946360 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 1	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	10.00	10.00	96153.8	984.62	Tx : 1923077 Rx : 1923077 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 2	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	55.00	55.00	528846.3	5415.39	Tx : 10576923 Rx : 10576923 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 3	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	77.50	77.50	745192.5	7630.77	Tx : 14903846 Rx : 14903846 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 4	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	88.75	88.75	853365.8	8738.47	Tx : 17067308 Rx : 17067308 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 5	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	94.38	94.38	907452.0	9292.31	Tx : 18149038 Rx : 18149038 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 6	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	97.19	97.19	934495.5	9569.23	Tx : 18689904 Rx : 18689904 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 7	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	98.59	98.59	948016.8	9707.69	Tx : 18960337 Rx : 18960337 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 8	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	99.30	99.30	954777.8	9776.93	Tx : 19095553 Rx : 19095553 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1280 / Iter: 9	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	100.00	100.00	961538.5	9846.15	Tx : 19230769 Rx : 19230769 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 1	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	10.00	10.00	81274.4	987.00	Tx : 1625488 Rx : 1625488 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 2	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	55.00	55.00	447009.2	5428.48	Tx : 8940182 Rx : 8940182 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 3	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	77.50	77.50	629876.6	7649.22	Tx : 12597529 Rx : 12597529 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 4	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	88.75	88.75	721310.4	8759.59	Tx : 14426203 Rx : 14426203 Loss : 0 Loss% : 0.000

Trial: 1 / FS: 1518 / Iter: 5	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	94.38	94.38	767027.4	9314.78	Tx : 15340540 Rx : 15340540 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 6	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	97.19	97.19	789885.5	9592.37	Tx : 15797708 Rx : 15797708 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 7	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	98.59	98.59	801314.7	9731.17	Tx : 16026292 Rx : 16026292 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 8	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	99.30	99.30	807029.2	9800.56	Tx : 16140584 Rx : 16140584 Loss : 0 Loss% : 0.000
Trial: 1 / FS: 1518 / Iter: 9	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	100.00	100.00	812743.8	9869.96	Tx : 16254876 Rx : 16254876 Loss : 0 Loss% : 0.000

RFC2544 - Throughput/Latency - Iteration Statistics - Part 2 of 2

Trial / Framesize / Iteration	Tx Port	Rx Port	Flow Group	Min Latency (ns)	Max Latency (ns)	Avg Latency (ns)
Trial: 1 / FS: 64 / Iter: 1	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	757	855	810.00
Trial: 1 / FS: 64 / Iter: 2	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	757	912	810.00
Trial: 1 / FS: 64 / Iter: 3	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	775	900	815.00
Trial: 1 / FS: 64 / Iter: 4	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	790	900	820.00
Trial: 1 / FS: 64 / Iter: 5	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	797	912	826.00
Trial: 1 / FS: 64 / Iter: 6	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	802	915	830.00
Trial: 1 / FS: 64 / Iter: 7	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	810	915	834.00
Trial: 1 / FS: 64 / Iter: 8	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	807	912	837.00
Trial: 1 / FS: 64 / Iter: 9	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	815	922	850.00
Trial: 1 / FS: 128 / Iter: 1	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	760	857	811.00
Trial: 1 / FS: 128 / Iter: 2	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	760	902	811.00
Trial: 1 / FS: 128 / Iter: 3	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	762	965	851.00
Trial: 1 / FS: 128 / Iter: 4	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	835	967	874.00
Trial: 1 / FS: 128 / Iter: 5	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	835	972	875.00
Trial: 1 / FS: 128 / Iter: 6	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	835	960	878.00
Trial: 1 / FS: 128 / Iter: 7	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	845	970	885.00
Trial: 1 / FS: 128 / Iter: 8	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	867	980	896.00
Trial: 1 / FS: 128 / Iter: 9	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	852	987	915.00
Trial: 1 / FS: 256 / Iter: 1	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	822	920	874.00

Trial: 1 / FS: 256 / Iter: 2	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	822	930	874.00
Trial: 1 / FS: 256 / Iter: 3	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	822	922	874.00
Trial: 1 / FS: 256 / Iter: 4	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	830	937	875.00
Trial: 1 / FS: 256 / Iter: 5	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	835	950	882.00
Trial: 1 / FS: 256 / Iter: 6	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	850	967	888.00
Trial: 1 / FS: 256 / Iter: 7	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	862	965	893.00
Trial: 1 / FS: 256 / Iter: 8	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	862	977	896.00
Trial: 1 / FS: 256 / Iter: 9	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	862	987	915.00
Trial: 1 / FS: 512 / Iter: 1	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	822	920	869.00
Trial: 1 / FS: 512 / Iter: 2	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	822	920	869.00
Trial: 1 / FS: 512 / Iter: 3	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	822	920	869.00
Trial: 1 / FS: 512 / Iter: 4	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	825	942	870.00
Trial: 1 / FS: 512 / Iter: 5	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	830	967	872.00
Trial: 1 / FS: 512 / Iter: 6	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	832	962	876.00
Trial: 1 / FS: 512 / Iter: 7	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	845	965	882.00
Trial: 1 / FS: 512 / Iter: 8	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	857	972	888.00
Trial: 1 / FS: 512 / Iter: 9	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	862	987	913.00
Trial: 1 / FS: 1024 / Iter: 1	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	822	920	869.00
Trial: 1 / FS: 1024 / Iter: 2	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	822	920	869.00
Trial: 1 / FS: 1024 / Iter: 3	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	822	920	869.00
Trial: 1 / FS: 1024 / Iter: 4	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	822	920	869.00

Trial: 1 / FS: 1024 / Iter: 5	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	822	920	869.00
Trial: 1 / FS: 1024 / Iter: 6	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	822	935	870.00
Trial: 1 / FS: 1024 / Iter: 7	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	825	970	871.00
Trial: 1 / FS: 1024 / Iter: 8	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	835	967	877.00
Trial: 1 / FS: 1024 / Iter: 9	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	850	985	909.00
Trial: 1 / FS: 1280 / Iter: 1	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	822	932	874.00
Trial: 1 / FS: 1280 / Iter: 2	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	822	932	874.00
Trial: 1 / FS: 1280 / Iter: 3	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	822	932	874.00
Trial: 1 / FS: 1280 / Iter: 4	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	822	967	874.00
Trial: 1 / FS: 1280 / Iter: 5	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	822	932	874.00
Trial: 1 / FS: 1280 / Iter: 6	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	835	955	877.00
Trial: 1 / FS: 1280 / Iter: 7	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	850	952	882.00
Trial: 1 / FS: 1280 / Iter: 8	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	837	955	887.00
Trial: 1 / FS: 1280 / Iter: 9	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	895	995	913.00
Trial: 1 / FS: 1518 / Iter: 1	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	825	922	872.00
Trial: 1 / FS: 1518 / Iter: 2	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	825	962	872.00
Trial: 1 / FS: 1518 / Iter: 3	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	825	935	872.00
Trial: 1 / FS: 1518 / Iter: 4	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	825	922	872.00
Trial: 1 / FS: 1518 / Iter: 5	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	825	922	872.00
Trial: 1 / FS: 1518 / Iter: 6	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	825	942	873.00
Trial: 1 / FS: 1518 / Iter: 7	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	842	947	879.00



Trial: 1 / FS: 1518 / Iter: 8	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	850	955	884.00
Trial: 1 / FS: 1518 / Iter: 9	Ethernet - 001	Ethernet - 002	S5900-24S4T2Q #1-Endpoint Set-1 - Flow Group 0001	895	982	909.00

Theoretical maximum Frame Rates (frames/second) for different frame sizes (bytes)

Speed	64	128	256	512	1024	1280	1518
10 Mbps	14881	8446	4529	2350	1198	962	813
100 Mbps	148810	84460	45290	23497	11973	9616	8128
1000 Mbps	1488096	844595	452899	234963	119732	96154	81275
10 Gbps	14880952	8445946	4528986	2349625	1197318	961539	812744
25 Gbps	37202380	21114864	11322463	5874060	2993295	2403846	2031859
40 Gbps	59523809	33783783	18115942	9398496	4789272	3846153	3250975
100 Gbps	148809523	84459459	45289855	23496240	11973180	9615384	8127438
155 Mbps (Oc - 3)	288000	145116	72840	36491	18263	14614	12324
622 Mbps (Oc - 12)	1152000	580465	291362	145965	73054	58454	49296
2488 Mbps (Oc - 48)	4608000	2321860	1165447	583860	292215	233817	197182
9952 Mbps (Oc - 192)	18432000	9287442	4661790	2335439	1168859	935270	788730